

The Revie Flex (EFF692SA3S) is a flexible PCB antenna for use in LTE CAT M1 and NB-IoT devices. The antenna is optimized for use when mounted to plastic via the supplied adhesive backing. This antenna operates within 698 - 875 MHz and 1710 – 2500 MHz with excellent radiation performance. The high efficiency ensures reliable connection in a variety of integration environments.

### FEATURES AND BENEFITS

- Ground plane independent
- Optimized for LTE CAT M1 and NB-IoT
- Wide bandwidth, pairs with all radios in specified frequency range
- Excellent efficiency: >51%
- Easy peel-and-stick Integration
- Alternative connectors and cable lengths available

### ELECTRICAL SPECIFICATIONS

Laird Part Number	EFF692SA3S	
	698 - 875	1710 - 2500
Operating Frequency (MHz)	698 - 875	1710 - 2500
Number of Ports	1	1
VSWR – Max	2.5:1	2.5:1
Gain (dBi)	1.9	3.7
Efficiency (%)*	51	80
Nominal Impedance (Ohms)	50	50
Max Power - Ambient 25°C (W)	5	5
Polarization	Linear	

\* A minimum cable length of 153 mm is required to achieve the stated efficiency.

### MECHANICAL SPECIFICATIONS

Dimensions – diameter x height – mm (inches)	90 x 20 x 0.16 (3.54 x 0.79 x 0.006)
Cable Type	1.13 mm
Connector	IPEX MHF1 (u.FL)
Cable Length mm	153
Adhesive Type	3M 467MP


### ENVIRONMENTAL SPECIFICATIONS

Operating Environment (Indoor or Outdoor)	Integrated/embedded
---	---------------------


### CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR
EFF6925A3S-15MHF1	153	IPEX MHF1 (u.FL)


MECHANICAL DRAWING



RADIATION PATTERNS




787 MHz




RADIATION PATTERNS


793 MHz



862 MHz




875 MHz




RADIATION PATTERNS


1710 MHz



1850 MHz




1990 MHz




RADIATION PATTERNS


2155 MHz



2400 MHz



2500 MHz



**✓RoHS**

**Americas:** +1.847.839.6925  
 IAS-AmericasSales@lairdtech.com  
**Europe:** +44.1628.858941  
 IAS-EUSales@lairdtech.com  
**Asia:** IAS-AsiaSales@lairdtech.com  
**Middle East and Africa:** +44.1628.858941  
 IAS-MEASales@lairdtech.com  
<https://connectivity.lairdtech.com>

Laird warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations Laird will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the Laird product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2019 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.

