



Date: 11/08/2007

MAIDA STYLE NUMBER D7311ZOV400RA03T17

MAIDA ITEM NUMBER 01-0295

CUSTOMER FUTURE

CUSTOMER P/N N/A

CONTACT ERIN BLACK

**VARISTOR SPEC SHEET**

**Electrical Specifications**


Continuous AC Voltage	40	VAC
Continuous DC Voltage	56	VDC
Maximum DC Leakage @ 56 VDC	200	uA
Low Varistor Voltage Limit	61	VDC
High Varistor Voltage Limit	75	VDC
Nominal Varistor Voltage	68	VDC
Current for Varistor Voltage	1	mA
Maximum Clamp Voltage	135	V
Maximum Clamp Voltage Test Current	2.5	A
Peak Current Rating (1 Pulse)	500	A
Peak Current Rating (2 Pulse)	250	A
Energy Rating (8X20us)	J	
Energy Rating (10X1000us)	5.2	J
Typical Capacitance	945	pF
Impulse Response Time	< 50	ns
Minimum Hipot of Coating	2500	VDC
Minimum I.R. of Coating	1000	MΩ

**Physical Specifications**

Lead Style	076F
X Nominal	0.2 in.
X Tolerance	0.03 in.
Lead Length Nominal	TAPE in.
Lead Length Tolerance	& REEL in.
Y Nominal	0.055 in.
Y Tolerance	0.03 in.
d Nominal	0.025 in.
Wire Gauge	22 AWG
Minimum Marking	Z400-03UL
Nominal Disk Size	7 mm
D Maximum	0.354 in.
T Maximum	0.211 in.
H Maximum	0.554 in.

**Thermal Specifications**

Minimum Operating Temperature	-40	°C
Maximum Operating Temperature	85	°C
Varistor Voltage Temperature Coeff	-0.05	%/°C
Minimum Storage Temperature	-50	°C
Maximum Storage Temperature	125	°C
Current/Energy Derating Above 85°C	-2.5	%/°C



\* Contact Maida for a more detailed configuration drawing.

**Notes**

Lead Free - Complies with RoHS



**DEVELOPMENT COMPANY**

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194

**Safety Agency Recognitions**

UL 1449 File Number	E86730
UL 1414 File Number	
UL 497B File Number	E180012
CSA File Number	
VDE File Number	
SEV File Number	