





# Major League Electronics .100 cl Low Profile Terminal Strip Headers - Horizontal



Tails may be clipped to achieve desired pin length

## Ordering Information

LTSHSM-1   - S -  -  - H -  -  -  - LF

Pins Per Row  
01 - 50

Row Specification  
S = Single Row

Pin Options		
Post Height		
.120	3.05mm	01
.230	5.84mm	02
.330	8.38mm	04
.430	10.92mm	06
.530	13.46mm	08
.630	16.00mm	10
.730	18.54mm	12

Packing Information  
TR-P = Tape and Reel with Plastic Pick and Place pad  
TB-P = Tube with Plastic Pick and Place pad  
TB-0 = Tube without Pick and Place Pad  
*If left blank, packaging at MLE's discretion  
Pad may be metal, mylar or plastic*

Polarized Position  
Leave blank if not needed  
If required, specify empty pin position, e.g. 012 for Pin 12

Horizontal

Plating Options	
H	30µ Gold on Contact Area / Matte Tin on Tail
T	Matte Tin All Over
GT	10µ Gold on Contact Area / Matte Tin on Tail
F	Gold Flash over Entire Pin
G	10µ Gold on Contact Area / Flash on Tail

## Specifications


Current Rating: 3.0 Ampere  
Insulation Resistance: 1000MΩ Min.  
Dielectric Withstanding: 600V AC  
Contact Resistance: 20 mΩ Max.  
Operating Temperature: -40°C to + 105°C  
Max. Process Temperature:  
Peak: 260°C up to 20 secs.  
Process: 230°C up to 60 secs.  
Wave: 260°C up to 6 secs.  
Reflow: 260°C up to 10 secs.  
Manual Solder: 350°C up to 5 secs.

## Materials

Contact Material: Phosphor Bronze  
Insulator Material: Nylon 6T  
Plating: Au or Sn over 50µ" (1,27) Ni

## Mates with:

BCSS,  
BSSH,  
BSSHCH,  
BSSQC,  
BSSQM,  
LBCSS,  
LSMBC,  
LSWSS,  
SMBC,  
SSHQ,  
SSHQR,  
SSHR,  
SSHS,  
SSHSM



Products cut to specific sizes are uncancellable/nonreturnable

Parts are subject to change without notice

LTSHSM-1-SH SERIES

.100 cl Single Row - Low Profile  
Terminal Strip Headers - Horizontal

29 JAN 07

Scale  
NTS

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS IN INCHES (MM)  
TOLERANCES ARE:

ONE PLACE DECIMALS ±.100  
TWO PLACE DECIMALS ±.010  
THREE PLACE DECIMALS ±.005  
FOUR PLACE DECIMALS ±.0020  
ANGLES  
±5°



4235 Earnings Way, New Albany, Indiana, 47150, USA  
1-800-782-3486 (USA/Canada/Mexico)

Tel: 812-944-7244

Fax: 812-944-7268

E-mail: mle@mlelectronics.com

Web: www.mlelectronics.com

Edition  
1

Sheet  
1/1