




Major League Electronics .100 cl Terminal Strip Headers - Straight



Tails may be clipped to achieve desired pin length

Ordering Information

TSHS-1 [XX] - S - [XX] - [XX] - [XX] - [XX] - [XX] - [XX] - LF

Pins Per Row
01 - 50

Row Specification
S = Single

Lead Free

Every Other Pin Filled (.200 Centers)
E = Filled

Polarized Position
Leave blank if not needed
If required, specify empty pin position, e.g. 012 for Pin 12

Lock Tight "LT" (Optional)
Leave blank if not needed
LT = With

Pin Option						
Length	Tail With .230 Post	Tail With .230 Post	Tail With .318 Post	Tail With .318 Post		
.430	10.92	.100	2.54	N/A	N/A	06
.445	11.30	.115	2.92	N/A	N/A	08
.456	11.58	.126	3.20	N/A	N/A	10
.480	12.19	.150	3.81	N/A	N/A	11
.530	13.46	.200	5.08	.112	2.84	14
.630	16.00	.300	7.62	.212	5.38	16
.730	18.54	.400	10.16	.312	7.92	20
.830	21.08	.500	12.70	.412	10.46	22
.930	23.62	.600	15.24	.512	13.00	24
1.030	26.16	.700	17.78	.612	15.54	26
1.130	28.70	.800	20.32	.712	18.08	28
1.230	31.24	.900	22.86	.812	20.62	30
1.330	33.78	1.000	25.40	.912	23.16	32
1.430	36.32	1.100	27.94	1.012	25.70	34
1.530	38.86	1.200	30.48	1.112	28.25	36

Post Height
A = .230 (5.84)
B = .318 (8.08)

Plating Options	
G	- 10 μ Gold on Contact area/Flash on Tail
T	- Matte Tin all Over
F	- Gold Flash Over Entire Pin
GT	- 10 μ Gold on Contact Area / Matte Tin on Tail
H	- 30 μ Gold on Contact Area / Matte Tin on Tail

Specifications

Current Rating: 3.0 Ampere
Insulation Resistance: 1000M Ω Min.
Dielectric Withstanding: 600V AC
Contact Resistance: 20 m Ω Max.
Operating Temperature: -40°C to + 105°C
Max. Process Temperature:
Peak: 260°C up to 20 secs.
Process: 230°C up to 60 secs.
Wave: 260°C up to 6 secs.
Manual Solder: 350°C up to 5 secs.

Materials


Contact Material: Phosphor Bronze
Insulator Material: Nylon 6T
Plating: Au or Sn over 50 μ " (1,27) Ni

Products cut to specific sizes are uncancellable/nonreturnable

Parts are subject to change without notice

Mates with:

BCSS,
BSSH,
BSSHC,
BSSQ,
BSSQC,
BSSQM,
LBCSS,
LSMBC,
LSWSS,
SMBC,
SSHQ,
SSHQR,
SSHR,
SSHS,
SSHSM



TSHS-1-S SERIES

.100 cl Single Row
Terminal Strip Headers - Straight

12 DEC 06

Scale
NTS

UNLESS OTHERWISE SPECIFIED
DIMENSIONS IN INCHES (MM)
TOLERANCES ARE:

ONE PLACE DECIMALS $\pm .100$
TWO PLACE DECIMALS $\pm .010$
THREE PLACE DECIMALS $\pm .005$
FOUR PLACE DECIMALS $\pm .0020$
ANGLES
 $\pm .5^\circ$



4235 Earnings Way, New Albany, Indiana, 47150, USA
1-800-782-3486 (USA/Canada/Mexico)
Tel: 812-944-7244
Fax: 812-944-7268
E-mail: mie@melectronics.com
Web: www.melectronics.com

Edition
1

Sheet
1/1