

SERIES 1055 - SUBSUBMINIATURE SNAP-ACTION SWITCHES IP 67

TO 4 A 12 V OR 2 A 24 V DC



PRODUCT FEATURES

- ◆ Compact design with dust and water protected switching system acc. to IP 67 (basic types 1055 / 1058)
- ◆ Large overtravel of ≥ 1.2 mm for small size
- ◆ The specially designed pushbutton guide enables a start-up angle of 40°
- ◆ The modular principle offers a wide selection of connections, auxiliary actuators and fastening types

ON REQUEST

- ◆ Rating 0.5 (0.5) A 250 V AC 25E3 and ENEC approval mark
- ◆ For higher ambient temperatures
- ◆ Customized cable assembly
- ◆ Basic type 1058 as double switch or with cable outlet in other directions

Mechanical life endurance	1E6 at 10 mA 12 V
Contact resistance (new condition)	< 50 mOhm (1 A 12 V DC)
Insulation resistance (new condition)	> 100 MOhm (500 V DC)
Protection type	IP 00 connection side basic types 1055 and 1056 IP 40 actuator side basic type 1056 IP 67 actuator side basic type 1055, connection and actuator side basic type 1058
Ambient temperature	-40 °C ... +85 °C
Flammability	UL 94 HB
Material	actuator POM additional actuator stainless steel spring steel housing PBTP connections tinned basic type 1058: wires FLRY 0.5 mm ² , tinned wire ends
Contact material	Ag gold-plated
Approval marks	Ⓢ on request
Shock resistance	50 g
Miscellaneous	connection side cast electrical life endurance at 12 V 2 A: 200E3 (ohmic load)



ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

POWER TOOL SWITCHES

TACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS

SERIES 1055 - SUBSUBMINIATURE SNAP-ACTION SWITCHES IP 67

TO 4 A 12 V OR 2 A 24 V DC

	4 A 12 V DC (ohmic load)	2 A 24 V DC (ohmic load)	0.5 (0.5) A 250 V AC 25E3	Connection type	Connection description	Operating force in N	Operating position (OP) in mm	Difference travel max. in mm	Free position (FP) max. in mm	Permissible total travel position (TP) in mm	Actuator description	Lever drawing	Miscellaneous	Stock version
Normally closed contact (SPNC)														
1058.0395	●	●			400 long crimped	≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 1.5 long	
Normally open contact (SPNO)														
1058.0373	●	●			150 long	≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 1.5 long	
1058.0593	●	●			300 long	≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin both sides 5 long	
1058.5172	●	●			254 long	≤ 2.6	12.4 ±0.65	0.8	14.7	10.3		L21	pin left 5 long	
Changeover switch (SPDT momentary)														
1055.0351	●	●				≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 1.5 long	●
1055.0551	●	●				≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 5 long	
1055.0552	●	●				≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin left 5 long	
1055.2061	●	●			coded cranked	≤ 1.8	13.75 ±0.3	0.4	14.75	12.25			without pin	
1055.2351	●	●				≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 1.5 long	●
1055.3653	●	●				≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 2.5 long	
1055.3654	●	●				≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin left 2.5 long	
1055.5155	●	●				≤ 2.6	12.4 ±0.65	0.8	14.7	10.3		L21	pin both sides 2.5 long	
1055.5253	●	●				≤ 4.2	9.7 ±0.45	0.5	11.6	8.25		L31	pin both sides 2.5 long	
1055.5350	●	●				≤ 4.2	14.05 ±0.45	0.5	15.85	12.65		L02	without pin	
1055.7255	●	●				≤ 4.2	14.05 ±0.45	0.5	15.95	12.6		L31	without pin	
1055.8155	●	●				≤ 2.6	12.4 ±0.65	0.8	14.7	10.3		L21	pin right 2.5 long	
1056.0351	●	●				≤ 1.3	6.15 ±0.3	0.4	7.15	4.65			pin right 1.5 long	●
1056.2351	●	●				≤ 1.3	6.15 ±0.3	0.4	7.15	4.65			pin right 1.5 long	●
1056.3060	●	●			coded cranked	≤ 1.3	10.5 ±0.3	0.4	11.5	9			without pin	
1056.3065	●	●	●		coded cranked	≤ 1.3	10.5 ±0.3	0.4	11.5	9			without pin	
1056.3351	●	●				≤ 1.3	6.15 ±0.3	0.4	7.15	4.65			pin right 1.5 long	
1056.3352	●	●				≤ 1.3	6.15 ±0.3	0.4	7.15	4.65			pin left 1.5 long	●
1058.0351	●	●			300 long	≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin right 1.5 long	●
1058.0553	●	●			300 long	≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin both sides 5 long	
1058.0653	●	●			300 long	≤ 1.8	9.4 ±0.3	0.4	10.4	7.9			pin both sides 2.5 long	●
1058.5253	●	●			300 long	≤ 4.2	9.7 ±0.45	0.5	11.6	8.25		L31	pin both sides 2.5 long	

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

POWER TOOL SWITCHES

TACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO SIGNAL SWITCHES

SENSORS