

Marquardt Produktkatalog



[Automotive switches and systems](#)[Power tool switches](#)[Standard switches and sensors](#)



Full text search...

GO

Productfinder

[General information](#)[Rocker switches](#)[Pushbutton switches](#)[Toggle switches](#)[Slide switches](#)[Rotary switches](#)[Foot switches](#)[Tact and key switches](#)[Snap-action switches](#)[Micro-signal switches](#)[Sensors](#)[Accessories](#)[Catalog request / download](#)

SERIES 1550 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES - TO 16 (4) A 250 V AC

[Show all products](#) [Send request](#)

Product 17 of 37


[Previous](#) [Next](#)


[Technical data](#)

Product image / drawing



Similar to original product





X = wall thickness

X	Y	Z
0.8 ... 5.0	27.2 ±0.1	12.2 +0.2

Further information

- [Drawing](#)

Technical data

Product number	1555.3108	
Actuator color / printing		
Inrush current (capacitive)	100 A	
Switching function	ON / OFF switch (DPST)	
Number of poles	2-pole	
connections	Quick-connect terminal, 6.3	
Mechanical life endurance	5E4	
Rating IEC	10 (4) A 250 V AC 5E4 16 (4) A 250 V AC 1E4	
Rating North America	16 A 250 V AC 2 HP	
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm	
Insulation resistance (new condition)	> 100 (500 V DC) MOhm	
Proof tracking	250 PTI	
Protection type	Connection	IP 40
	Connection side min.	-20 °C
	Connection side max.	100 °C
Temperature	Actuation side min.	-20 °C
	Actuation side max.	55 °C
Flammability	UL 94 V-2	
Glow wire test temperature	850 °C	
Actuators and additional actuators	PA, black	
Housing description	PA, black	

Contact material	Ag
Contact distance	$\geq 3\text{ mm}$
Lighting	230 V
Plug force of the terminals	$\leq 80\text{ N}$
Approval marks	CSA / ENEC 05 / UL
Suitable for appliances of protection class	II
Stock version	•

[Back](#)

[Home](#)[Imprint](#)[Privacy Notice](#)[Terms of Service](#)[Site map](#)
[Print](#)