

Data sheet

RT076xxHBLU Typ 093

Page 1/6

P/N
310931xx

xx=number of poles


2019/10/24

Version: V


Illustrations



Dimensional drawing



Drill pattern



See enlarged drawings at the end of document



Product specification

- screw type terminal block, solderable, double solder pins
- centerline 5.08 mm, direction of connection 90°
- lift system, modular
- color black
- double stacked

Technical Data

General Data			
Tightening torque SEV	0.5 Nm		
Tightening torque UL	7 lb-in		
Solder pin length	3.4 mm		
min. number of poles	4		
max. number of poles	16		
Insulating material class	CTI 600		
clearance/creepage dist.	3.2 mm		
protection category	IP10		
Min. insul. strip length	6 mm		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	50 V	250 V	250 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Connection Data	
rat.wiring solid AWGmax	0.34 mm ² - 1.5 mm ² / AWG 26 - AWG 16
rat.wiring strand.AWGmax	0.34 mm ² - 1.5 mm ² / AWG 26 - AWG 16

Approvals	
 V / A / AWG	300 / 10 / 26 - 16
approval UL - File No.	E121004
 1.5 mm ²	250 V / 17.5 A / 17.5A / T60

Material	
insulating material	PA66
flammability class	V0
contact material	CuSn
contact surface	Sn
terminal body material	CuZn
terminal body surface	Ni
screw surface	Zn Cr(VI)-frei/free
screw thread	M3
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13
REACH - substance (SVHC)	Lead / 7439-92-1

Data sheet
RT076xxHBLU Typ 093

Page 3/6

P/N
310931xx**xx=number of poles**

2019/10/24

Version: V

Technical Data**Climatic Data**

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

Tolerance	ISO 2768 -mH
Solderability	Acc. to JEDEC JESD22-B102E 245°C/5s



Data sheet RT076xxHBLU Typ 093

Page 4/6

P/N
310931xx

xx=number of poles

2019/10/24

Version: V


Accessories

P/N	Designation
711401-092-02-2	711401
711401-092-03-2	711401



Illustrations


Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 5.08 \text{ mm [0.2]}$

Illustrations

Drill pattern



© 2019 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!

