


- Our lowest profile DIP socket with an above PCB height of only 2,41mm.
- Special short Hi-Rel, 4-finger BeCu #12 contact is rated at 3 amps. See page 218 for details.
- Series 115 use MM #1534 pins. See page 132 for details.
- Insulators are high temperature thermoplastic.



Total number of pins	Pin Configuration			Quantity per tube	Ordering Information
	A	B	C		

Total number of pins	A	B	C	Quantity per tube	Ordering Information
6	7,6	7,62	10,1	68	115-XX-306-41-003000
8	10,1	7,62	10,1	50	115-XX-308-41-003000
14	17,7	7,62	10,1	28	115-XX-314-41-003000
16	20,3	7,62	10,1	25	115-XX-316-41-003000
18	22,8	7,62	10,1	22	115-XX-318-41-003000
20	25,3	7,62	10,1	20	115-XX-320-41-003000
22	27,8	7,62	10,1	18	115-XX-322-41-003000
24	30,4	7,62	10,1	16	115-XX-324-41-003000
28	35,5	7,62	10,1	14	115-XX-328-41-003000
20	25,4	10,16	12,7	20	115-XX-420-41-003000
22	27,8	10,16	12,7	18	115-XX-422-41-003000
24	30,4	10,16	12,7	16	115-XX-424-41-003000
28	35,5	10,16	12,7	14	115-XX-428-41-003000
24	30,4	15,24	17,7	16	115-XX-624-41-003000
28	35,5	15,24	17,7	14	115-XX-628-41-003000
32	40,6	15,24	17,7	12	115-XX-632-41-003000
36	45,7	15,24	17,7	11	115-XX-636-41-003000
40	50,8	15,24	17,7	10	115-XX-640-41-003000
48	60,9	15,24	17,7	8	115-XX-648-41-003000
50	63,5	15,24	17,7	8	115-XX-650-41-003000



For RoHS compliance select \diamond plating code.

For Electrical, Mechanical & Environmental Data, See pg. 4

XX=Plating Code See Below

SPECIFY PLATING CODE XX=				93			43 \diamond	44 \diamond
Sleeve (Pin)				5,08 μ m Sn/Pb			5,08 μ m Sn	5,08 μ m Sn
Contact (Clip)				0,76 μ m Au			0,76 μ m Au	5,08 μ m Sn