

<h3>0501</h3> <p>0501-0-15-XX-30-XX-04-0 Press-fit in 1,45 mounting hole</p>	<h3>8427</h3> <p>8427-0-15-XX-30-XX-04-0 Press-fit in 1,45 mounting hole</p>	<h3>1434</h3> <p>1434-0-15-XX-30-XX-10-0 Press-fit in 1,4 mounting hole</p>	<h3>9970</h3> <p>9970-0-15-XX-30-XX-04-0 Square press-fit for 0,81±0,05 plated thru hole</p>
---	---	--	---

<h3>5970</h3> <p>5970-X-15-XX-32-XX-04-0 Square press-fit for 0,81 or 1,0 ±0,05 plated thru hole</p>	<table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>U Square</th> <th>Mounting Hole</th> </tr> </thead> <tbody> <tr> <td>5970-1</td> <td>0,71</td> <td>0,81</td> </tr> <tr> <td>5970-2</td> <td>0,86</td> <td>1,0</td> </tr> </tbody> </table>	Basic Part Number	U Square	Mounting Hole	5970-1	0,71	0,81	5970-2	0,86	1,0	<h3>0477/0478</h3> <p>047X-0-18-XX-30-XX-04-0 Solderless press-fit in 0,97 +0,08 / -0,05 plated thru hole (use 1.1mm drill prior to plating)</p>	<table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Board Thickness</th> <th>Length V</th> <th>Length A</th> </tr> </thead> <tbody> <tr> <td>0477-0</td> <td>1,57</td> <td>1,91</td> <td>4,45</td> </tr> <tr> <td>0478-0</td> <td>3,18</td> <td>3,56</td> <td>6,35</td> </tr> </tbody> </table>	Basic Part Number	Board Thickness	Length V	Length A	0477-0	1,57	1,91	4,45	0478-0	3,18	3,56	6,35
Basic Part Number	U Square	Mounting Hole																						
5970-1	0,71	0,81																						
5970-2	0,86	1,0																						
Basic Part Number	Board Thickness	Length V	Length A																					
0477-0	1,57	1,91	4,45																					
0478-0	3,18	3,56	6,35																					

<h3>4612</h3> <p>4612-0-31-XX-30-XX-04-0 Compliant press-fit in 1,02 ±0,08 plated hole. For 1,52 → 2,54 thick board</p>	<h3>4613</h3> <p>4613-0-31-XX-30-XX-04-0 Compliant press-fit in 1,02 ±0,08 plated hole. For 2,29 → 3,30 thick board</p>	<h3>0680</h3> <p>0680-0-15-XX-32-XX-10-0 Solder mount in 1,3 min. mounting hole</p>	<h3>0149</h3> <p>0149-0-15-XX-30-XX-04-0 Press-fit in 1,5 mounting hole</p>
--	--	--	--

<h3>SPECIFICATIONS</h3> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>PART MANUFACTURED IN INCHES, METRIC FOR REF ONLY</p> <p>TOLERANCES ON: LENGTHS: ± 0,13 DIAMETERS: ± 0,05 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - XX - XX - 3X - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH: →</p> <p>01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL ◊ 15 0,25µm GOLD OVER NICKEL ◊</p> <p>SPECIFY CONTACT FINISH: →</p> <p>02 2,54µm TIN/LEAD OVER NICKEL 84 2,54µm TIN OVER NICKEL ◊ 27 0,76µm GOLD OVER NICKEL ◊</p> <p>SELECT CONTACT #30 or #32 CONTACT (DATA ON PAGE 208)</p>
---	---

