

- Our lowest profile DIP sockets with an above PCB height of 2,41mm.
- Special short, Hi-Rel, 4-finger BeCu #12 clip rated at 3 amps. See page 207 for details.
- Uses Mill-Max #1534 pin. See page 130 for details.

Total number of pins				Quantity per tube	<h2 style="margin: 0;">Ordering Information</h2>	
	A	B	C			

6	7,6	7,62	10,1	68		115-XX-306-41-003000
8	10,1	7,62	10,1	50		115-XX-308-41-003000
14	17,7	7,62	10,1	28		115-XX-314-41-003000
16	20,3	7,62	10,1	25		115-XX-316-41-003000
18	22,8	7,62	10,1	22		115-XX-318-41-003000
20	25,3	7,62	10,1	20		115-XX-320-41-003000
22	27,8	7,62	10,1	18		115-XX-322-41-003000
24	30,4	7,62	10,1	16		115-XX-324-41-003000
28	35,5	7,62	10,1	14		115-XX-328-41-003000
20	25,4	10,16	12,7	20		115-XX-420-41-003000
22	27,8	10,16	12,7	18		115-XX-422-41-003000
24	30,4	10,16	12,7	16		115-XX-424-41-003000
28	35,5	10,16	12,7	14		115-XX-428-41-003000
24	30,5	15,24	17,7	16		115-XX-624-41-003000
28	35,5	15,24	17,7	14		115-XX-628-41-003000
32	40,6	15,24	17,7	12		115-XX-632-41-003000
36	45,7	15,24	17,7	11		115-XX-636-41-003000
40	50,8	15,24	17,7	10		115-XX-640-41-003000
48	60,9	15,24	17,7	8		115-XX-648-41-003000
50	63,5	15,24	17,7	8		115-XX-650-41-003000

XX= Plating Code
See Below

For RoHS compliance, select \diamond plating code. For the all gold option (XX=13) also change part number from 115-XX-XXX-41-003000 to 115-13-XXX-41-003100

RoHS
2002/95/EC

SPECIFY PLATING CODE XX=	13 \diamond		93	99		43 \diamond	44 \diamond
Sleeve (Pin)	0,25 μ m Au		5,08 μ m Sn/Pb	5,08 μ m Sn/Pb		5,08 μ m Sn	5,08 μ m Sn
Contact (Clip)	0,76 μ m Au		0,76 μ m Au	5,08 μ m Sn/Pb		0,76 μ m Au	5,08 μ m Sn