



5062




5062-0-00-XX-00-00-33-0
Solder mount in .029 mounting hole

8451




8451-0-00-XX-00-00-33-0
Solder mount in .029 mounting hole

6477




6477-0-00-XX-00-00-38-0
Solder mount in .034 mounting hole

4477




4477-0-00-XX-00-00-33-0
Solder mount in .034 mounting hole

4268




4268-0-00-XX-00-00-33-0
Solder mount in .039 mounting hole

9086




9086-0-00-XX-00-00-33-0
Solder mount in .040 mounting hole

8330




8330-0-00-XX-00-00-38-0
Solder mount in .044 mounting hole

9228



9228-0-00-XX-00-00-38-0
Solder mount in .044 mounting hole


6095



6095-X-00-XX-00-00-38-0
Solder mount in .044 mounting hole

Basic Part Number	Pin Length L
6095-0	.580
6095-1	.475

6092



6092-0-00-XX-00-00-33-0
Solder mount in .044 mounting hole

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
(Except where noted)

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 3X - 0

BASIC PART #

SPECIFY PIN FINISH:
01 200µ" TIN/LEAD OVER NICKEL
80 200µ" TIN OVER NICKEL ◇
15 10µ" GOLD OVER NICKEL ◇
21 20µ" GOLD OVER NICKEL ◇
34 50µ" GOLD OVER NICKEL ◇

