


# Ultra Fast Rectifier

## 1N6304 — 1N6306



**Notes:**

1. 1/4-28UNF3A threads
2. Full threads within 2 1/2 threads
3. For Reverse Polarity add R to Part Number  
Standard Polarity: Stud is Cathode  
Reverse Polarity: Stud is Anode

Dim.	Inches		Millimeter		Notes
	Minimum	Maximum	Minimum	Maximum	
A	---	---	---	---	1
B	.669	.688	16.99	17.48	
C	---	.793	---	20.14	
D	.750	1.00	19.05	25.40	
E	.422	.453	10.72	11.51	
F	.115	.200	2.92	5.08	
G	---	.450	---	11.43	
H	.220	.249	5.59	6.32	2
J	---	.375	---	9.53	
K	.156	---	3.97	---	
M	---	.667	---	16.94	Dia
N	---	.080	---	2.03	
P	.140	.175	3.56	4.45	Dia

D0203AB (D05)

Microsemi Catalog Number

Working Peak Reverse Voltage

Peak Reverse Voltage

1N6304*	50V	50V
1N6305*	100V	100V
1N6306*	150V	150V

\*Add Suffix R For Reverse Polarity

- Ultra Fast Recovery Rectifier
- 70 Amps current rating
- 800 Amps surge rating
- $V_{RRM}$  50 to 150 Volts

### Electrical Characteristics

Average forward current  
Maximum surge current  
Max peak forward voltage  
Max peak reverse current  
Max peak reverse current  
Max reverse recovery time  
Typical junction capacitance

$I_F(AV)$  70 Amps       $T_C = 100^\circ\text{C}$ , Square wave,  $R_{\theta JC} = 0.8^\circ\text{C}/\text{W}$   
 $I_{FSM}$  800 Amps      8.3 ms, half sine  $T_C = 55^\circ\text{C}$   
 $V_{FM}$  .975 Volts       $I_{FM} = 70\text{A}$ :  $T_J = 25^\circ\text{C}^*$   
 $I_{RM}$  30 mA       $V_{RRM}$ ,  $T_J = 150^\circ\text{C}^*$   
 $I_{RM}$  25  $\mu\text{A}$        $V_{RRM}$ ,  $T_J = 25^\circ\text{C}$   
 $t_{RR}$  50 ns       $I_F = .5\text{A}$ ,  $I_R = 1\text{A}$ ,  $I_{(REC)} = .25\text{A}$ ,  $di/dt = 85\text{A}/\mu\text{s}$   
 $C_J$  300 pF       $V_R = 10\text{V}$ ,  $f = 1\text{MHz}$ ,  $T_J = 25^\circ\text{C}$

\*Pulse test: Pulse width 300  $\mu\text{sec}$ , Duty cycle 2%

### Thermal and Mechanical Characteristics

Storage temp range  
Operating junction temp range  
Max thermal resistance  
Mounting torque  
Weight

$T_{STG}$   
 $T_J$   
 $R_{\theta JC}$

-65°C to 175°C  
-65°C to 175°C  
0.8°C/W Junction to case  
25–30 inch pounds  
.54 ounces (15.3 grams) typical

# 1N6304 - 1N6306

Figure 1  
Typical Forward Characteristics




Figure 3  
Typical Junction Capacitance




Figure 4  
Forward Current Derating




Figure 2  
Typical Reverse Characteristics

