




PRODUCT NUMBER: 499-10-252-10-009000

www.mill-max.com  
DATA SHEET



#### General Info

<b>Description<sup>1</sup>:</b>	Right Angle Pin Header .018" (0,457mm) Pin Head
<b>Type:</b>	Interconnect
<b>Category:</b>	Machined Pin Header
<b>Mounting Style:</b>	Through Hole Solder Mount
<b>Tail Type:</b>	Solder Tail
<b># Pins:</b>	52
<b>Packaging<sup>2</sup>:</b>	Packaged in Box or Tube
<b>Rows:</b>	Double Row
<b>Head Type:</b>	Pin Head
<b>ECCN:</b>	EAR99
<b>HTSUS:</b>	8536.90.4040
<b>Product Lifecycle:</b>	Active

# 499-10-252-10-009000- SPECIFICATIONS

Environmental Specs		Materials	
Temperature Range <sup>3</sup> :	-55/+125° C	Loose Pin/Receptacle # (Material):	5011 (Brass Alloy)
RoHS <sup>4</sup> :	Yes	Shell Plating:	10 $\mu$ " Gold over 100 $\mu$ " Nickel
Moisture Sensitivity Level (MSL):	1 (Unlimited)	Inner Plating:	
REACH Status:	REACH Unaffected	Insulator Material:	High Temp Thermoplastic
Mechanical Specs		Technical Specs	
Mounting Hole:	.028" (0,711mm)	Pitch:	.100" (2,540mm)
Electrical Specs			
Current Rating <sup>5</sup> :	Application Specific	Rated Voltage:	100 VRMS/150 VDC
Insulation Resistance:	10,000 M $\Omega$ min.	Dielectric Withstanding Voltage:	1,000 VRMS min.

## NOTES:

### 1. Standard Tolerances

Assembly tolerance:  $+\/-0.010"$  (.25mm)

Connector Length "L"

Connector Length "L"	Tolerance
$L \leq 2"$ ( $L \leq 50.8$ mm)	$+\/- .005"$ ( $+\/- .127$ mm)
$2 < L \leq 3"$ ( $50.8 < L \leq 76.2$ mm)	$+\ .007 / - .006"$ ( $+\ .178 / - .152$ mm)
$3 < L \leq 4"$ ( $76.2 < L \leq 101.6$ mm)	$+\ .009 / - .007"$ ( $+\ .229 / - .178$ mm)
$4 < L \leq 5"$ ( $101.6 < L \leq 127$ mm)	$+\ .011 / - .008"$ ( $+\ .279 / - .203$ mm)
$5 < L \leq 6.4"$ ( $127 < L \leq 162.56$ mm)	$+\ .013 / - .009"$ ( $+\ .330 / - .229$ mm)

Insulator width:  $+\/-0.005$  (.13mm)

Insulator height:  $+\/-0.005$  (.13mm)

Co-planarity of SMT connectors:  $.005"$  (.13mm) up to  $1"$  (25.4mm) in connector length

Insulator Flatness:  $.005"$  (.13mm) up to  $1"$  (25.4mm) in connector length

Pin Length:  $+\/-0.005$  (.13mm)

Pin Diameter:  $+\/-0.002$  (.051mm)

Pin Angle:  $+\/-2^\circ$

- Not all part numbers in the series may be packaged in tubes. Some specific part numbers may be packaged in a box.
- Per IEC 60512-11-(4,9,10,12)
- Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).
- Current rating is typically a measured function of the female socket/connector. The amount of current a solid, male, brass pin can tolerate is a direct relation of the heat displaced based on current and the ability of neighboring components to handle displaced heat.

## ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

## RELATED LINKS AND DOCUMENTS

Engineering Notebook: (<https://www.mill-max.com/engineering-notebooks/machined-pin-pcb-connectors-interconnects>)

Environmental Compliance: (<https://www.mill-max.com/rohs>)