



# Microwave Coaxial Connectors





## Coaxial Cable Connectors

MM4829-2702





Dimensions

MM5829-2700



Dimensions

MM9329-2700



Dimensions




Part Number	Rated Voltage (Vrms)	Frequency Rating (GHz)	Temperature Range	VSWR
MM4829-2702	250	to 6.0	-40 to +85°C	1.3 max. (DC to 3GHz)
MM5829-2700	30	to 12	-40 to +85°C	1.3 max. (DC to 3GHz)
MM9329-2700	250	to 6.0	-40 to +90°C	1.2 max. (DC to 3GHz)
MXHP32	250	to 6.0	-40 to +85°C	1.3 max.(DC to 3GHz)
MXJA01	30	to 12	-40 to +85°C	1.3 max.(DC to 3GHz)
MXTK92	250	to 6.0	-40 to +90°C	1.2 max.(DC to 3GHz)

Impedance: 50ohm


# Microwave Coaxial Connectors




## Coaxial Connectors with Switch




Measurement Probe for MM8030-2610  
 (P/N: MM126310)




Measurement Probe for MM8030-2610  
 (P/N: MXHQ87WA3000)



Measurement Probe for MM8130-2600/MM8430-2610  
 (P/N: MM126036)




Measurement Probe for MM8130-2600/MM8430-2610  
 (P/N: MXHS83QE3000)



Continued from the preceding page.

**Measurement Probe for MM8130-2600/MM8430-2610  
 (P/N: MXHS83QH3000)**



(in mm)

Part Number	Rated Voltage (Vrms)	Frequency Rating (GHz)	Temperature Range	VSWR (1)
<b>MM8030-2610</b>	250	to 11	-40 to +85°C	1.2 max. (DC to 3GHz)
<b>MM8130-2600</b>	250	to 6	-40 to +85°C	1.2 max. (DC to 3GHz)
<b>MM8430-2610</b>	250	to 6	-40 to +85°C	1.2 max.(DC to 3GHz)

Impedance: 50ohm