



**NIC COMPONENTS CORP.**

70 Maxess Road • Melville, New York 11747  
(631) 396-7500 • Fax (631) 396-7575


03132008

### INDIVIDUAL SPECIFICATION


**NIC P/N: NRSN06I2J220TRF**

0603 x 2 ELEMENT SURFACE MOUNT RESISTOR NETWORK

<b>Specifications:</b>	
Resistance Value:	22 ohms
Resistance Tolerance:	± 5% (J)
Operating Temperature Range:	-55°C ~ +125°C
Temperature Coefficient:	± 200ppm
Power Rating:	1/16 (0.0625) Watts per resistor (derated above 70°C)
Working Voltage Rating:	1.17Vdc max. @ +70°C
Overload Voltage Rating:	2.34Vdc max. for 5 seconds @ +70°C
<b>Dimensions (mm):</b>	
Length (L):	1.6 ± 0.20
Width (W):	1.6 ± 0.20
Height (H):	0.6 ± 0.10
Termination Width (a):	0.6 ± 0.10
Termination Width (b):	0.3 ± 0.15



**Power Derating Curve:** For operation above 70°C, power rating must be derated according to the following chart:



ISO 9002 REGISTERED