



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'HSTT38-Q45'

Your search criteria matched only one product, shown below

HSTT38-Q45



Flexible Polyolefin DRY-SHRINK™ Heat Shrink

- General purpose heat shrink tubing for dry lo
- Applications include insulating, protecting, ha
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 275°F (-55°C t
- Flammability Rating: Flame Retardant EXCE
- Voltage: 600V
- UL Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 1 (Colors

▪ Part Number	HSTT38-Q45
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Thin Wall Polyolefin Heat Shrink
▪ Material	Polyolefin cross-linked
▪ Color	Yellow/Green
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/5 Class 1
▪ UL Recognized	E122770
▪ CE Compliant	No
▪ Flammability Rating	Flame Retardant
▪ Length Per Reel (ft.)	25
▪ Length Per Reel (m)	7.6
▪ Max. Recovered I.D. (In.)	0.187
▪ Max. Recovered I.D. (mm)	4.8
▪ Min. Expanded I.D. (In.)	0.375
▪ Min. Expanded I.D. (mm)	9.5
▪ Nominal Diameter / Size	0.375
▪ Nominal Recovered Wall Thickness (In.)	0.025
▪ Nominal Recovered Wall Thickness (mm)	0.6
▪ Pricing Description	Heat Shrink Thin, .38"(9.5mm) Dia, Yellow/C
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F – 275°F (-55°C – 135°C)
▪ Min. Order UOM	RL
▪ Min. Order Qty.	1

▪ BOM Qty. (# of Pkgs.)

▪ Add to Favorite Product List

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Proc

[Home](#) | [Industries](#) | [Solutions](#) | [Products](#) | [Partners](#) | [Support](#) | [Contact Us](#) | [Site Map](#) |
Copyright © 1995-2010, PANDUIT CORP. All rights reserved. | [Legal Information](#) | [Pri](#)