


LEDINTA0024V28FO

| Brand Name | XITANIUM |
|-----------------|--------------|
| Description | 67W 24V 2.8A |
| Input Voltage | 120~277 |
| Input Frequency | 50/60Hz |
| RoHS | Yes |
| Approbations | UL, CSA |
| Status | Active |

Electrical Specifications

| Output Power (W) | Output Voltage (V) | Output Current (A) | Tcase Max | Input Current at I20V (A) | Max. Input Power (W) | Inrush Current (A _{pk} /µs) | Max. THD (%) | Min. Power Factor | Surge Protection (KV) | Weight (Lbs) | Envir. Protection Rating |
|------------------------|--------------------------|--------------------------|-----------|------------------------------------|-------------------------------|--|--------------------|-------------------------|-----------------------------|-----------------|--------------------------------|
| 67 | 24 | 0.10~2.8 | 90°C | 0.65 | 78 | 100/200 | 20 | 0.99 | 2.5 | I.4/635 | UL Dry & Damp |




Input and output use lead-wires. Lead-wires are 18AWG 105C/600V solid copper

Standard Lead Length

| | in. | cm. |
|--------|-----|-----|
| Black | 9 | 22 |
| White | 9 | 22 |
| Blue | 26 | 66 |
| Red | 26 | 66 |
| Gray | | |
| Violet | | |

Maximum Wiring Distance (at full load)

| U | · · · |
|-----------------|-----------------|
| Wire Size (AWG) | Distance (feet) |
| 26 | 2 |
| 24 | 3 |
| 22 | 5 |
| 20 | 9 |
| 18 | 14 |
| 16 | 21 |
| 14 | 34 |
| 12 | 53 |
| 10 | 89 |





UL Class 2 E220165 7310 S-000

3426-32

Revised 05/16/2012

PHILIPS LIGHTING ELECTRONICS N.A.

10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018 Tel: 800-322-2086 · Fax: 888-423-1882 · www.philips.com/advance Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886

PHILIPS ADVANCE

LEDINTA0024V28FO

| Brand Name | XITANIUM |
|-----------------|--------------|
| Description | 67W 24V 2.8A |
| Input Voltage | 120~277 |
| Input Frequency | 50/60Hz |
| RoHS | Yes |
| Approbations | UL, CSA |
| Status | Active |

Installation & Application Notes:

Section I – Physical Characteristics

- 1.1 LED Driver shall be installed inside an electrical enclosure
- 1.2 Wiring inside electrical enclosure shall comply with 600V/105°C rating or higher.

Section II – Performance

- 2.1 LED Driver is UL Class 2 power unit as per UL1310. It is also listed in the UL Sign Accessory Manual (UL SAM).
- 2.2 LED Driver has Class A sound rating.
- 2.3 LED Driver has a minimum operating ambient temperature of -40°C.
- 2.4 LED Driver has a 400 maximum switching cycle between cycling temperature of -40°C to -20°C.
- 2.5 LED Driver has a life expectancy of 50,000 hours at Tcase of $\leq 80^{\circ}$ C.
- 2.6 LED Driver has a life expectancy of 100,000 hours at Tcase of \leq 70°C.
- 2.7 LED Driver has a typical self rise of 30°C at maximum load in open air without heat sink.
- 2.8 LED Driver is certified by UL for use in a dry or damp location (Outdoor Type I).
- 2.9 LED Driver tolerates sustained open circuit and short circuit output conditions without damage.
- 2.10 LED Driver maximum allowable case temperature is 90°C see product label for measurement location.
- 2.11 LED Driver reduces output power to LEDs if maximum allowable case temperature is exceeded.
- 2.12 LED Driver has a failure rate of $\leq 0.01\%$ per 1,000 hours.
- 2.13 LED Driver complies with FCC rules and regulations, as per Title 47 CFR Part 15 Non-Consumer (Class A).

Section III – UL Conditions of Acceptability (File E220165)

- When installed in the end product, consideration shall be given to the following:
- 3.1 These LED Drivers have been evaluated to comply with Class 2 output criteria.
- 3.2 These Led Drivers are only suitable for use in Dry and Damp locations.
- 3.3 These products are rated as follows:

| | Input, 60 Hz. | | | OUTPUT V and Amperes DC |
|------------------|---------------|-----------|---------|----------------------------|
| Model | Volt/V | Amp/A | Power/W | |
| LEDINTA0024V28FO | 120-277 | 0.66-0.30 | 67 | 24V and 2.9A(###) |

(####) - For connection to LED array consisting of 67W maximum

- 3.4 In the end product, power supply spacing to to other heat producing components shall be minimum 4 inches spacing to sidewalls, and minimum 2 inches spacing to top of enclosure and mounted not closer than 1 in. end to end or 4in. side to side from adjacent LED power supplies.
- 3.5 The units were submitted and tested for a maximum manufacturer's recommended Tc point described in the table below. If adjacent LED power supplies are spaced closer then 1 in. end to end or 4 in. side to side a temperature test shall be conducted in the end use product.

| Model No. | | Max. Case @ | Ambient, °C |
|------------------|-------------------|-------------|---------------------|
| | Input Voltage, Hz | Tc, °C | (Reference only)(*) |
| LEDINTA0024V28FO | 120-277,60 | 90 | 56.6/59 |

Revised 05/16/2012

PHILIPS LIGHTING ELECTRONICS N.A.

PHILIPS ADVANCE

LEDINTA0024V28FO

| Brand Name | XITANIUM |
|-----------------|--------------|
| Description | 67W 24V 2.8A |
| Input Voltage | 120~277 |
| Input Frequency | 50/60Hz |
| RoHS | Yes |
| Approbations | UL, CSA |
| Status | Active |

(*) - 120V/ 277V Revision History:

| Rev No. | Date | Description | Approval | Remarks |
|---------|------------|--|----------|---------|
| 1.1 | 01/16/2012 | * Add Envir. Protection Rating | N.T. | |
| 1.3 | 04/06/2012 | *Add Installation & Application Notes: | N.T. | |
| | | Section II – 2.4: Max Switching Cycles | | |
| 1.4 | 05/16/2012 | *Add Approbations: UL, CSA | N.T. | |
| | | | | |

Revised 05/16/2012

PHILIPS LIGHTING ELECTRONICS N.A.

10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018 Tel: 800-322-2086 · Fax: 888-423-1882 · www.philips.com/advance Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886