


## High cost-performance DIP8-pin type with reinforced insulation

## PhotoMOS Relays GU-E 2 Form A (AQW210EH)



### FEATURES

- 1. Reinforced insulation of 5,000 V**  
More than 0.4 mm internal insulation distance between inputs and outputs. Con-forms to EN41003, EN60950 (reinforced insulation).
- 2. Applicable for 2 Form A use as well as two independent 1 Form A use**
- 3. Controls low-level analog signals**  
PhotoMOS relays feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.
- 4. High sensitivity and high speed response**  
Can control max. 0.14 A load current with 5 mA input current. Fast operation speed of typ. 0.5 ms (AQW210EH).
- 5. Low-level off state leakage current of max. 1  $\mu$ A**

### TYPICAL APPLICATIONS

- Modem
- Telephone equipment
- Security equipment
- Sensing equipment

### TYPES

	I/O isolation voltage	Output rating*		Package	Part No.				Packing quantity	
					Through hole terminal	Surface-mount terminal		Tube	Tape and reel	
						Tape and reel packing style				
		Load voltage	Load current		Tube packing style	Picked from the 1/2/3/4-pin side	Picked from the 5/6/7/8-pin side			
AC/DC dual use	Reinforced 5,000 V	60 V	500 mA	DIP8-pin	AQW212EH	AQW212EHA	AQW212EHAX	AQW212EHAZ	1 tube contains: 40 pcs. 1 batch contains: 400 pcs.	1,000 pcs.
		350 V	120 mA		AQW210EH	AQW210EHA	AQW210EHAX	AQW210EHAZ		
		400 V	100 mA		AQW214EH	AQW214EHA	AQW214EHAX	AQW214EHAZ		
		600 V	40 mA		AQW216EH	AQW216EHA	AQW216EHAX	AQW216EHAZ		

\*Indicate the peak AC and DC values.  
Note: The surface mount terminal shape indicator "A" and the packing style indicator "X" or "Z" are not marked on the relay.

### RATING

#### 1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)


Item		Symbol	AQW212EH(A)	AQW210EH(A)	AQW214EH(A)	AQW216EH(A)	Remarks
Input	LED forward current	$I_F$	50mA				
	LED reverse voltage	$V_R$	5V				
	Peak forward current	$I_{FP}$	1A				f = 100 Hz, Duty factor = 0.1%
	Power dissipation	$P_{in}$	75mW				
Output	Load voltage (peak AC)	$V_L$	60 V	350 V	400 V	600 V	
	Continuous load current	$I_L$	0.5 A (0.6 A)	0.12 A (0.14 A)	0.1 A (0.13 A)	0.04 A (0.05 A)	Peak AC, DC ( ) : in case of using only 1 channel
	Peak load current	$I_{peak}$	1.5 A	0.36 A	0.3 A	0.15 A	100 ms (1 shot), $V_L = DC$
	Power dissipation	$P_{out}$	800mW				
Total power dissipation		$P_T$	850mW				
I/O isolation voltage		$V_{iso}$	5,000 V AC				
Temperature limits	Operating	$T_{opr}$	-40°C to +85°C -40°F to +185°F				Non-condensing at low temperatures
	Storage	$T_{stg}$	-40°C to +100°C -40°F to +212°F				

# GU-E 2 Form A (AQW210EH)

## 2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item		Symbol	AQW212EH(A)	AQW210EH(A)	AQW214EH(A)	AQW216EH(A)	Condition
Input	LED operate current	Typical	1.2mA				$I_L = \text{Max.}$
		Maximum	3.0mA				
	LED turn off current	Minimum	0.4mA				$I_L = \text{Max.}$
		Typical	1.1mA				
LED dropout voltage	Typical	1.25 V (1.14 V at $I_F = 5\text{mA}$ )				$I_F = 50\text{mA}$	
	Maximum	1.5V					
Output	On resistance	Typical	0.83Ω	18Ω	26Ω	52Ω	$I_F = 5\text{mA}$ $I_L = \text{Max.}$ Within 1 s on time
		Maximum	2.5Ω	25Ω	35Ω	120Ω	
	Off state leakage current	Maximum	1μA				$I_F = 0\text{mA}$ $V_L = \text{Max.}$
Transfer characteristics	Turn on time*	Typical	1ms	0.5ms		$I_F = 5\text{mA}$ $I_L = \text{Max.}$	
		Maximum	4ms	2.0ms			
	Turn off time*	Typical	0.08ms			0.04ms	$I_F = 5\text{mA}$ $I_L = \text{Max.}$
		Maximum	1.0ms				
	I/O capacitance	Typical	0.8pF				$f = 1\text{MHz}$ $V_B = 0\text{V}$
		Maximum	1.5pF				
Initial I/O isolation resistance	Minimum	1,000MΩ				500V DC	

\*Turn on/Turn off time



## RECOMMENDED OPERATING CONDITIONS

Please obey the following conditions to ensure proper relay operation and resetting.

Item	Symbol	Recommended value	Unit
Input LED current	$I_F$	5 to 10	mA

### ■ Dimensions

### ■ Schematic and Wiring Diagrams

### ■ Cautions for Use

■ These products are not designed for automotive use.


If you are considering to use these products for automotive applications, please contact your local Panasonic Electric Works technical representative.

Please refer to our information on [PhotoMOS Relays for Automotive Applications](#).

## REFERENCE DATA


1-(1). Load current vs. ambient temperature characteristics

Allowable ambient temperature: -20°C to +85°C  
-4°F to +185°F




1-(2). Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40°C to +85°C  
-40°F to +185°F



1-(3). Load current vs. ambient temperature characteristics


Allowable ambient temperature: -40°C to +85°C  
-40°F to +185°F



# GU-E 2 Form A (AQW210EH)


## 2-(1). On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8;  
LED current: 5 mA; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 2-(2). On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8;  
LED current: 5 mA; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 2-(3). On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8;  
LED current: 5 mA; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 3. Turn on time vs. ambient temperature characteristics

Sample: All types  
LED current: 5 mA; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 4. Turn off time vs. ambient temperature characteristics

Sample: All types  
LED current: 5 mA; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 5. LED operate current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 6. LED turn off current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




## 7. LED dropout voltage vs. ambient temperature characteristics

Sample: All types; LED current: 5 to 50 mA




## 8-(1). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8;  
Ambient temperature: 25°C 77°F




## 8-(2). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 3 and 4;  
Ambient temperature: 25°C 77°F




## 8-(3). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 3 and 4;  
Ambient temperature: 25°C 77°F



## 9-(1). Off state leakage current vs. load voltage characteristics


Measured portion: between terminals 5 and 6, 7 and 8;  
Ambient temperature: 25°C 77°F



# GU-E 2 Form A (AQW210EH)


## 9-(2). Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8;  
Ambient temperature: 25°C 77°F




## 10. Turn on time vs. LED forward current characteristics

Sample: All types  
Measured portion: between terminals 5 and 6, 7 and 8;  
Load voltage: Max. (DC); Continuous load current:  
Max. (DC); Ambient temperature: 25°C 77°F




## 11. Turn off time vs. LED forward current characteristics

Sample: All types  
Measured portion: between terminals 5 and 6, 7 and 8;  
Load voltage: Max. (DC); Continuous load current:  
Max. (DC); Ambient temperature: 25°C 77°F



## 12-(1). Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8;  
Frequency: 1 MHz; Ambient temperature: 25°C 77°F



## 12-(2). Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8;  
Frequency: 1 MHz; Ambient temperature: 25°C 77°F

