
PHILIPS ADVANCE

LED120A0700C28FO

| Brand Name | XITANIUM |
|-----------------|------------|
| Driver Type | Electronic |
| Input Voltage | 120 |
| Input Frequency | 50/60Hz |
| RoHS | Yes |
| Approbations | UL, CSA |
| Status | Active |

Electrical Specifications

| Max. Output Power (W) | Output Voltage (V) | Output Current (A) | Operating Temp. Range (°F/°C) | Input Current at I20V (A) | Max. Input Power (W) | Inrush Current (A _{pk} /µs) | Max. THD (%) | Min. Power Factor | Surge Protection (KV) | Weight (Lbs) | Envir. Protection Rating |
|--------------------------------|--------------------------|--------------------------|--|------------------------------------|-------------------------------|--|--------------------|-------------------------|-----------------------------|-----------------|--------------------------------|
| 20 | 2.8~28.0 | 0.7 | -40°~140°F (-40~60°C) | 0.2 | 24 | - | 20 | 0.9 | 2.0 | 0.3/135 | UL Dry & Damp |



Input, Output and 0-10V Dimming use lead-wires. Lead-wires are 18AWG 105C/600V solid copper


Standard Lead Length

| | in. | cm. |
|--------|-----|-----|
| Black | 6 | 15 |
| White | 6 | 15 |
| Blue | 6 | 15 |
| Red | 6 | 15 |
| Gray | | |
| Violet | | |

Maximum Wiring Distance (at full load)

| Wire Size (AWG) | Distance |
|-----------------|----------|
| | (feet) |
| 26 | 8 |
| 24 | 13 |
| 22 | 21 |
| 20 | 34 |
| 18 | 54 |
| 16 | 85 |
| 14 | 137 |
| 12 | 210 |
| 10 | 357 |
| 05/16/2012 | |

Revised 05/16/2012







UL Class 2 E220165 7310_S-000 3426-32

PHILIPS LIGHTING ELECTRONICS N.A. 10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018 Tel: 800-322-2086 · Fax: 888-423-1882 · www.philips.com/advance Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886

PHILIPS ADVANCE

LED120A0700C28FO

| Brand Name | XITANIUM |
|-----------------|------------|
| Driver Type | Electronic |
| Input Voltage | 120 |
| Input Frequency | 50/60Hz |
| RoHS | Yes |
| Approbations | UL, CSA |
| Status | Active |

Installation & Application Notes:

Section I – Physical Characteristics

- 1.1 LED Driver shall be installed inside an electrical enclosure.
- 1.2 Wiring inside electrical enclosure shall comply with 600V/105°C rating or higher.

Section II – Performance

- 2.1 LED Driver is UL Class 2 power unit as per UL879 & UL1310. It is also listed in the UL Sign Accessory Manual.
- 2.2 LED Driver is certified by UL for use in a dry or damp location (Outdoor Type I).
- 2.3 LED Driver has Class A sound rating.
- 2.4 LED Driver tolerates sustained open circuit and short circuit output conditions without damage.
- 2.5 LED Driver maximum allowable case temperature is 90°C see product label for measurement location.
- 2.6 LED Driver complies with FCC rules and regulations, as per Title 47 CFR Part 15 Non-Consumer (Class A).

Section III – UL Conditions of Acceptability (File E220165)

When installed in the end product, consideration shall be given to the following:

- 3.1 This component has been judged on the basis of the required spacings in the Standard for Class 2 Power Units, UL 1310, Fourth Edition, which would cover the component itself if submitted for Listing.
- 3.2 The supply terminals and connectors are suitable for factory wiring only of solid or tinned stranded No. 18 AWG conductors.
- 3.3. The LED Drivers listed below are suitable for use in Dry and Damp locations: LED120A0012V10F, LED120A0350C28FO, LED120A0700C24FO and GEXNPS31-120.
- *3.4 The equipment was submitted and tested for a maximum manufacturer's recommended ambient (Tmra) of 25°C. except the Models LED 120A0350C28FO, LED 120A0700C24FO, LED 120A0012V10F, 913700534302, LED 120A0350C33F and GEXNPS31-120 were tested for a 69.1 deg. C ambient for a max. Tcase temperature of 90 deg. C.
- *3.4 This unit is provided with a Class **I30(B)** insulation system. A temperature test is required when the unit is installed within an electrical enclosure or raceway.
- 3.5 Leakage current measurements shall be performed when more than four LED drivers are used in the equipment or when the LED driver is used in combination with other equipment in the end-use product.
- 3.6 The unit is intended for installation inside an electrical enclosure.
- 3.7 The Models LED I 20A0350C28FO, LED I 20A0700C24FO, LED I 20A0012V10F and GEXNPS31-120 may be used within an electrical enclosure or raceway without temperature test provided they are mounted not closer than 1 in. end to end or 4 in. side to side from adjacent LED power supplies.

Revised 05/16/2012

PHILIPS LIGHTING ELECTRONICS N.A.

PHILIPS ADVANCE

LED120A0700C28FO

| Brand Name | XITANIUM |
|-----------------|------------|
| Driver Type | Electronic |
| Input Voltage | 120 |
| Input Frequency | 50/60Hz |
| RoHS | Yes |
| Approbations | UL, CSA |
| Status | Active |

Revision History:

| Rev No. | Date | Description | Approval | Remarks |
|---------|------------|--------------------------------|----------|---------|
| 1.1 | 01/16/2012 | * Add Envir. Protecting Rating | N.T. | |
| 1.2 | 03/02/2012 | *Modify Part #(Remove Dashes) | N.T. | |
| 1.3 | 05/16/2012 | *Add Approbations: UL, CSA | N.T. | |
| | | | | |

Revised 05/16/2012

PHILIPS LIGHTING ELECTRONICS N.A.

10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018 Tel: 800-322-2086 · Fax: 888-423-1882 · www.philips.com/advance Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886