PHILIPS ADVANCE

Electrical Specifications

LEDINTA0024V30FLO				
Brand Name	XITANIUM			
Description	72W 24V 3.0A			
Input Voltage	120~277			
Input Frequency	50/60Hz			
RoHS	Yes			
Approbations	UL, CSA, CE, ENEC			
Status	Active			

Output Power (W)	Output Voltage (V)	Output Current (A)	Tcase Max	Input Current (A)	Max. Input Power (W)	Inrush Current (A _{pk} /µs)	Max. THD (%)	Min. Power Factor	Surge Protection (KV)	Weight (Lbs)	Envir. Protection Rating
72	24	0.10~3.0	85°C	0.72@120V 0.32@277V	86	100/200	20	0.90	3.0	2.8/1270	UL Dry & Damp

Wiring Diagram INPUT OUTPUT RED (POSITIVE) LED DRIVER UNHITE (NEUTRAL) BLUE (NEGATIVE)

Input and output use lead-wires. Lead-wires are 18AWG 105C/600V solid copper

Standard Lead Length

٠.	odd Longin					
		in.	cm.			
	Black	9	22			
	White	9	22			
	Blue	26	66			
	Red	26	66			
	Gray					
	Violet					

Maximum Wiring Distance (at full load)

Wire Size (AWG)	Distance
	(feet)
26	3
24	5
22	9
20	14
18	23
16	36
14	58
12	88
10	150









UL Class 2 E220165 7310_S-000 3426-32

Revised 05/16/2012



LEDINTA0024V30FLO				
Brand Name	XITANIUM			
Description	72W 24V 3.0A			
Input Voltage	120~277			
Input Frequency	50/60Hz			
RoHS	Yes			
Approbations	UL, CSA, CE, ENEC			
Status	Active			

Installation & Application Notes:

Section I – Physical Characteristics

- 1.1 LED Driver shall be installed inside an electrical enclosure
- 1.2 Wiring inside electrical enclosure shall comply with 600V/105°C rating or higher.

Section II - Performance

- 2.1 LED Driver is UL Class 2 power unit as per UL1310. It is also listed in the UL Sign Accessory Manual (UL SAM).
- 2.2 LED Driver has Class A sound rating.
- 2.3 LED Driver has a minimum operating ambient temperature of -40°C.
- 2.4 LED Driver has a maximum life expectancy of 50,000 hours at Tcase of $\leq 75^{\circ}$ C.
- 2.5 LED Driver has a maximum life expectancy of 100,000 hours at Tcase of \leq 65°C.
- 2.6 LED Driver has a typical self rise of 25°C at maximum load in open air without heat sink.
- 2.7 LED Driver is certified by UL for use in a dry or damp location (Outdoor Type I).
- 2.8 LED Driver tolerates sustained open circuit and short circuit output conditions without damage.
- 2.9 LED Driver maximum allowable case temperature is 85°C see product label for measurement location.
- 2.10 LED Driver reduces output power to LEDs if maximum allowable case temperature is exceeded.
- 2.11 LED Driver complies with FCC rules and regulations, as per Title 47 CFR Part 15 Non-Consumer (Class A).

Section III – UL Conditions of Acceptability (File E220165)

When installed in the end product, consideration shall be given to the following:

- 3.1 These LED Drivers have been evaluated to comply with Class 2 output criteria.
- 3.2 These LED Drivers are only suitable for use in Dry and Damp locations.
- 3.3 These products are rated as follows:

	I	nput, 60 Hz.	OUTPUT V@Amperes DC	
Model	Volt/V	Amp/A	Power/W	
LEDINTA0024V41DLO	120-277	0.95-0.40	100	24V@4.1(*)
LEDINTA0024V41FLO	120-277	0.95-0.40	100	24V@4.1 (*)
LEDINTA0024V41FO	120-277	0.95-0.40	100	24V@4.1(*)
LEDINTA0024V30FLO	120-277	0.72-0.32	72	24@3.0 (**)
LEDINTA0024V30DLO	120-277	0.72-0.32	72	24@3.0 (**)
LEDINTA0024V20FLO	120-277	0.48-0.22	48	24@2.0 (***)
LEDINTA0024V20DLO	120-277	0.48-0.22	48	24@2.0 (***)
LEDINTA0024V32FO	120-277	0.75-0.35	77	24@3.2 (+)
LEDINTA0024V22FO	120-277	0.50-0.25	53	24@2.2 (++)

- (*) For connection to LED array consisting of 100 Watt maximum.
- (**) For connection to LED array consisting of 72 Watt maximum.
- (***) For connection to LED array consisting of 48 Watt maximum.
- (+) For connection to LED array consisting of 77 Watt maximum.
- (++) For connection to LED array consisting of 53 Watt maximum.

Revised 05/16/2012

PHILIPS LIGHTING N.A.



LEDINTA0024V30FLO				
Brand Name	XITANIUM			
Description	72W 24V 3.0A			
Input Voltage	120~277			
Input Frequency	50/60Hz			
RoHS	Yes			
Approbations	UL, CSA, CE, ENEC			
Status	Active			

- 3.4 In the end product, power supply spacing to other heat producing components shall be minimum 4 inches spacing to sidewalls, and minimum 2 inches spacing to top of enclosure and mounted not closer than 1 in. end to end or 4 in. side to side from adjacent LED power supplies.
- 3.5 The units were submitted and tested for a maximum manufacturer's recommended Tc point described in the table below. If adjacent LED power supplies are spaced close than 1 in. end to end or 4 in. side to side, a temperature test shall be conducted in the end use product.

Model No.	Input Voltage,	Max. Case @	Ambient, °C
	Hz	Tc, °C	(Reference only)*
LEDINTA0024V41DLO	120-277,60	85	61.5/63.2
LEDINTA0024V41FO	120-277,60	90	56.6/59
LEDINTA0024V41FLO	120-277,60	85	61.5/63.2
LEDINTA0024V30DLO	120-277,60	85	61.5/63.2
LEDINTA0024V30FLO	120-277,60	85	61.5/63.2
LEDINTA0024V20DLO	120-277,60	85	61.5/63.2
LEDINTA0024V20FLO	120-277,60	85	61.5/63.2
LEDINTA0024V32FO	120-277,60	90	56.6/59
LEDINTA0024V22FO	120-277,60	90	56.6/59

^{* - 120}V/ 277V

Revision History:

Rev No.	Date	Description	Approval	Remarks
1.1	01/16/2012	* Add Envir. Protection Rating	N.T.	
1.2	03/02/2012	*Modify Part #(Remove Dashes)	N.T.	
1.3	05/16/2012	*Add Approbations: UL, CSA, CE, ENEC	N.T.	