

## Specification Status: RELEASED

### Electrical Rating

**Voltage: 16V<sub>DC</sub> MAX**




### Insulating Material:


Cured, Flame Retardant Epoxy Polymer

### Lead Material:

18 AWG Tin Plated Copper  
(1.0 mm [0.040] nom. diameter)

### Part Marking:

 Manufacturer's Mark and Voltage  
 Part Identification  
 Lot Identification (can be on back)



**TABLE I. INSTALLATION ENVELOPE DIMENSIONS:**

	A		B		C		D		E		F	G	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	TYP	MIN	MAX
mm:	--	23.5	--	28.7	9.4	10.9	7.6	--	--	3.5	1.4	--	7.82
in*:	--	(0.925)	--	(1.13)	(0.37)	(0.43)	(0.30)	--	--	(0.14)	(0.06)	--	(0.308)

\*Rounded off approximation

**TABLE II. PERFORMANCE RATINGS:**

CURRENT RATINGS			TIME TO TRIP	INITIAL RESISTANCE		R <sub>1</sub> MAX 1 HR. POST TRIP RESISTANCE STANDARD TRIP	R <sub>A</sub> MAX	TRIPPED-STATE POWER DISSIPATION
HOLD AT R <sub>1</sub> MAX	AMPS AT 25°C		SECONDS AT 25°C, 70 A MAX	OHMS AT 25°C		OHMS AT 25°C	OHMS AT 25°C	WATTS AT 25°C TYP
	HOLD AT R <sub>A</sub> MAX	TRIP		MIN	MAX			
14.0	13.0	27.3	9.0	0.0022	0.0043	0.0064	0.0067	4.6

### Reference Documents:

PS400, PS300 (reference for R<sub>1</sub> MAX)

### Precedence:

This specification takes precedence over documents referenced herein.

### Effectivity:

Reference documents shall be the issue in effect on the date of invitation to bid.

### CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

## Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC  
Compliant

Directive 2000/53/EC  
Compliant





308 Constitution Drive  
Menlo Park, CA 94025-1164  
Phone: 800-227-4856  
www.circuitprotection.com

**PolySwitch®**  
**PTC Devices**  
**Overcurrent Protection Device**

**Raychem Circuit Protection Products**

**PRODUCT: AGRF1400**

DOCUMENT: SCD 25240  
PCN: C62521  
REV LETTER: C  
REV DATE: MAY 8, 2007  
PAGE NO.: 2 OF 2

**TABLE III. AUTOMOTIVE SPECIFIC STRESS TESTS AND TEST CONDITIONS:**

ELECTRICAL STRESS TESTS	TEST CONDITIONS (see note 2)
ESD Voltage Withstand (see note 1)	25kV
Short Circuit Fault Current Durability	25 cycles, 16V, 200A
Fault Current Durability	350 cycles, 16V/100A
End-of-life Mode Verification	1750 cycles, 16V/100A
Jump Start Endurance (see note 1)	3 cycles, 26V, 1 minute duration
Load Dump Endurance (see note 1)	10 cycles, 86.5V

Note 1: The PolySwitch devices are tested in series with a load resistance and the voltages specified in the test conditions are shared between the PolySwitch device and the load resistance as specified in PS400.

Note 2: Please refer to Appendix A of PS400 for the detailed test procedures