

Specification Status: RELEASED

Electrical Rating

Voltage: 30V MAX
Current: 100A MAX

Insulating Material:
None

Lead Material:
20 AWG Tin Plated Copper

Marking:
None




TABLE I. DIMENSIONS:

	A		B		C	D	E	
	MIN	MAX	MIN	MAX	TYPICAL	MIN	MIN	MAX
mm:	7.1	8.1	15.0	16.3	5.0	7.6	--	2.8
in*:	(0.28)	(0.32)	(0.59)	(0.64)	(0.2)	(0.3)	--	(0.11)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS:

I HOLD	CURRENT RATINGS				TIME TO TRIP	RESISTANCE		ONE-HOUR POST-TRIP RESISTANCE STANDARD TRIP	NOMINAL TRIPPED POWER DISSIPATION
	AMPS 20°C HOLD	AMPS AT 20°C HOLD	AMPS AT 20°C TRIP	AMPS AT 50°C HOLD		AMPS AT 50°C TRIP	SECONDS AT 20°C, 8A MAX		
2.5	2.5	4.9	2.0	3.7	5.0	0.031	0.044	0.080	1.75

Agency Recognitions
Reference Documents:
Precedence:
Effectivity:
CAUTION:

UL, CSA, TUV
PS300
This specification takes precedence over documents referenced herein.
Reference documents shall be the issue in effect on the date of invitation for bid.
Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

