### **Panasonic**

#### 2.6 mm×1.6 mm SMD Light Touch Switches

**EVPBB** Type:




#### Features

- External dimensions: 2.6 mm× 1.6 mm, Height 0.50 mm, 0.53 mm, 0.55 mm
- High operability Equipped with an actuator (push plate)
- IP67

#### ■ Recommended Applications

 Opearation switches for Smartphone, Wearable devices (Smartwatch, Headset, Hearing aid)

#### Explanation of Part Numbers



#### ■ Specifications

Туре		Snap action/Push-on type SPST						
	Rating	10 μA 2 V DC to 20 mA 15 V DC (Resistive load)						
Electrical	Contact Resistance	500 mΩ max.						
	Insulation Resistance	50 MΩ min. (at 100 V DC)						
	Dielectric Withstanding Voltage	250 V AC for 1 minute						
	Bouncing	10 ms max. (ON, OFF)						
Mechanical	Operating Force	0.7 N	1.0 N	1.6 N, 2.4 N				
	Travel	0.08 mm	0.08 mm	0.11 mm				
Endurance	Operating Life	200,000 cycles min.	cles min. 500,000 cycles min.					
ID07/*4)	IP6x (Dust resistance)	Dust : Talc (Type4) 8 h						
IP67(*1)	IPx7 (Water resistance)	Immersion depth : 1m 30min.						
Operating Tem	perature	−40 °C to +85 °C						
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)						
Minimum Quantity/Packing Unit		10,000 pcs. Embossed Taping (Reel Pack)						
Quantity/Carton		50,000 pcs.						

Note: Non washable

(\*1) IP67: Switch shall not be operated during test.

Water or dust ingress shall be limited enough to prevent deleterious effect to the switch function. However, IP67 shall be guaranteed under single product state,


then there is a possibility that IP67 performance become impaired depending on your mounting condition or usage.

So, please ask us in advance, if the switch is applied to important usage for water and dust resistant.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## **Panasonic**


#### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

# **Panasonic**


#### ■ Recommended Reflow Soldering Conditions



\*Reflow temperature may vary by location even in the same reflow condition. Please check the reflow temperature at terminals and at the top of a switch to make sure the both temperatures are withiin the specification. If even one of them is out of the specifications, please adjust.

#### Embossed Carrier Taping

Tape width=12.0 mm



Taping condition: Lack of products in the middle of taping should be one MAX, but total quantity specified in the specifications should be secured.

Peeling off strength of top tape: It should be within 0.2N to 1.0N at 165 degree in peeling off angle.

Joint of carrier tape: One joint per one reel may exist.

Unit: mm

Part No.	Height	Α	В	С	D	E	F	G	Н	I	J	K	t
EVPBB	0.50	12.0±0.3	1.75±0.10	5.5±0.1	8.0±0.1	4.0±0.1	2.0±0.1	1.5±0.3	1.95±0.20	3.3±0.2	0.7±0.2	(10.25)	0.3+0.15
	0.53												
	0.55												

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

# Guidelines and cautions for using the product technical information and the products displayed on this material

- The products described on this material were designed and manufactured for standard applications such as general electronics devices, office equipment, data and communications equipment, measuring instruments, household appliances and audio-video equipment. For special applications in which quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or cause threat of personal injury (such as for aircraft and aerospace equipment, traffic and transport equipment, combustion equipment, medical equipment, accident prevention and anti-theft devices, and safety equipment), please use only after your company has sufficiently tasted our products' suitability for that application.
- •When using our products in equipment that requires a high degree of reliability, regardless of the application, it is recommended that you use protection circuits and redundancy circuits for equipment safety and test for safety.
- ■The products and product specifications described on this material are subject to change for improvement without prior notice. Therefore, be sure to request and confirm in advance the most current specifications, which explain the specifications in detail, before the final stage of your design, purchasing or use for any application.
- ●The technical information on this material provides examples of the products' typical operations and application circuits. It is not intended to guarantee the non-infringement of or grant license for intellectual property rights of this company or any third party.
- Permission must be obtained from the Japanese government if products, products specifications and technical information on this material that are subject to the "Foreign Exchange and Foreign Trade Law" are to be exported or taken out of Japan.
- ●The information contained on this material may not be reprinted or reproduced whether wholly or in part, without the prior written permission of Panasonic Corporation.

# **Safety Precautions**

When using our products, no matter what sort of equipment they might be used for, be sure to confirm the applications and environmental conditions with our specifications in advance.

Please contact ......

## Panasonic Corporation

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan industrial.panasonic.com/ac/e/



©Panasonic Corporation 2018