



# PSE Technology Corporation

# SPECIFICATION FOR APPROVAL

## CUSTOMER

NOMINAL FREQUENCY

125.000000 MHz

## PRODUCT TYPE

## TYPE FN 7.0x5.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

SPEC. NO. ( P/N )

FNC500131

CUSTOMER P/N

ISSUE DATE

January 19, 2011

## VERSION

D

|                                                |          |            |
|------------------------------------------------|----------|------------|
| APPROVED                                       | PREPARED | QA         |
| Brenda                                         | Clair    | Isaiah     |
| APPROVED BY CUSTOMER :                         |          | AVL Status |
| Please return one copy with approval to PSE-TW |          |            |

# PSE Technology Corporation

No.2, Tzu-Chiang 5th Rd, Chung Li Industrial Park,  
Chung Li City, Taoyuan County, Taiwan (R.O.C.)

TEL: 886-3-451-8888

FAX: 886-3-461-3865

<http://www.saronix-ecera.com.tw>

\*Pb-free

\*RoHS Compliant

\*HF-Halogen Free

\*REACH Compliant

\*\*\* A company of  **PERICOM Semiconductor Corporation** \*\*\*

VER. D 19-Jan-11

# TYPE FN 7.0x5.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**FNC500131**

VER. D 19-Jan-11

## ELECTRICAL SPECIFICATIONS

**SRe Part Number : FNC500131**

| Item                            | Symbol                         | Specifications      | Units | Notes                             |
|---------------------------------|--------------------------------|---------------------|-------|-----------------------------------|
| Nominal Frequency               | Fo                             | 125.000000          | MHz   |                                   |
| Frequency Stability             | FT                             | ± 50                | ppm   | **See note                        |
| Operating Temperature Range     | TR                             | -40 to +85          | °C    |                                   |
| Supply Voltage                  | V <sub>DD</sub>                | +3.3 ± 10.0%        | V     |                                   |
| Logic Type                      | LT                             | LVC MOS             |       |                                   |
| Supply Current, Output Enabled  | I <sub>DD</sub> /OE            | 55                  | mA    | Max.                              |
| Supply Current, Output Disabled | I <sub>DD</sub> /OD            | 10                  | µA    | Max.                              |
| Duty Cycle (Symmetry)           | DC/SY                          | 45 / 55             | %     | Measured 50% of Waveform          |
| Rise / Fall Time                | T <sub>R</sub> /T <sub>F</sub> | 3                   | ns    | Max. measured 20/80% of Waveform  |
| Output Voltage "0" Level        | V <sub>OL</sub>                | 10% V <sub>DD</sub> | V     | Max.                              |
| Output Voltage "1" Level        | V <sub>OH</sub>                | 90% V <sub>DD</sub> | V     | Min.                              |
| Output Load                     | CL                             | 15                  | pF    | Max                               |
| Jitter, Phase                   | RMS(1-σ)                       | 1                   | ps    | Max, 12KHz ~ 20MHz Frequency Band |
| Jitter, Accumulated             | RMS(1-σ)                       | 3                   | ps    | Max, 20,000 Consecutive Periods   |
| Jitter, Peak to Peak            | Pk-Pk                          | 30                  | ps    | Max, 100,000 Random Periods       |
| Storage Temperature Range       |                                | -55°C to +125°C     | °C    |                                   |

※ This product doesn't include harmful substance that stipulated by SONY SS-00259 Level 1 and S-AT2-001 Level 1 standard. RoHS Compliant (Pb - Free).

**\*\*Stability includes all combinations of Operating Temperature, Load changes, rated Input (Supply) Voltage changes, Initial Calibration Tolerance (25°C), Aging (1 year at 25°C Average Effective Ambient Temperature), Shock and Vibration.**

### Output Enable / Disable Function


| Parameter                                                | Min.               | Typ. | Max.               | Units | Notes          |
|----------------------------------------------------------|--------------------|------|--------------------|-------|----------------|
| Input Voltage (Pin1), Output Enable                      | 0.7V <sub>DD</sub> |      |                    | V     | Or Open        |
| Input Voltage (Pin1), Output Disable (low power standby) |                    |      | 0.3V <sub>DD</sub> | V     | Output is Hi-Z |
| Internal Pullup Resistance                               | 30                 |      |                    | KΩ    |                |
| Output Disable Delay                                     |                    |      | 200                | ns    |                |
| Output Enable Delay                                      |                    |      | 2                  | ms    |                |

# TYPE FN 7.0x5.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**FNC500131**

VER. D 19-Jan-11

## TEST CIRCUIT



## OUTPUT WAVEFORM



### RELIABILITY SPECIFICATIONS

#### ENVIRONMENTAL:


- a) THERMAL SHOCK: MIL-STD-883, Method 1011, Condition A
- b) MOISTURE RESISTANCE: MIL-STD-883, Method 1004
- c) VIBRATION: MIL-STD-883, Method 2007, Condition A
- d) RESISTANCE TO SOLDERING HEAT: J-STD-020D Table 5-2 Pb-free devices (except 2 cycles max)
- e) HAZARDOUS SUBSTANCE: Pb - free and RoHS Compliant.

#### MECHANICAL:

- a) SHOCK: MIL-STD-883, Method 2002, Condition B
- b) SOLDERABILITY: JESD22-B102-D Method 2 (Preconditioning E)
- c) TERMINAL STRENGTH: MIL-STD-883, Method 2004, Test Condition D
- d) GROSS LEAK: MIL-STD-883, Method 1014, Condition C
- e) FINE LEAK: MIL-STD-883, Method 1014, Condition A2,  $R1=2 \times 10^{-8}$  atm cc/s
- f) SOLVENT RESISTANCE: MIL-STD-202, Method 215

### SUGGESTED IR REFLOW PROFILE

\*As per IPC-JEDEC J-STD-020D



Note:

|   | Stage        | Temperature | Time       |
|---|--------------|-------------|------------|
| A | Preheat      | 150~200°C   | 60~120 Sec |
| B | Primary Heat | 217°C       | 60~150 Sec |
| C | Peak         | 260°C       | 10 Sec     |


For soldering reflow profile and reliability test ratings go to: <http://www.pericom.com/pdf/sre/reflow.pdf>

# TYPE FN 7.0x5.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**FNC500131**

VER. D 19-Jan-11

## MARKING



## MECHANICAL DRAWINGS ( Scale:None. Dimensions are in mm.)




# TYPE FN 7.0x5.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**FNC500131**

VER. D 19-Jan-11

## TAPE&REEL



1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.

# TYPE FN 7.0x5.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**FNC500131**

VER. D 19-Jan-11

## PACKING

