



REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	23/07/04	NJB
02	MAX CABLE DIA ADDED	24/09/04	NJB
03	PART No. UPDATED	28/09/04	NJB
04	APPLICATION VIEW & SECONDARY DIMS ADDED	04/10/04	NJB
05	ECN 04-229	10/12/04	NJB
06	ECN 07-221	06/12/07	NJB

NOTES:

- 1) STANDARD PACK QUANTITY: 1000.
- 2) ALL PRIMARY DIMENSIONS IN mm, ALL SECONDARY DIMENSIONS IN [INCHES].
- 3) MAX. CABLE DIAMETER = 4.5mm.
- 4) MAXIMUM SCREW SIZES: M3 x 0.6, No. 6 SCREW UNC, No.6 SCREW UNF.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT



METRIC GENERAL TOLERANCES ±0.25
 ARE PRIMARY UNLESS OTHERWISE STATED
 1 DECIMAL PLACE ±
 2 DECIMAL PLACES ±
 ANGULAR ±1°

IMPERIAL GENERAL TOLERANCES ±0.010
 ARE FOR REFERENCE UNLESS OTHERWISE
 1 DECIMAL PLACE ±
 2 DECIMAL PLACES ±
 ANGULAR ±1°

MATERIAL: NYLON 6/6 (RMS-48)		COLOUR: GREY	
DESCRIPTION: STRAIN RELIEF CABLE CLAMP		PART No: SRCC-1	
DRG No: 04-081	NPR REF:		SIZE A4
DRN NJB	DATE 23/07/04		CHKD OW
SCALE NTS	SHEET No 1 OF 1		