

**Specification Status: Released**

**Electrical Rating**


**Voltage: 32V<sub>DC</sub> MAX**  
**Current: 100A MAX**

Insulating Material:  
Cured, Flame Retardant Epoxy Polymer

Lead Material :  
24 AWG Tin Plated Copper Clad Steel

Marking:

- Manufacturer's Mark and Voltage
- ⊗ 32 — Part Identification
- EF0.7 — Lot Identification (can be on back)
- — Lot Identification (can be on back)



**TABLE I. DIMENSIONS:**

	A		B		C		D		E	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	--	6.9	--	10.8	4.3	5.8	7.6	--	--	3.0
in*:	--	(0.27)	--	(0.43)	(0.17)	(0.23)	(0.30)	--	--	(0.12)

\*Rounded off approximation

**TABLE II. PERFORMANCE RATINGS :**

I HOLD RATED CURRENT	CURRENT RATINGS		INITIAL RESISTANCE VALUES		TIME TO TRIP	R <sub>aMAX</sub>	TRIPPED-STATE POWER DISSIPATION
AMPS AT 25°C HOLD	AMPS AT 25°C HOLD	AMPS AT 25°C TRIP	OHMS AT 25°C MIN	OHMS AT 25°C MAX	SECONDS AT 25°C, 3.5 A MAX	OHMS AT 25°C MAX	WATTS AT 25°C TYP
0.70	0.70	1.40	0.23	0.54	3.2	0.8	1.4

Reference Documents:

PS400, PS300 (reference for R<sub>1</sub> MAX)

Precedence:

This specification takes precedence over documents referenced herein.

Effectivity:

Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

**Materials Information**

ROHS Compliant

ELV Compliant

Pb-Free





308 Constitution Drive  
Menlo Park, CA 94025-1164  
Phone: 800-227-4856  
[www.circuitprotection.com](http://www.circuitprotection.com)

**PolySwitch®**  
**PTC Devices**  
**Overcurrent Protection Device**

*Raychem Circuit Protection Products*

**PRODUCT: AHEF070**

DOCUMENT: SCD 26996  
PCN: RF1045  
REV LETTER: B  
REV DATE: JANUARY 22, 2009  
PAGE NO.: 2 OF 2

**TABLE III. AUTOMOTIVE SPECIFIC STRESS TESTS AND TEST CONDITIONS:**

ELECTRICAL STRESS TESTS	TEST CONDITIONS (see note 2)
ESD Voltage Withstand (see note 1)	25kV
Short Circuit Fault Current Durability	25 cycles, 32V, 200A
Fault Current Durability	350 cycles, 32V/100A
End-of-life Mode Verification	1750 cycles, 32V/100A
Jump Start Endurance (see note 1)	3 cycles, 48V, 2 minute duration
Load Dump Endurance (see note 1)	10 cycles, 86.5V

Note 1: The PolySwitch devices are tested in series with a load resistance and the voltages specified in the test conditions are shared between the PolySwitch device and the load resistance as specified in PS400.

Note 2: Please refer to Appendix A of PS400 for the detailed test procedures