

ZLG SERIES
Load Life: 105°C 1000~5000hours. Ultra Low impedance.
◆FEATURES

- Extremely reduced impedance at high frequency range than ZL series.
- Load Life : 105°C 1000~5000hours.
- RoHS compliance.


◆SPECIFICATIONS

Items	Characteristics																					
Category Temperature Range	-40~+105°C																					
Rated Voltage Range	6.3~35V.DC																					
Capacitance Tolerance	±20% (20°C, 120Hz)																					
Leakage Current(MAX)	I=0.03CV or 3 μA whichever is greater. (After 2 minutes) I=Leakage Current(μA) C=Rated Capacitance(μF) V=Rated Voltage(V)																					
(tanδ) Dissipation Factor(MAX)	<table border="1"> <tr> <td>Rated Voltage (V)</td> <td>6.3</td> <td>10</td> <td>16</td> <td>25</td> <td>35</td> <td>(20°C, 120Hz)</td> </tr> <tr> <td>tan δ</td> <td>0.22</td> <td>0.19</td> <td>0.16</td> <td>0.14</td> <td>0.12</td> <td></td> </tr> </table> <p>When nominal capacitance is over 1000 μF, tanδ shall be added 0.02 to the listed value with increase of every 1000 μF.</p>	Rated Voltage (V)	6.3	10	16	25	35	(20°C, 120Hz)	tan δ	0.22	0.19	0.16	0.14	0.12								
Rated Voltage (V)	6.3	10	16	25	35	(20°C, 120Hz)																
tan δ	0.22	0.19	0.16	0.14	0.12																	
Endurance	<p>After life test with rated ripple current at conditions stated in the table below, the capacitors shall meet the following requirements.</p> <table border="1"> <tr> <td>Capacitance Change</td> <td>Within ±25% of the initial value.</td> </tr> <tr> <td>Dissipation Factor</td> <td>Not more than 200% of the specified value.</td> </tr> <tr> <td>Leakage Current</td> <td>Not more than the specified value.</td> </tr> </table> <table border="1"> <tr> <td>Case Size</td> <td>Life Time(hrs)</td> </tr> <tr> <td>L = 7</td> <td>1000</td> </tr> <tr> <td rowspan="4">L ≧ 11</td> <td>φD ≦ 6.3</td> <td>2000</td> </tr> <tr> <td>φD = 8</td> <td>3000</td> </tr> <tr> <td>φD = 10</td> <td>4000</td> </tr> <tr> <td>φD ≧ 12.5</td> <td>5000</td> </tr> </table>	Capacitance Change	Within ±25% of the initial value.	Dissipation Factor	Not more than 200% of the specified value.	Leakage Current	Not more than the specified value.	Case Size	Life Time(hrs)	L = 7	1000	L ≧ 11	φD ≦ 6.3	2000	φD = 8	3000	φD = 10	4000	φD ≧ 12.5	5000		
Capacitance Change	Within ±25% of the initial value.																					
Dissipation Factor	Not more than 200% of the specified value.																					
Leakage Current	Not more than the specified value.																					
Case Size	Life Time(hrs)																					
L = 7	1000																					
L ≧ 11	φD ≦ 6.3	2000																				
	φD = 8	3000																				
	φD = 10	4000																				
	φD ≧ 12.5	5000																				
Low Temperature Stability Impedance Ratio(MAX)	<table border="1"> <tr> <td>Rated Voltage (V)</td> <td>6.3</td> <td>10</td> <td>16</td> <td>25</td> <td>35</td> <td>(120Hz)</td> </tr> <tr> <td>Z(-25°C)/Z(20°C)</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td></td> </tr> <tr> <td>Z(-40°C)/Z(20°C)</td> <td>12</td> <td>12</td> <td>10</td> <td>8</td> <td>6</td> <td></td> </tr> </table>	Rated Voltage (V)	6.3	10	16	25	35	(120Hz)	Z(-25°C)/Z(20°C)	2	2	2	2	2		Z(-40°C)/Z(20°C)	12	12	10	8	6	
Rated Voltage (V)	6.3	10	16	25	35	(120Hz)																
Z(-25°C)/Z(20°C)	2	2	2	2	2																	
Z(-40°C)/Z(20°C)	12	12	10	8	6																	


◆MULTIPLIER FOR RIPPLE CURRENT

Frequency coefficient

Frequency (Hz)		120	1k	10k	100k ≤
Coefficient	4.7~10 μF	0.24	0.53	0.80	1.00
	22~33 μF	0.42	0.70	0.90	1.00
	47~270 μF	0.50	0.73	0.92	1.00
	330~680 μF	0.55	0.77	0.94	1.00
	820~1500 μF	0.60	0.80	0.96	1.00
	2200~3900 μF	0.70	0.85	0.98	1.00

◆DIMENSIONS

(mm)


◆PART NUMBER

□□□	ZLG	□□□□□	□	□□□	□□	D×L
Rated Voltage	Series	Rated Capacitance	Capacitance Tolerance	Option	Lead Forming	Case Size

◆ STANDARD SIZE

Rated Voltage (V·DC)	Rated capacitance (μF)	Size φ D×L(mm)	Rated ripple current (mA r.m.s./105°C, 100kHz)	Impedance (ΩMAX)		Rated Voltage (V·DC)	Rated capacitance (μF)	Size φ D×L(mm)	Rated ripple current (mA r.m.s./105°C, 100kHz)	Impedance (ΩMAX)	
				20°C, 100kHz	-10°C, 100kHz					20°C, 100kHz	-10°C, 100kHz
6.3 (0J)	33	4×7	230	0.48	1.6	25 (1E)	10	4×7	230	0.52	1.7
	47	5×7	350	0.26	0.86		22	5×7	350	0.27	0.89
	100	6.3×7	480	0.15	0.5		33	6.3×7	480	0.16	0.53
	150	5×11	405	0.15	0.5		47	6.3×7	480	0.15	0.5
	330	6.3×11	760	0.065	0.19		47	5×11	405	0.15	0.5
	560	8×11.5	1000	0.036	0.11		100	6.3×11	760	0.065	0.19
	820	8×16	1250	0.028	0.083		220	8×11.5	1000	0.036	0.11
	1000	10×12.5	1430	0.027	0.070		330	8×16	1250	0.028	0.083
	1200	8×20	1600	0.020	0.056		330	10×12.5	1430	0.027	0.070
	1200	10×16	1820	0.020	0.056		470	8×20	1600	0.020	0.056
	1500	10×20	2180	0.014	0.033		470	10×16	1820	0.020	0.056
	1500	12.5×16	2200	0.018	0.033		680	10×20	2180	0.014	0.033
	2200	10×23	2360	0.013	0.030		680	12.5×16	2200	0.018	0.033
	3300	12.5×20	2480	0.013	0.030		820	10×23	2360	0.013	0.030
3900	12.5×25	2900	0.012	0.024	1000	12.5×20	2480	0.013	0.030		
10 (1A)	22	4×7	230	0.49	1.6	35 (1V)	4.7	4×7	230	0.64	2.1
	33	5×7	350	0.26	0.86		10	5×7	350	0.33	1.1
	47	5×7	350	0.26	0.86		22	6.3×7	480	0.17	0.56
	100	6.3×7	480	0.15	0.5		33	6.3×7	480	0.16	0.53
	100	5×11	405	0.15	0.5		33	5×11	405	0.15	0.5
	220	6.3×11	760	0.065	0.19		56	6.3×11	760	0.065	0.19
	470	8×11.5	1000	0.036	0.11		150	8×11.5	1000	0.036	0.11
	680	8×16	1250	0.028	0.083		220	8×16	1250	0.028	0.083
	680	10×12.5	1430	0.027	0.070		220	10×12.5	1430	0.027	0.070
	1000	8×20	1600	0.020	0.056		270	8×20	1600	0.020	0.056
	1000	10×16	1820	0.020	0.056		330	10×16	1820	0.020	0.056
	1200	10×20	2180	0.014	0.033		470	10×20	2180	0.014	0.033
	1200	12.5×16	2200	0.018	0.033		470	12.5×16	2200	0.018	0.033
	1500	10×23	2360	0.013	0.030		560	10×23	2360	0.013	0.030
2200	12.5×20	2480	0.013	0.030	680	12.5×20	2480	0.013	0.030		
3300	12.5×25	2900	0.012	0.024	1000	12.5×25	2900	0.012	0.024		
16 (1C)	22	5×7	350	0.27	0.89						
	33	5×7	350	0.26	0.86						
	47	6.3×7	480	0.15	0.5						
	56	5×11	405	0.15	0.5						
	120	6.3×11	760	0.065	0.19						
	330	8×11.5	1000	0.036	0.11						
	470	8×16	1250	0.028	0.083						
	470	10×12.5	1430	0.027	0.070						
	680	8×20	1600	0.020	0.056						
	680	10×16	1820	0.020	0.056						
	1000	10×20	2180	0.014	0.033						
	1000	12.5×16	2200	0.018	0.033						
	1200	10×23	2360	0.013	0.030						
	1500	12.5×20	2480	0.013	0.030						
2200	12.5×25	2900	0.012	0.024							