

CHARACTERISTICS

- Weight: 0,9 Kg / 1,99 Lb
- Housing in Aluminium
- Impeller in plastic UL 94 V-0
- L-10 life expectancy at 40°C: 80.000 hours
- Operating temperature range: -10 / +55 °C
- Storage temperature: -40 / +70°C
- Connection: Terminals
- GAM T1 listed
- Electrical protection:
 - VE-VP : impedance protected
 - VK : thermally protected



OPTIONS

- Speed sensor
- Other IP levels
- Flying leads connection
- Salt spray protection
- Shocks and vibrations protection
- Marine application
- Wide temperature range
- Other voltages
- Three phases

Part Number	Voltage V	Frequency Hz	Nb Phases	Airflow		Pressure		Nominal speed RPM	Noise level LP dBA	Nominal current mA	Starting current mA	power W	Capacitor µF
				l/s	CFM	mm H. o	inch H. o						
148VE0282030	115	50	1	49,0	103,88	4,5	0,18	1400	36	100	140	11	1
82	115	60	1	58,0	122,96	6	0,24	1650	39	90	140	11	1
81	220	50	1	49,0	103,88	4,5	0,18	1400	36	60	80	13	0,32
81	220	60	1	58,0	122,96	6	0,24	1650	39	60	80	14	0,32
148VP0282030	115	50	1	81,0	171,72	7,3	0,29	2350	50	120	170	14	2,2
82	115	60	1	70,0	148,40	5,6	0,22	2100	45,5	160	180	18	2,2
81	220	50	1	82,0	173,84	8,3	0,33	2400	49	70	100	16	0,69
81	220	60	1	70,0	148,40	5,4	0,21	2000	44	100	105	22	0,69
148VK0282030	115	50	1	100,0	212,00	18,7	0,74	2850	54	300	610	32	2,7
82	115	60	1	119,0	252,28	24	0,94	3300	57	270	590	32	2,7
81	220	50	1	100,0	212,00	18	0,71	2800	53	200	390	35	2,2
81	220	60	1	117,0	248,04	21	0,83	3200	57	170	370	33	2,2

