

# GROMMETS & BUSHINGS, LED SPACERS AND INSULATORS

G


| Part No.     | "L"<br>± 0.25<br>mm | "A"<br>± 0.25<br>mm | "B"<br>± 0.25<br>mm | "C"<br>± 0.10<br>mm | "D"<br>± 0.10<br>mm |
|--------------|---------------------|---------------------|---------------------|---------------------|---------------------|
| MNI-HT-4-2   | 0.8                 | 7.1                 | 1.2                 | 3.7                 | 3.0                 |
| MNI-HT-4-8   | 3.2                 |                     |                     | 3.8                 | 2.8                 |
| MNI-HT-4-12  | 4.7                 |                     | 1.1                 |                     |                     |
| MNI-HT-4-220 | 0.8                 | 5.5                 | 1.0                 | 3.4                 | 2.9                 |
| MNI-HT-6-2   | 0.8                 | 7.9                 | 1.2                 | 4.8                 | 3.7                 |
| MNI-HT-10-6  | 2.4                 | 10.1                | 1.6                 | 6.6                 | 5.1                 |



Features: • Ideal for high temperature applications.

## MNI-HT

MOULDED NYLON INSULATOR,  
HIGH TEMPERATURE



Material: 40% glass filled  
Polyphenylene-Sulfide - black;  
UL 94 V-0, RMS-50  
Std. Pk.: 1.000 pcs.

Note:

|        |      |      |
|--------|------|------|
| MNI-HT | 4    | 1    |
| Part   | Size | Type |