

Digital transistors (built-in resistor)


DTC343TK / DTC343TS

●Features

In addition to the features of regular digital transistors,

- 1) Low $V_{CE(sat)}$ makes these transistors ideal for muting circuits. (Typ. 0.04V at $I_C/I_B=50/2.5mA$)
- 2) They can be used at high current. ($I_{CMax.}=600mA$)

●Circuit schematic



●Absolute maximum ratings (Ta=25°C)

Parameter		Symbol	Limits	Unit
Collector-base voltage		V_{CBO}	30	V
Collector-emitter voltage		V_{CEO}	15	V
Emitter-base voltage		V_{EBO}	5	V
Collector current		I_C	600	mA
Collector power dissipation	DTC343TK	P_C	200	mW
	DTC343TS		300	
Junction temperature		T_j	150	°C
Storage temperature		T_{stg}	-55 to +150	°C

●Package, marking, and packaging specifications

Part No.	DTC343TK	DTC343TS
Package	SMT3	SPT
Marking	H03	—
Packaging code	T146	TP
Basic ordering unit (pieces)	3000	5000

●External characteristics (Ta=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Collector-base breakdown voltage	BV_{CBO}	30	—	—	V	$I_C=50\mu A$
Collector-emitter breakdown voltage	BV_{CEO}	15	—	—	V	$I_C=1mA$
Emitter-base breakdown voltage	BV_{EBO}	5	—	—	V	$I_E=50\mu A$
Collector cutoff current	I_{CBO}	—	—	0.5	μA	$V_{CB}=20V$
Emitter cutoff current	I_{EBO}	—	—	0.5	μA	$V_{EB}=4V$
Collector-emitter saturation voltage	$V_{CE(sat)}$	—	40	80	mV	$I_C=50mA, I_B=2.5mA$
DC current transfer ratio	h_{FE}	100	250	600	—	$I_C=50mA, V_{CE}=5V$
Input resistance	R_1	3.29	4.7	6.11	k Ω	—
Transition frequency	f_T	—	200	—	MHz	$V_{CE}=10V, I_E=-50mA, f=100MHz$ *
Output on resistance	R_{on}	—	0.95	—	Ω	$V_I=7V, R=1k\Omega, f=1kHz$

*Transition frequency of the device.

Transistors

●Electrical characteristics curves






Fig.1 DC current gain vs. Collector current Fig.2 Collector-emitter saturation voltage vs. Collector current Fig.3 ON resistance vs. Input voltage

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.

This datasheet has been downloaded from:

www.DatasheetCatalog.com

Datasheets for electronic components.