

# SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL05A104KO5NNNC**
- Description : **CAP, 100nF, 16V, ±10%, X5R, 0402**

## A. Samsung Part Number

CL 05 A 104 K O 5 N N N C  
①    ②    ③    ④    ⑤    ⑥    ⑦    ⑧    ⑨    ⑩    ⑪

① Series	Samsung Multi-layer Ceramic Capacitor		
② Size	0402 (inch code)	L: 1.0 ± 0.05 mm	W: 0.5 ± 0.05 mm
③ Dielectric	X5R	⑧ Inner electrode	Ni
④ Capacitance	100 nF	Termination	Cu
⑤ Capacitance tolerance	±10 %	Plating	Sn 100% (Pb Free)
⑥ Rated Voltage	16 V	⑨ Product	Normal
⑦ Thickness	0.5 ± 0.05 mm	⑩ Special	Reserved for future use
		⑪ Packaging	Cardboard Type, 7" reel

## B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
Capacitance	Within specified tolerance	1kHz±10%      1.0±0.2Vrms
Tan δ (DF)	0.035 max.	
Insulation Resistance	10,000Mohm or 100Mohm·μF Whichever is Smaller	Rated Voltage      60~120 sec.
Appearance	No abnormal exterior appearance	Microscope (×10)
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
Temperature Characterisitcs	X5R (From -55℃ to 85℃, Capacitance change should be within ±15%)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g·F, for 10±1 sec.
Bending Strength	Capacitance change : within ±12.5%	Bending to the limit (1mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	1) Sn63Pb37 solder 235±5℃, 5±0.5sec. 2) SnAg3.0Cu0.5 solder 245±5℃, 3±0.3sec. (preheating : 80~120℃ for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within ±7.5% Tan δ, IR : initial spec.	Solder pot : 270±5℃, 10±1sec.

	<b>Performance</b>	<b>Test condition</b>
<b>Vibration Test</b>	Capacitance change : within $\pm 5\%$ Tan $\delta$ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
<b>Humidity</b>	Capacitance change : within $\pm 12.5\%$ Tan $\delta$ : 0.05 max IR : 1000Mohm or 50Mohm $\cdot \mu F$ Whichever is Smaller	40 $\pm 2$ $^{\circ}C$ , 90~95%RH, 500+12/-0hrs
<b>Moisture Resistance</b>	Capacitance change : within $\pm 12.5\%$ Tan $\delta$ : 0.05 max IR : 500Mohm or 25Mohm $\cdot \mu F$ Whichever is Smaller	With rated voltage 40 $\pm 2$ $^{\circ}C$ , 90~95%RH, 500+12/-0hrs
<b>High Temperature Resistance</b>	Capacitance change : within $\pm 12.5\%$ Tan $\delta$ : 0.05 max IR : 1000Mohm or 50Mohm $\cdot \mu F$ Whichever is Smaller	With 200% of the rated voltage Max. operating temperature  1000+48/-0hrs
<b>Temperature Cycling</b>	Capacitance change : within $\pm 7.5\%$ Tan $\delta$ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow$ 25 $^{\circ}C$ $\rightarrow$ Max. operating temperature $\rightarrow$ 25 $^{\circ}C$  5 cycle test

**C. Recommended Soldering method :**

Reflow ( Reflow Peak Temperature : 260+0/-5 $^{\circ}C$ , 10sec. Max )

\* For the more detail Specification, Please refer to the Samsung MLCC catalogue.