

SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Part Number : **CL31C122JBCNNC**
- Description : **CAP, 1.2nF, 50V, ±5%, COG, 1206**

A. Samsung Part Number

CL
①
31
②
C
③
122
④
J
⑤
B
⑥
C
⑦
N
⑧
N
⑨
N
⑩
C
⑪

| | | | |
|--------------------------------|---------------------------------------|--------------------------|-------------------------|
| ① Series | Samsung Multi-layer Ceramic Capacitor | | |
| ② Size | 1206 (inch code) | L: 3.2 ± 0.15 mm | W: 1.6 ± 0.15 mm |
| ③ Dielectric | COG | ⑧ Inner electrode | Ni |
| ④ Capacitance | 1.2 nF | Termination | Cu |
| ⑤ Capacitance tolerance | ± 5 % | Plating | Sn 100% (Pb Free) |
| ⑥ Rated Voltage | 50 V | ⑨ Product | Normal |
| ⑦ Thickness | 0.85 ± 0.15 mm | ⑩ Special | Reserved for future use |
| | | ⑪ Packaging | Cardboard Type, 7" reel |

B. Samsung Reliability Test and Judgement condition

| | Performance | Test condition |
|---|--|--|
| Capacitance | Within specified tolerance | 1kHz±10% 0.5~5Vrms |
| Q | 1000 min | |
| Insulation Resistance | 10,000Mohm or 500Mohm·μF Whichever is Smaller | Rated Voltage 60~120 sec. |
| Appearance | No abnormal exterior appearance | Microscope (×10) |
| Withstanding Voltage | No dielectric breakdown or mechanical breakdown | 300% of the rated voltage |
| Temperature Characterisitcs | COG (From -55℃ to 125℃, Capacitance change should be within ±30PPM/℃) | |
| Adhesive Strength of Termination | No peeling shall be occur on the terminal electrode | 500g-F, for 10±1 sec. |
| Bending Strength | Capacitance change : within ±5% or ±0.5pF whichever is larger | Bending to the limit (1mm) with 1.0mm/sec. |
| Solderability | More than 95% of terminal surface is to be soldered newly | 1) Sn63Pb37 solder 235±5℃, 5±0.5sec. 2) SnAg3.0Cu0.5 solder 245±5℃, 3±0.3sec. (preheating : 80~120℃ for 10~30sec.) |
| Resistance to Soldering heat | Capacitance change : within ±2.5% or ±0.25pF whichever is larger Tan δ, IR : initial spec. | Solder pot : 270±5℃, 10±1sec. |

| | Performance | Test condition |
|------------------------------------|--|---|
| Vibration Test | Capacitance change : within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger Tan δ , IR : initial spec. | Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours \times 3 direction (x, y, z) |
| Humidity | Capacitance change : within $\pm 5\%$ or $\pm 0.5\text{pF}$ whichever is larger Q: 350 min IR : 1000Mohm or 50Mohm $\cdot \mu\text{F}$ Whichever is Smaller | 40 \pm 2 $^{\circ}\text{C}$, 90~95%RH, 500+12/-0hrs |
| Moisture Resistance | Capacitance change : within $\pm 7.5\%$ or $\pm 0.75\text{pF}$ whichever is larger Q : 200 min IR : 500Mohm or 25Mohm $\cdot \mu\text{F}$ Whichever is Smaller | With rated voltage 40 \pm 2 $^{\circ}\text{C}$, 90~95%RH, 500+12/-0hrs |
| High Temperature Resistance | Capacitance change : within $\pm 3\%$ or $\pm 0.3\text{pF}$ whichever is larger Q : 350 min IR : 1000Mohm or 50Mohm $\cdot \mu\text{F}$ Whichever is Smaller | With 200% of the rated voltage Max. operating temperature 1000+48/-0hrs |
| Temperature Cycling | Capacitance change : within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger Tan δ , IR : initial spec. | 1 cycle condition Min. operating temperature \rightarrow 25 $^{\circ}\text{C}$ \rightarrow Max. operating temperature \rightarrow 25 $^{\circ}\text{C}$ 5 cycle test |

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : 250 \pm 5 $^{\circ}\text{C}$, 6sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.