





REVISIONS				
REV.	ECO. NO	DESCRIPTION	DATE	BY
A	939	INITIAL RELEASE	03/08/06	MNH



**PART NUMBER CODING**  
**NR \_ J052TKEN-RC**

**PLATING**  
 ALL PLATINGS HAVE .000050" NICKEL UNDERPLATE  
 T = .000120" PURE TIN OVERALL  
 P = GOLD FLASH OVERALL

**RoHS COMPLIANT**

- NOTES:**
- INSULATOR MATERIAL: NYLON 6T
  - CONTACT MATERIAL: BRASS
  - PLATING: SEE PART NUMBER CODING
  - TEMPERATURE: -55 °C TO +105 °C
  - PROCESSING TEMP: 260 °C FOR 5 SECONDS MAX, 230 °C FOR 10 SECONDS MAX
  - UL FLAMMABILITY RATING: 94V-0
  - VOLTAGE RATING: 1500 VDC MINIMUM AT SEA LEVEL.
  - CURRENT RATING: 3 AMP PER CONTACT PAIR
  - VOLTAGE DROP: 30 MILLI VOLT AT RATED CURRENT
  - INSULATION RESISTANCE: 5000 MEGA OHM.



**RoHS COMPLIANT**

**CUSTOMER COPY**

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES[MM]		DATE	NAME	<b>SULLINS ELECTRONICS</b> DESCRIPTION <b>HEADER, 2 ROW</b>
TOLERANCES: ANGULAR: ± 1° XX = ± .02 [ .508] .XXX = ± .005 [ .1270] .XXXX = ± .0005 [ .0127] PARENTHETICAL INFORMATION IS FOR REFERENCE ONLY		DRAWN	MNH	
INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING PER: ANSI Y14.5-1984		THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.		PART NUMBER <b>NR_J052TKEN-RC</b>
SIZE	DWG. NO	REV	SCALE: 8:1 SHEET 1 OF 1	
<b>C</b>	<b>C10687</b>	<b>A</b>		