

RXW Series

Features

- 105°C, 4,000 ~ 7,000 hours assured
- Low ESR, suitable for switching power supplies
- Smaller size with large permissible ripple current
- RoHS Compliance




Sleeve & Marking Color: Black & Golden

Specifications

Items	Performance																															
Category	6.3 ~ 63V	100V																														
Temperature Range	-55°C ~ +105°C	-40°C ~ +105°C																														
Capacitance Tolerance	± 20 % (at 120Hz, 20°C)																															
Leakage Current (at 20°C)	I = 0.01CV or 3 (µA) whichever is greater (after 2 minutes) Where, C = rated capacitance in µF, V = rated DC working voltage in V																															
Tanδ (at 120 Hz, 20°C)	<table border="1"> <tr> <th>Rated Voltage</th> <td>6.3</td> <td>10</td> <td>16</td> <td>25</td> <td>35</td> <td>50</td> <td>63</td> <td>100</td> </tr> <tr> <th>Tanδ (max)</th> <td>0.22</td> <td>0.19</td> <td>0.16</td> <td>0.14</td> <td>0.12</td> <td>0.10</td> <td>0.09</td> <td>0.08</td> </tr> </table> <p>When the capacitance exceeds 1000µF, 0.02 shall be added every 1000µF increase.</p>		Rated Voltage	6.3	10	16	25	35	50	63	100	Tanδ (max)	0.22	0.19	0.16	0.14	0.12	0.10	0.09	0.08												
Rated Voltage	6.3	10	16	25	35	50	63	100																								
Tanδ (max)	0.22	0.19	0.16	0.14	0.12	0.10	0.09	0.08																								
Low Temperature Characteristics (at 120Hz)	<p>Impedance ratio shall not exceed the values given in the table below.</p> <table border="1"> <tr> <th>Rated Voltage</th> <td>6.3</td> <td>10</td> <td>16</td> <td>25</td> <td>35</td> <td>50</td> <td>63</td> <td>100</td> </tr> <tr> <th>Impedance Ratio</th> <td>Z(-55°C/-40°C) / Z(+20°C)</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> </tr> </table>		Rated Voltage	6.3	10	16	25	35	50	63	100	Impedance Ratio	Z(-55°C/-40°C) / Z(+20°C)	3	3	3	3	3	3	3												
Rated Voltage	6.3	10	16	25	35	50	63	100																								
Impedance Ratio	Z(-55°C/-40°C) / Z(+20°C)	3	3	3	3	3	3	3																								
Endurance	<table border="1"> <tr> <th>Test Time</th> <td>4,000 Hrs for φD ≤ 6.3 mm; 5,000 Hrs for φD = 8 mm; 6,000 Hrs for φD = 10 mm; 7,000 Hrs for φD ≥ 12.5 mm</td> </tr> <tr> <th>Capacitance Change</th> <td>Within ±25% of initial value</td> </tr> <tr> <th>Tanδ</th> <td>Less than 200% of specified value</td> </tr> <tr> <th>Leakage Current</th> <td>Within specified value</td> </tr> </table> <p>* The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied with rated ripple current for 4,000 ~ 7,000 hours at 105°C.</p>		Test Time	4,000 Hrs for φD ≤ 6.3 mm; 5,000 Hrs for φD = 8 mm; 6,000 Hrs for φD = 10 mm; 7,000 Hrs for φD ≥ 12.5 mm	Capacitance Change	Within ±25% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																						
Test Time	4,000 Hrs for φD ≤ 6.3 mm; 5,000 Hrs for φD = 8 mm; 6,000 Hrs for φD = 10 mm; 7,000 Hrs for φD ≥ 12.5 mm																															
Capacitance Change	Within ±25% of initial value																															
Tanδ	Less than 200% of specified value																															
Leakage Current	Within specified value																															
Shelf Life Test	<table border="1"> <tr> <th>Test Time</th> <td>1,000 Hrs</td> </tr> <tr> <th>Capacitance Change</th> <td>Within ±25% of initial value</td> </tr> <tr> <th>Tanδ</th> <td>Less than 200% of specified value</td> </tr> <tr> <th>Leakage Current</th> <td>Within specified value</td> </tr> </table> <p>* The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied.</p>		Test Time	1,000 Hrs	Capacitance Change	Within ±25% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																						
Test Time	1,000 Hrs																															
Capacitance Change	Within ±25% of initial value																															
Tanδ	Less than 200% of specified value																															
Leakage Current	Within specified value																															
Ripple Current and Frequency Multipliers	<table border="1"> <tr> <th>Cap.(µF) \ Freq.(Hz)</th> <th>120</th> <th>1k</th> <th>10k</th> <th>100k up</th> </tr> <tr> <td>under ~ 33</td> <td>0.42</td> <td>0.70</td> <td>0.90</td> <td>1.0</td> </tr> <tr> <td>39 ~ 270</td> <td>0.5</td> <td>0.73</td> <td>0.92</td> <td>1.0</td> </tr> <tr> <td>330 ~ 680</td> <td>0.55</td> <td>0.77</td> <td>0.94</td> <td>1.0</td> </tr> <tr> <td>820 ~ 1,800</td> <td>0.6</td> <td>0.80</td> <td>0.96</td> <td>1.0</td> </tr> <tr> <td>2,200 ~ 15,000</td> <td>0.7</td> <td>0.85</td> <td>0.98</td> <td>1.0</td> </tr> </table>		Cap.(µF) \ Freq.(Hz)	120	1k	10k	100k up	under ~ 33	0.42	0.70	0.90	1.0	39 ~ 270	0.5	0.73	0.92	1.0	330 ~ 680	0.55	0.77	0.94	1.0	820 ~ 1,800	0.6	0.80	0.96	1.0	2,200 ~ 15,000	0.7	0.85	0.98	1.0
Cap.(µF) \ Freq.(Hz)	120	1k	10k	100k up																												
under ~ 33	0.42	0.70	0.90	1.0																												
39 ~ 270	0.5	0.73	0.92	1.0																												
330 ~ 680	0.55	0.77	0.94	1.0																												
820 ~ 1,800	0.6	0.80	0.96	1.0																												
2,200 ~ 15,000	0.7	0.85	0.98	1.0																												


Diagram of Dimensions



Lead Spacing and Diameter Unit: mm

φD	5	6.3	8	10	12.5	16	18
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5
φd	0.5		0.6		0.8		
α	L < 20: 1.5, L ≥ 20: 2.0						
β	0.5						

The case size of 16×20, 18×20 and 18×25 are suitable for below diagram:



All product specifications in the catalog are subject to change without notice. (CAT. 2019E1)

Dimension: $\phi \times L$ (mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Dimension and Permissible Ripple Current

Rated Volt. V_{DC}	Contents																
	Cap. (μF)	6.3V (0J)				10V (1A)				16V (1C)				25V (1E)			
		$\phi \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C)	$\phi \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C)	$\phi \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C)	$\phi \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C)
			20°C	-10°C	100k Hz		20°C	-10°C	100k Hz		20°C	-10°C	100k Hz		20°C	-10°C	100k Hz
4.7													5×11	0.6	1.2	180	
10									5×11	0.6	1.2	180	5×11	0.6	1.2	180	
22	5×11	0.6	1.2	180	5×11	0.6	1.2	180	5×11	0.6	1.2	180	5×11	0.6	1.2	180	
33	5×11	0.6	1.2	180	5×11	0.6	1.2	180	5×11	0.6	1.2	180	5×11	0.6	1.2	180	
39													5×11	0.6	1.2	180	
47	5×11	0.6	1.2	180	5×11	0.6	1.2	180	5×11	0.6	1.2	180	5×11	0.6	1.2	180	
56									5×11	0.6	1.2	180					
82					5×11	0.6	1.2	180					6.3×11	0.25	0.50	290	
100	5×11	0.6	1.2	180	5×11	0.6	1.2	180	6.3×11	0.25	0.5	290	6.3×11	0.25	0.50	290	
120									6.3×11	0.25	0.5	290	6.3×15	0.23	0.46	430	
150	6.3×11	0.25	0.5	290	6.3×11	0.25	0.5	290	6.3×11	0.25	0.5	290	8×11.5	0.117	0.234	555	
180					6.3×11	0.25	0.5	290	6.3×15	0.23	0.46	430					
220	6.3×11	0.25	0.5	290	6.3×11	0.25	0.5	290	8×11.5	0.117	0.234	555	8×11.5	0.117	0.234	555	
					6.3×15	0.23	0.46	430									
330	6.3×11	0.25	0.50	290	8×11.5	0.117	0.234	555	8×11.5	0.117	0.234	555	8×15	0.085	0.17	730	
	6.3×15	0.23	0.46	430					8×15	0.085	0.17	730	10×12.5	0.090	0.18	755	
470	8×11.5	0.117	0.234	555	8×11.5	0.117	0.234	555	10×12.5	0.090	0.18	755	8×20	0.065	0.130	995	
													10×16	0.068	0.136	1,050	
560	8×11.5	0.117	0.234	555									10×20	0.052	0.104	1,220	
680	10×12.5	0.090	0.180	755	8×15	0.085	0.170	730	8×20	0.065	0.130	995	10×20	0.052	0.104	1,220	
					10×12.5	0.090	0.180	755	10×16	0.068	0.136	1,050					
820	8×15	0.085	0.170	730					10×20	0.052	0.104	1,220	10×25	0.045	0.090	1,440	
	10×12.5	0.090	0.180	755													
1,000	10×12.5	0.090	0.180	755	8×20	0.065	0.130	995	10×20	0.052	0.104	1,220	10×30	0.035	0.070	1,815	
					10×16	0.068	0.136	1,050					12.5×20	0.030	0.060	1,945	
1,200	8×20	0.065	0.130	955	10×20	0.052	0.104	1,220	10×25	0.045	0.090	1,440	16×25	0.022	0.044	2,555	
	10×16	0.068	0.136	1,050													
1,500	10×20	0.052	0.104	1,220	10×20	0.052	0.104	1,220	12.5×20	0.038	0.076	1,655	12.5×25	0.030	0.060	1,945	
					10×25	0.045	0.090	1,440	10×30	0.035	0.070	1,815	16×25	0.022	0.044	2,555	
1,800													12.5×30	0.025	0.050	2,310	
													16×20	0.029	0.058	2,205	
2,200	10×25	0.045	0.090	1,440	10×30	0.035	0.070	1,815	12.5×25	0.030	0.06	1,945	12.5×35	0.022	0.044	2,510	
	12.5×20	0.038	0.076	1,615	12.5×20	0.038	0.076	1,655					16×25	0.022	0.044	2,555	
2,700	10×30	0.035	0.070	1,815	12.5×25	0.030	0.060	1,945	12.5×30	0.025	0.05	2,310	16×20	0.028	0.056	2,490	
									16×20	0.029	0.058	2,205	18×20	0.028	0.056	2,490	
3,300	12.5×20	0.038	0.076	1,655	12.5×25	0.030	0.060	1,945	16×25	0.022	0.044	2,555	16×31.5	0.018	0.036	3,010	
					12.5×30	0.025	0.050	2,310	12.5×35	0.022	0.044	2,510	18×25	0.020	0.040	2,740	
3,900	12.5×25	0.030	0.060	1,945	12.5×35	0.022	0.044	2,510	16×25	0.022	0.044	2,555	16×35.5	0.016	0.032	3,150	
					16×20	0.029	0.058	2,205	18×20	0.028	0.056	2,490	18×31.5	0.016	0.032	3,635	
4,700	12.5×30	0.025	0.050	2,310	16×25	0.022	0.044	2,555	16×31.5	0.018	0.036	3,010	18×35.5	0.015	0.030	3,680	
	16×25	0.022	0.044	2,555					18×25	0.020	0.040	2,740					
5,600	16×20	0.029	0.058	2,205	16×25	0.022	0.044	2,555	16×35.5	0.016	0.032	3,150					
					18×20	0.028	0.056	2,490	18×25	0.020	0.040	2,740					
6,800	16×25	0.022	0.044	2,555	16×31.5	0.018	0.036	3,010	18×35.5	0.015	0.030	3,680	18×40	0.014	0.028	3,800	
	18×20	0.028	0.056	2,490	18×25	0.020	0.040	2,740									
8,200	16×31.5	0.018	0.036	3,010	16×35.5	0.016	0.032	3,150	18×35.5	0.015	0.030	3,680					
					18×31.5	0.016	0.032	3,635									
10,000	16×31.5	0.016	0.032	3,150	18×35.5	0.015	0.030	3,680	18×40	0.014	0.028	3,800					
	18×25	0.020	0.040	2,740													
12,000	18×31.5	0.016	0.032	3,635													
15,000	18×35.5	0.015	0.030	3,680	18×40	0.014	0.028	3,800									

Dimension: $\phi D \times L$ (mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Dimension and Permissible Ripple Current

Rated Volt. V_{DC} Contents Cap. (μF)	35V (1V)				50V (1H)				63V (1J)			100V (2A)				
	$\phi D \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance (Ω , max./100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz
		20°C	-10°C			20°C	-10°C			20°C	-10°C			20°C	-10°C	
2.2													5×11	9.8	19.6	44
3.3													5×11	6.6	13.2	58
4.7	5×11	0.6	1.2	180	5×11	2.3	4.6	90	5×11	4.7	9.4	68	5×11	4.6	9.2	74
6.8									5×11	2.5	5.0	95	5×11	3.5	7.0	95
10	5×11	0.6	1.2	180	5×11	1.4	2.8	120	5×11	2.1	4.2	110	6.3×11	1.8	3.6	130
12									5×11	2.0	4.0	145				
15									6.3×11	1.2	2.4	160	8×11.5	0.83	1.66	180
18					5×11	1.3	2.6	155					6.3×15	0.80	1.60	200
22	5×11	0.6	1.2	180	5×11	1.2	2.4	170	6.3×11	0.71	1.42	250	8×11.5	0.68	1.36	230
27	5×11	0.6	1.2	180												
33	5×11	0.6	1.2	180	6.3×11	0.43	0.86	300	6.3×11	0.71	1.42	250	8×15 10×12.5	0.45 0.46	0.90 0.92	360 320
39									6.3×15	0.70	1.40	330				
47	6.3×11	0.25	0.5	290	6.3×11	0.43	0.86	300	8×11.5	0.342	0.684	405	10×16 8×20	0.37 0.37	0.74 0.74	420 420
56	6.3×11	0.25	0.5	290	6.3×15	0.40	0.80	360								
68									8×11.5	0.342	0.684	405	10×20	0.30	0.60	490
82	6.3×15	0.23	0.46	430	8×11.5	0.234	0.468	485					10×25	0.25	0.50	540
100	8×11.5	0.117	0.234	555	8×11.5	0.234	0.468	485	10×12.5 8×15	0.256 0.230	0.512 0.460	535 535	12.5×20	0.18	0.36	580
120					8×15 10×12.5	0.155 0.162	0.310 0.324	635 615	10×16	0.194	0.388	600				
150	8×11.5	0.117	0.234	555	10×12.5	0.162	0.324	615	10×16	0.194	0.388	660	12.5×25	0.13	0.26	710
180					8×20 10×16	0.120 0.119	0.240 0.238	860 850	10×20 12.5×16	0.147 0.150	0.294 0.300	885 1,020	12.5×30 16×20	0.12 0.13	0.24 0.26	790 750
220	8×15 10×12.5	0.085 0.090	0.17 0.18	730 755	10×16 10×20	0.119 0.090	0.238 0.180	850 1,030	10×20 10×25	0.147 0.130	0.294 0.260	885 1,050	16×25 18×20	0.10 0.11	0.20 0.22	890 850
270					10×25	0.082	0.164	1,200	16×16	0.090	0.180	1,410				
330	8×20 10×16	0.065 0.068	0.130 0.136	995 1,050	10×20 10×30	0.090 0.060	0.180 0.120	1,030 1,610	12.5×20	0.085	0.170	1,285	16×25	0.090	0.180	1,080
390	10×20	0.052	0.104	1,220	12.5×20	0.063	0.126	1,480	12.5×25 18×16	0.070 0.086	0.140 0.172	1,720 1,690	18×25	0.083	0.166	1,260
470	10×20	0.052	0.104	1,220	12.5×20	0.060	0.120	1,500	12.5×25 12.5×30 16×20	0.070 0.055 0.059	0.140 0.110 0.118	1,720 2,090 1,765	16×31.5	0.076	0.152	1,310
560	10×25	0.045	0.090	1,440	12.5×25	0.050	0.100	1,832	16×25	0.050	0.100	2,160	18×31.5 18×35.5	0.068 0.064	0.136 0.128	1,370 1,410
680	10×30 12.5×20	0.035 0.038	0.070 0.076	1,815 1,655	12.5×25 16×20	0.050 0.048	0.100 0.096	1,832 1,835	12.5×35 18×20	0.047 0.055	0.094 0.110	2,265 2,290				
820					12.5×35 18×20	0.034 0.042	0.068 0.084	2,285 2,200	16×31.5 18×25	0.043 0.043	0.086 0.086	2,670 2,585	18×40	0.047	0.094	1,520
1,000	12.5×25	0.030	0.060	1,945	16×25	0.034	0.068	2,235	16×31.5 16×35.5	0.043 0.036	0.086 0.072	2,670 2,770				
1,200	12.5×30 16×20	0.025 0.029	0.050 0.058	2,310 2,205	16×31.5 18×25	0.028 0.029	0.056 0.058	2,700 2,610	18×31.5	0.032	0.064	2,950				
1,500	12.5×35 16×25	0.022 0.022	0.044 0.044	2,510 2,555	16×31.5 16×35.5	0.028 0.025	0.056 0.050	2,700 2,790	18×35.5	0.030	0.060	3,095				
1,800	16×25 18×20	0.022 0.028	0.044 0.056	2,555 2,490	18×31.5	0.025	0.05	3,000								
2,200	16×31.5 18×25	0.018 0.020	0.036 0.040	3,010 2,740	18×35.5	0.023	0.046	3,100	18×40	0.028	0.056	3,200				
2,700	16×35.5 18×31.5	0.016 0.016	0.032 0.032	3,150 3,635												
3,300	18×35.5	0.015	0.030	3,680												
4,700	18×40	0.014	0.028	3,800												

Part Numbering System

RXW Series	470 μF	$\pm 20\%$	6.3V	Bulk Package	Gas Type	8 $\phi \times 11.5L$	Pb-free and PET sleeve
<u>RXW</u>	<u>471</u>	<u>M</u>	<u>OJ</u>	<u>BK</u>	-	<u>0811</u>	<u>S</u>
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Lead Configuration & Package	Rubber Type	Case Size	Lead Wire and Sleeve type
							Supplement Code

Note: For more details, please refer to "Part Numbering System (Radial Type)"