



## Sierra Wireless® WP Series Embedded Modules

### ULTRA-LOW POWER DOMAIN

Ideal for remote solar or battery-powered applications, the WP Series integrated power management feature can reduce power consumption by 200x compared to previous modules, enabling new use-cases for cellular. For example:

- Devices that only need to transmit data once a day can now run on a single battery for up to 3 years\*
- Devices that only need to transmit data once a week can now run on a single battery for 10 years\*

\*based on sending 100kb of data, powered by a standard consumer-grade battery, operating on a 2G network.

22mm



23mm

## Expect more, do more with the next-gen WP

Sierra Wireless® AirPrime® WP Series provides an integrated device-to-cloud architecture enabling IoT developers to build a Linux-based product on a single module and seamlessly send valuable user and product data to the cloud. Offering an application processor running the open source Legato® platform, GNSS receiver, and cellular modem with an ultra-low power domain, WP modules reduce system complexity and get you to market faster.

### SIMPLIFY SYSTEM DEVELOPMENT WITH A DEVICE-TO-CLOUD ARCHITECTURE

- All the key hardware components of your connected product in a compact form factor to save board space and reduce total BOM (bill of materials)
- Integrated Legato platform that maintains your Linux distribution and includes an application framework, development tools, and community support
- Integrated AirVantage® cloud services make it easy to access product and user data into your backend enterprise applications.

### FUTURE-PROOF YOUR PRODUCT DESIGNS

- CF3® (common flexible form factor) module design provides worldwide coverage on 2G, 3G, 4G, and LPWA networks, is compatible with HL Series of modules, and capable of supporting new wireless technologies
- The professionally maintained open source Legato platform for IoT enables you to reuse software components and applications in future designs with no vendor lock-in
- AirVantage cloud services with big data storage grows with your deployments and can power future revenue-generating services as your business evolves

### KEEP YOUR PRODUCTS DEPLOYED FOR YEARS IN THE FIELD

- New ultra-low power domain can reduce power consumption by 200x opening new use-cases for cellular where 100% connectivity to the network is not required
- Application sandbox within the Legato platform hosts your proprietary software and provides a secure place for 3rd party applications to enable future services for your customers
- Unlimited FOTA (firmware over-the-air) powered by AirVantage maintains optimized connectivity as networks evolve and keeps your data transmission protected as new security threats arise

Sierra Wireless  
WP SERIES EMBEDDED MODULES

|  | WP7502   | WP7504   | WP7504-1                                       | WP8548   |
|--|--|--|--|--|
| <b>Target Region</b>                           | EMEA   | Americas                                       | Americas                                       | Global   |
| <b>4G LTE</b>                                  |  |  |  |  |
| <b>Category</b>                                | Cat-3  | Cat-3  | Cat-3  |  |
| <b>Frequency Bands</b>                         | B1, B3, B7, B8, B20                            | B2, B4, B5, B12, B17, B25, B26                 | B2, B4, B5, B12, B17, B25, B26                 |  |
| <b>3G</b>                                      |  |  |  |  |
| <b>Technology supported</b>                    | HSPA+, UMTS                                    | HSPA+, UMTS                                    | HSPA+, UMTS                                    | HSPA+, UMTS                                    |
| <b>Frequency Bands</b>                         | B1, B8   | B2, B4, B5                                     | B2, B4, B5                                     | B1, B2, B5, B6, B8, B19                        |
| <b>Technology supported</b>                    |  | EVDO   |  |  |
| <b>Frequency Bands</b>                         |  | BC0, BC1, BC10                                 |  |  |
| <b>2G</b>                                      |  |  |  |  |
| <b>Technology supported</b>                    | EDGE, GSM, GPRS                                | CDMA   |  | EDGE, GSM, GPRS                                |
| <b>Frequency Bands</b>                         | 900, 1800                                      | BC0, BC1, BC10                                 |  | 850, 900, 1800, 1900                           |
| <b>DATA SPEED</b>                              |  |  |  |  |
| <b>Peak Download Rate</b>                      | 100 Mbps                                       | 100 Mbps                                       | 100 Mbps                                       | 42 Mbps  |
| <b>Peak Upload Rate</b>                        | 50 Mbps  | 50 Mbps  | 50 Mbps  | 5.76 Mbps                                      |
| <b>LOCATION SERVICES</b>                       |  |  |  |  |
| <b>Satellite Systems (Optional)</b>            | GPS, Galileo, Glonass                          | GPS, Galileo, Glonass                          | GPS, Galileo, Glonass                          | GPS, Galileo, Glonass                          |
| <b>CORES</b>                                   |  |  |  |  |
| <b>Application Core</b>                        | ARM® Cortex™- A5 (550MHz)                      | ARM® Cortex™- A5 (550MHz)                      | ARM® Cortex™- A5 (550MHz)                      | ARM® Cortex™- A5 (550MHz)                      |
| <b>Telecom Core</b>                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            |
| <b>EMBEDDED SOFTWARE</b>                       |  |  |  |  |
| <b>Pre-certified Firmware</b>                  | ✓  | ✓  | ✓  | ✓  |
| <b>APPLICATION FRAMEWORK</b>                   |  |  |  |  |
| <b>Embedded Platform</b>                       | Legato® open source                            | Legato® open source                            | Legato® open source                            | Legato® open source                            |
| <b>Linux Distribution</b>                      | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) |
| <b>AUDIO CODECS</b>                            |  |  |  |  |
| <b>Digital audio</b>                           | ✓  | ✓  | ✓  | ✓  |
| <b>PCM/12S</b>                                 | ✓  | ✓  | ✓  | ✓  |
| <b>Codec: HR, FR, EFR, AMR</b>                 | ✓  | ✓  | ✓  | ✓  |
| <b>Echo cancellation &amp; noise reduction</b> | ✓  | ✓  | ✓  | ✓  |
| <b>DTMF</b>                                    | ✓  | ✓  | ✓  | ✓  |
| <b>USB DRIVERS</b>                             |  |  |  |  |
| <b>Windows® 7 and 8</b>                        | ✓  | ✓  | ✓  | ✓  |
| <b>Linux Driver</b>                            | ✓  | ✓  | ✓  | ✓  |
| <b>INTERFACES</b>                              |  |  |  |  |
| <b>UART</b>                                    | 2  | 2  | 2  | 2  |
| <b>USB</b>                                     | 1  | 1  | 1  | 1  |
| <b>I2C</b>                                     | 1  | 1  | 1  | 1  |
| <b>ADC</b>                                     | 4  | 4  | 4  | 4  |
| <b>GPIO</b>                                    | 20   | 20   | 20   | 20   |
| <b>Tx ON Indicator</b>                         | 1  | 1  | 1  | 1  |
| <b>SIM Interface 1.8V/3V</b>                   | 2  | 2  | 2  | 2  |
| <b>HARDWARE</b>                                |  |  |  |  |
| <b>CF3™ Form Factor (LGA)</b>                  | ✓  | ✓  | ✓  | ✓  |
| <b>Snap-in socket option</b>                   | ✓  | ✓  | ✓  | ✓  |
| <b>Dimensions</b>                              | 22x23x4.4mm                                    | 22x23x4.4mm                                    | 22x23x4.4mm                                    | 22x23x4.4mm                                    |
| <b>Antenna: Diversity</b>                      | ✓  | ✓  | ✓  | ✓  |
| <b>Antenna: MIMO</b>                           | ✓  | ✓  | ✓  | ✓  |
| <b>TEMPERATURE RANGE</b>                       |  |  |  |  |
| <b>Industrial Grade</b>                        | -40°C to +85°C                                 | -40°C to +85°C                                 | -40°C to +85°C                                 | -40°C to +85°C                                 |
| <b>APPROVALS</b>                               |  |  |  |  |
| <b>Regulatory</b>                              | CE, GCF  | PTCRB, FCC, GCF, IC                            | PTCRB, FCC, GCF, IC                            | CE, FCC, PTCRB, GCF, IC, JRF/JPA, NCC          |
| <b>Carrier</b>                                 |  | AT&T, Sprint, T-Mobile                         | AT&T, Sprint, T-Mobile                         | AT&T   |
| <b>CLOUD SERVICES</b>                          |  |  |  |  |
| <b>Free Unlimited FOTA upgrades</b>            | ✓  | ✓  | ✓  | ✓  |
| <b>Device Management option</b>                | ✓  | ✓  | ✓  | ✓  |
| <b>Application Enablement option</b>           | ✓  | ✓  | ✓  | ✓  |
| <b>Connectivity Management option</b>          | ✓  | ✓  | ✓  | ✓  |

Sierra Wireless  
WP SERIES EMBEDDED MODULES

|   | WP7601   | WP7601-1                                       | WP7603   | WP7603-1                                       |
|---|--|--|--|--|
| <b>Target Region</b>  | Americas                                       | Americas                                       | Americas                                       | Americas                                       |
| <b>4G LTE</b>   |  |  |  |  |
| <b>Category</b>   | Cat-4  | Cat-1  | Cat-4  | Cat-1  |
| <b>Frequency Bands</b>  | B4, B13  | B4, B13  | B2, B4, B5, B12                                | B2, B4, B5, B12                                |
| <b>3G</b>   |  |  |  |  |
| <b>Technology supported</b>                                   |  |  | HSPA+, UMTS                                    | HSPA+, UMTS                                    |
| <b>Frequency Bands</b>  |  |  | B2, B4, B5                                     | B2, B4, B5                                     |
| <b>DATA SPEED</b>   |  |  |  |  |
| <b>Peak Download Rate</b>                                     | 150 Mbps                                       | 10 Mbps  | 150 Mbps                                       | 10 Mbps  |
| <b>Peak Upload Rate</b>                                       | 50 Mbps  | 5 Mbps   | 50 Mbps  | 50 Mbps  |
| <b>LOCATION SERVICES</b>                                      |  |  |  |  |
| <b>Satellite Systems (Optional)</b>                           | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  |
| <b>CORES</b>  |  |  |  |  |
| <b>Application Core</b>                                       | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      |
| <b>Telecom Core</b>   | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            |
| <b>EMBEDDED SOFTWARE</b>                                      |  |  |  |  |
| <b>Secure Boot</b>  | ✓  | ✓  | ✓  | ✓  |
| <b>Pre-certified Firmware</b>                                 | ✓  | ✓  | ✓  | ✓  |
| <b>APPLICATION FRAMEWORK</b>                                  |  |  |  |  |
| <b>Embedded Platform</b>                                      | Legato® open source                            | Legato® open source                            | Legato® open source                            | Legato® open source                            |
| <b>Linux Distribution</b>                                     | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) |
| <b>AUDIO CODECS</b>   |  |  |  |  |
| <b>Digital audio</b>  | ✓  | ✓  | ✓  | ✓  |
| <b>PCM/12S</b>  | ✓  | ✓  | ✓  | ✓  |
| <b>Codec: HR, FR, EFR, AMR</b>                                | ✓  | ✓  | ✓  | ✓  |
| <b>Echo cancellation &amp; noise reduction</b>                | ✓  | ✓  | ✓  | ✓  |
| <b>DTMF</b>   | ✓  | ✓  | ✓  | ✓  |
| <b>USB DRIVERS</b>  |  |  |  |  |
| <b>Windows® 7 and 8</b>                                       | ✓  | ✓  | ✓  | ✓  |
| <b>Linux</b>  | ✓  | ✓  | ✓  | ✓  |
| <b>INTERFACES</b>   |  |  |  |  |
| <b>UART</b>   | 2  | 2  | 2  | 2  |
| <b>USB</b>  | 1  | 1  | 1  | 1  |
| <b>I2C</b>  | 1  | 1  | 1  | 1  |
| <b>ADC</b>  | 4  | 4  | 4  | 4  |
| <b>GPIO</b>   | 18   | 18   | 18   | 18   |
| <b>Tx ON Indicator</b>  | 1  | 1  | 1  | 1  |
| <b>SIM Interface 1.8V/3V</b>                                  | 1  | 1  | 1  | 1  |
| <b>HARDWARE</b>   |  |  |  |  |
| <b>CF3™ Form Factor (LGA)</b>                                 | ✓  | ✓  | ✓  | ✓  |
| <b>Snap-in socket option</b>                                  | ✓  | ✓  | ✓  | ✓  |
| <b>Dimensions</b>   | 22x23x2.5mm                                    | 22x23x2.5mm                                    | 22x23x2.5mm                                    | 22x23x2.5mm                                    |
| <b>Antenna: Diversity</b>                                     | ✓  | ✓  | ✓  | ✓  |
| <b>Antenna: MIMO</b>  | ✓  | ✓  | ✓  | ✓  |
| <b>TEMPERATURE RANGE</b>                                      |  |  |  |  |
| <b>Industrial Grade</b>                                       | -40°C to +85°C                                 | -40°C to +85°C                                 | -40°C to +85°C                                 | -40°C to +85°C                                 |
| <b>APPROVALS</b>  |  |  |  |  |
| <b>Regulatory</b>   | FCC, IC  | FCC, IC  | FCC, IC  | FCC, IC  |
| <b>Carrier</b>  | Verizon  | Verizon  | AT&T, T-Mobile                                 | AT&T, T-Mobile                                 |
| <b>APPROVALS</b>  |  |  |  |  |
| <b>Optional Ready-to-Connect Sierra Wireless embedded SIM</b> | ✓  | ✓  | ✓  | ✓  |
| <b>CLOUD SERVICES</b>   |  |  |  |  |
| <b>Free Unlimited FOTA upgrades</b>                           | ✓  | ✓  | ✓  | ✓  |
| <b>Device Management option</b>                               | ✓  | ✓  | ✓  | ✓  |
| <b>Application Enablement option</b>                          | ✓  | ✓  | ✓  | ✓  |
| <b>Connectivity Management option</b>                         | ✓  | ✓  | ✓  | ✓  |

Note: VoLTE supported as a firmware upgrade

Sierra Wireless  
WP SERIES EMBEDDED MODULES

|   | WP7607   | WP7607-1                                       | WP7608   | WP7608-1                                       | WP7609   |
|---|--|--|--|--|--|
| <b>Target Region</b>  | EMEA   | EMEA   | India/China                                    | India/China                                    | Australia                                      |
| <b>4G LTE</b>   |  |  |  |  |  |
| <b>Category</b>   | Cat-4  | Cat-1  | Cat-4  | Cat-1  | Cat-4  |
| <b>Frequency Bands</b>  | B1, B3, B7, B8, B20, B28                       | B1, B3, B7, B8, B20, B28                       | B1, B3, B5, B8, B40, B41*                      | B1, B3, B5, B8, B40, B41*                      | B1, B3, B5, B7, B8, B28                        |
| <b>3G</b>   |  |  |  |  |  |
| <b>Technology supported</b>                                   | HSPA+, UMTS                                    | HSPA+, UMTS                                    | HSPA+, UMTS                                    | HSPA+, UMTS                                    | HSPA+, UMTS                                    |
| <b>Frequency Bands</b>  | B1, B8   | B1, B8   | B1, B8   | B1, B8   | B1, B5, B8                                     |
| <b>2G</b>   |  |  |  |  |  |
| <b>Technology supported</b>                                   | EDGE, GSM, GPRS                                | EDGE, GSM, GPRS                                | EDGE, GSM, GPRS                                | EDGE, GSM, GPRS                                |  |
| <b>Frequency Bands</b>  | 900, 1800                                      | 900, 1800                                      | 900, 1800                                      | 900, 1800                                      |  |
| <b>DATA SPEED</b>   |  |  |  |  |  |
| <b>Peak Download Rate</b>                                     | 150 Mbps                                       | 10 Mbps  | 150 Mbps                                       | 10 Mbps  | 150 Mbps                                       |
| <b>Peak Upload Rate</b>                                       | 50 Mbps  | 5 Mbps   | 5 Mbps   | 5 Mbps   | 50 Mbps  |
| <b>LOCATION SERVICES</b>                                      |  |  |  |  |  |
| <b>Satellite Systems (Optional)</b>                           | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  | GPS, Galileo, Glonass, Beidou                  |
| <b>CORES</b>  |  |  |  |  |  |
| <b>Application Core</b>                                       | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      | ARM® Cortex™- A7 (1.3GHz)                      |
| <b>Telecom Core</b>   | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            | Dual QDSP6 (600MHz)                            |
| <b>EMBEDDED SOFTWARE</b>                                      |  |  |  |  |  |
| <b>Secure Boot</b>  | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Pre-certified Firmware</b>                                 | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>APPLICATION FRAMEWORK</b>                                  |  |  |  |  |  |
| <b>Embedded Platform</b>                                      | Legato® open source                            | Legato® open source                            | Legato® open source                            | Legato® open source                            | Legato® open source                            |
| <b>Linux Distribution</b>                                     | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) | Yocto, Long-term supported Linux Kernel (LTSI) |
| <b>AUDIO CODECS</b>   |  |  |  |  |  |
| <b>Digital audio</b>  | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>PCM/12S</b>  | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Codec: HR, FR, EFR, AMR</b>                                | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Echo cancellation &amp; noise reduction</b>                | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>DTMF</b>   | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>USB DRIVERS</b>  |  |  |  |  |  |
| <b>Windows® 7 and 8</b>                                       | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Linux</b>  | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>INTERFACES</b>   |  |  |  |  |  |
| <b>UART</b>   | 2  | 2  | 2  | 2  | 2  |
| <b>USB</b>  | 1  | 1  | 1  | 1  | 1  |
| <b>I2C</b>  | 1  | 1  | 1  | 1  | 1  |
| <b>ADC</b>  | 4  | 4  | 4  | 4  | 4  |
| <b>GPIO</b>   | 18   | 18   | 18   | 18   | 18   |
| <b>Tx ON Indicator</b>  | 1  | 1  | 1  | 1  | 1  |
| <b>SIM Interface 1.8V/3V</b>                                  | 1  | 1  | 1  | 1  | 1  |
| <b>HARDWARE</b>   |  |  |  |  |  |
| <b>CF3™ Form Factor (LGA)</b>                                 | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Snap-in socket option</b>                                  | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Dimensions</b>   | 22x23x2.5mm                                    | 22x23x2.5mm                                    | 22x23x2.5mm                                    | 22x23x2.5mm                                    | 22x23x2.5mm                                    |
| <b>Antenna: Diversity</b>                                     | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Antenna: MIMO</b>  | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>TEMPERATURE RANGE</b>                                      |  |  |  |  |  |
| <b>Industrial Grade</b>                                       | -40°C to +85°C                                 | -40°C to +85°C                                 | -40°C / +85°C                                  | -40°C / +85°C                                  | -40°C to +85°C                                 |
| <b>APPROVALS</b>  |  |  |  |  |  |
| <b>Regulatory</b>   | GCF  | GCF  | GCF  | GCF  | GCF, RCM                                       |
| <b>Carrier</b>  |  |  |  |  | Telstra, Optus, Vodafone                       |
| <b>CONNECTIVITY</b>   |  |  |  |  |  |
| <b>Optional Ready-to-Connect Sierra Wireless embedded SIM</b> | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>CLOUD SERVICES</b>   |  |  |  |  |  |
| <b>Free Unlimited FOTA upgrades</b>                           | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Device Management option</b>                               | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Application Enablement option</b>                          | ✓  | ✓  | ✓  | ✓  | ✓  |
| <b>Connectivity Management option</b>                         | ✓  | ✓  | ✓  | ✓  | ✓  |

\*B41 supported frequency range: (2535–2655 MHz)  
Note: VoLTE supported as a firmware upgrade

|   | WP7700   | WP7702   |
|---|--|--|
| <b>Target Region</b>  | Global   | Global   |
| <b>4G LTE</b>   |  |  |
| <b>Category</b>   | Cat-M1/NB1   | Cat-M1/NB1   |
| <b>Frequency Bands</b>  | B1, B2, B3, B4, B5, B8, B12, B13, B17, B18, B19, B20, B26, B28 | B1, B2, B3, B4, B5, B8, B12, B13, B17, B18, B19, B20, B26, B28 |
| <b>2G</b>   |  |  |
| <b>Technology supported</b>                                   |  | GSM, GPRS  |
| <b>Frequency Bands</b>  |  | 900, 1800  |
| <b>DATA SPEED</b>   |  |  |
| <b>Peak Download Rate</b>                                     | Cat-M1: 300kbps   Cat-NB1: 27kbps                              | Cat-M1: 300kbps   Cat-NB1: 27kbps                              |
| <b>Peak Upload Rate</b>                                       | Cat-M1: 375kbps   Cat-NB1: 65kbps                              | Cat-M1: 375kbps   Cat-NB1: 65kbps                              |
| <b>LOCATION SERVICES</b>                                      |  |  |
| <b>Satellite Systems (Optional)</b>                           | GPS, Galileo, Glonass, Beidou                                  | GPS, Galileo, Glonass, Beidou                                  |
| <b>CORES</b>  | ARM® Cortex™- A7 (1.3GHz)                                      | ARM® Cortex™- A7 (1.3GHz)                                      |
| <b>Application Core</b>                                       |  |  |
| <b>Telecom Core</b>   | Dual QDSP6 (600MHz)  | Dual QDSP6 (600MHz)  |
| <b>EMBEDDED SOFTWARE</b>                                      |  |  |
| <b>Secure Boot</b>  | ✓  | ✓  |
| <b>Pre-certified Firmware</b>                                 | ✓  | ✓  |
| <b>APPLICATION FRAMEWORK</b>                                  |  |  |
| <b>Embedded Platform</b>                                      | Legato® open source  | Legato® open source  |
| <b>Linux Distribution</b>                                     | Yocto, Long-term supported Linux Kernel (LTSI)                 | Yocto, Long-term supported Linux Kernel (LTSI)                 |
| <b>AUDIO CODECS</b>   |  |  |
| <b>Digital audio</b>  | ✓  | ✓  |
| <b>PCM/12S</b>  | ✓  | ✓  |
| <b>Codec: HR, FR, EFR, AMR</b>                                | ✓  | ✓  |
| <b>Echo cancellation &amp; noise reduction</b>                | ✓  | ✓  |
| <b>DTMF</b>   | ✓  | ✓  |
| <b>USB DRIVERS</b>  |  |  |
| <b>Windows® 7 and 8</b>                                       | ✓  | ✓  |
| <b>Linux</b>  | ✓  | ✓  |
| <b>INTERFACES</b>   |  |  |
| <b>UART</b>   | 2  | 2  |
| <b>USB</b>  | 1  | 1  |
| <b>I2C</b>  | 1  | 1  |
| <b>ADC</b>  | 4  | 4  |
| <b>GPIO</b>   | 18   | 18   |
| <b>Tx ON Indicator</b>  | 1  | 1  |
| <b>SIM Interface 1.8V/3V</b>                                  | 1  | 1  |
| <b>SPI</b>  | 1  | 1  |
| <b>HARDWARE</b>   |  |  |
| <b>CF3™ Form Factor (LGA)</b>                                 | ✓  | ✓  |
| <b>Snap-in socket option</b>                                  | ✓  | ✓  |
| <b>Dimensions</b>   | 22x23x2.5mm  | 22x23x2.5mm  |
| <b>Antenna: Diversity</b>                                     | ✓  | ✓  |
| <b>Antenna: MIMO</b>  | ✓  | ✓  |
| <b>TEMPERATURE RANGE</b>                                      |  |  |
| <b>Industrial Grade</b>                                       | -40°C to +85°C   | -40°C to +85°C   |
| <b>APPROVALS</b>  |  |  |
| <b>Regulatory</b>   | PTCRB, FCC, GCF, IC  | GCF  |
| <b>Carrier</b>  | AT&T, Verizon, NTT, Telstra                                    | AT&T, Verizon, NTT, Telstra                                    |
| <b>CONNECTIVITY</b>   |  |  |
| <b>Optional Ready-to-Connect Sierra Wireless embedded SIM</b> | ✓  | ✓  |
| <b>CLOUD SERVICES</b>   |  |  |
| <b>Free Unlimited FOTA upgrades</b>                           | ✓  | ✓  |
| <b>Device Management option</b>                               | ✓  | ✓  |
| <b>Application Enablement option</b>                          | ✓  | ✓  |
| <b>Connectivity Management option</b>                         | ✓  | ✓  |

Note: VoLTE supported as a firmware upgrade

**About Sierra Wireless**

Sierra Wireless is building the Internet of Things with intelligent wireless solutions that empower organizations to innovate in the connected world. We offer the industry's most comprehensive portfolio of 2G, 3G, 4G, and LPWA embedded modules and gateways, seamlessly integrated with our secure cloud and connectivity services. OEMs and enterprises worldwide trust our innovative solutions to get their connected products and services to market faster. For more information, visit [www.sierrawireless.com](http://www.sierrawireless.com).

Sierra Wireless, the Sierra Wireless logo, AirPrime, and the red wave design are trademarks of Sierra Wireless. Other registered trademarks that appear on this brochure are the property of the respective owners. © 2017 Sierra Wireless, Inc. 2017.09.27

