




LOC		DIST		REVISIONS					
FT		0		DESCRIPTION			DATE	DWN	APVD
		P	LTR						
			D4	ADDED -6 PER ECO-11-010232			18MAR2011	RK	HMR





#8-32 PAN HEAD
SCREW


1954381-2 & -3




#10-32 THREAD
CUTTING SCREW



SCALE 2:1



SCALE 2:1
1954381-5 ONLY



CLOSED POSITION

- ⚠ MATERIALS AND FINISH:
SLIDER: PBT OR EQUIVALENT, UV FI RATING, BLACK, 94V5
BASE: COPPER ALLOY; FINISH: Sn OVER Ni
MOUNTING HARDWARE: STAINLESS STEEL EXCEPT #8-32 HEX NUT WHICH IS CARBON STEEL

2. COMPLIES WITH DIRECTIVE 2002/95/EC (ROHS)
3. US PATENT NO: 7326069

- ⚠ 8-32 NUT IS PACKAGED AS A SEPARATE COMPONENT OF 1954381-2.
⚠ NUT WITH LOCKWASHER IS PACKAGED AS A SEPARATE COMPONENT OF 1954381-3 AND 1954381-4
⚠ APPROVED FOR USE WITH 4mm² AND 6mm² WIRE SIZES.

⚠ 6	NONE	NONE	6mm ² AND 4mm ²	1954381-6
⚠ 6	NONE	#10-32 THREAD CUTTING	6mm ² AND 4mm ²	1954381-5
⚠ 5	NUT WITH LOCKWASHER	#10-32 PAN HEAD .625LG	10-12 AWG, 4mm ²	1954381-4
⚠ 5	NUT WITH LOCKWASHER	#8 PAN HEAD	10-12 AWG, 4mm ²	1954381-3
⚠ 4	HEX NUT	#8-32 PAN HEAD	10-12 AWG, 4mm ²	1954381-2
	NONE	#10-32 THREAD CUTTING	10-12 AWG, 4mm ²	1954381-1
	NUT	SCREW	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MOHAN 31OCT2006	 TE Connectivity	
DIMENSIONS:		CHK S. DUESTERHOEFF 01NOV2006		
mm		APVD M. STROCKENWALD 01JUN2007	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	GROUNDING CLIP ASSEMBLY SOLID WIRE	
9 PLC ±.1		APPLICATION SPEC		
2 PLC ±0.10		WEIGHT	SIZE CAGE CODE DRAWING NO	
3 PLC ±.1		CUSTOMER DRAWING	A100779C=1954381	
4 PLC ±.1		SCALE 5:1	SHEET 1 OF 1	
ANGLES ±°		REV D4		
FINISH				