

Mini Relay Latching

- Magnetically latched, ISO plug-in relay
- Two coils with set and reset function
- Pin assignment similar to ISO 7588 part 1
- Plug-in terminals

Typical applications
Active power management, disconnection of power outlets and all applications that require a quiescent current of 0A.



Contact Data	
Contact arrangement	1 form A, 1 NO
Rated voltage	12VDC
Limiting continuous current	
23°C	40A
85°C	30A
125°C	10A
Contact material	silver based
Min. recommended contact load	1A at 5VDC
Initial voltage drop, form A (NO) contact at 10A, typ./max.	50mV
Frequency of operation	6 ops./min (0.1Hz)
Operate/release time max.	typ. 1.5/1.5ms
Electrical endurance	
cyclic temperature: -40°C, +23°C, +85°C	
resistive load at 14VDC	>1x10 ⁵ cycles 40A on/off
Mechanical endurance	typ. >10 ⁶ cycles


Coil Data	
Magnetic system	bistable (two coil system)
Rated coil voltage	12VDC, pulsed
Max. coil temperature	155°C

Coil versions, bistable 2 coils					
Coil code	Rated voltage VDC	Set voltage VDC	Reset voltage VDC	Coil resistance Ω±10%	Rated coil power W
0001	12	6.9	6.9	20	7.2 ¹⁾

1) Set pulse 10ms <pulse width <100ms.
All figures are given for coil without pre-energization, at ambient temperature +23°C.

Insulation Data	
Initial dielectric strength between contact and coil	500VAC _{rms}

Max. DC load breaking capacity



Load limit curve: safe shutdown, no stationary arc/make contact.

Other Data	
EU RoHS/ELV compliance	compliant
Ambient temperature	-40°C to +125°C
Cold storage, IEC 60068-2-1	1000h, -40°C
Dry heat, IEC 60068-2-2	1000h, as per BA at 125°C
Temperature cycling, IEC 60068-2-14, Nb	10 cycles, -40/+85°C (5°C/min)
Damp heat cyclic, IEC 60068-2-30, Db, Variant 1	6 cycles, upper air temp. 55°C
Damp heat constant, IEC 60068-2-3, Ca	56 days
category of environmental protection, IEC 61810	RT I – dustproof
Degree of protection, IEC 60529	IP54 (dustproof)
Corrosive gas	
IEC 60068-2-42	10±2cm ³ /m ³ SO ₂ , 10 days
IEC 60068-2-43	1±0.3cm ³ /m ³ H ₂ S, 10 days
Vibration resistance (functional) IEC 60068-2-6 (sine sweep)	30 to 500Hz >10g ²⁾
Shock resistance (functional) IEC 60068-2-27 (half sine)	6 ms >30g ²⁾

Mini Relay Latching (Continued)

Other Data (continued)


Terminal type	plug-in, QC
Cover retention	
axial force	150 N
pull force	150 N
push force	200 N
Terminal retention	
pull force	100 N
push force	100 N
resistance to bending ³⁾	10 N
force applied to side ³⁾	10 N
torque	0.3 Nm
Weight	approx. 30g (1.1oz)

- 2) No change in the switching state >10µs. Valid for NC contacts, NO contact values significantly higher.
3) Values apply 2mm from the end of the terminals. When the force is removed, the terminals must not have moved by more than 0.3mm.

Accessories

For details see datasheet Connectors for Mini ISO Relays


Dimensions




Terminals Similar to ISO-8092-6.3 x 0.8 ECU, Sn plated 2...4 µm

Terminal Assignment

NO2D
1 form A, 1 NO



View of the terminals (bottom view)



Product code structure

Typical product code **V23141 -L 0001 -X 039**

Type V23141 Mini Relay Latching	-L	0001	-X	039
Magnetic system L Bistable				
Coil 001 12VDC				
Terminals X Plug-in, QC version				
Contact material 039 Silver based X050 Customized: resistor 560Ω				

Product code	Arrangement	Coil	Coil system	Coil suppr.	Circuit ¹⁾	Contact material	Terminals	Part number
V23141-L0001-X039	1 form A, 1 NO	12VDC	Bistable (2 coils)	Diode	NO2D	Silver based	Plug-in, QC	3-1414968-6

1) See terminal assignment diagrams.

Power Relay F7

- Pin assignment similar to ISO 7588 part 1
- Customized versions on request
 - 24VDC versions with contact gap >0.8mm
 - Integrated components (e.g. resistor, diode)
 - Customized marking/color
 - Special covers (e.g. notches, release features, brackets)

Typical applications

Cross carline up to 70A for example: ABS control, cooling fan, energy management, engine control, glow plug, heated front screen, ignition, lamps: front, rear, fog light, main switch/supply relay.



Contact Data

Contact arrangement	1 form A, 1 NO	1 form A, 1 NO	1 form A, 1 NO
Contact gap	-	-	>0.8mm
Rated voltage	12VDC	24VDC	24VDC ¹⁾
Limiting continuous current			
23°C	70A	70A	70A
85°C	50A	50A	50A
125°C	30A	30A	30A
Limiting making current ²⁾	240A	240A	240A
Limiting breaking current	70A	25A	40A
Limiting short-time current overload current, ISO 8820-3 ³⁾		1.35 x 50A, 1800s 2.00 x 50A, 5s 3.50 x 50A, 0.5s 6.00 x 50A, 0.2s	
Jump start test, ISO 16750-1		24VDC for 5min, conducting nominal current at 23°C	
Contact material		Silver based	
Min. recommended contact load ⁴⁾		1A at 5VDC	
Initial voltage drop, form A (NO) contact at 10A, typ./max.		10/300mV	
Frequency of operation at nominal load		6 ops./min (0.1Hz)	
Operate/release time typ.		7/2ms ⁵⁾	
Electrical endurance			
resistive load at 14VDC	>1x10 ⁵ ops. 70A	-	-
resistive load at 28VDC	>2x10 ⁵ ops. 50A	-	-
		>1x10 ⁵ ops. 25A	>1x10 ⁵ ops. 50A

Contact Data (continued)

- Mechanical endurance >1x10⁷ops.
- 1) Special high performance 24VDC version with contact gap >0.8mm, part number V23134-A0056-X408 (see part number table).
 - 2) The values apply to a resistive or inductive load with suitable spark suppression and at maximum 14VDC for 12VDC or 28VDC for 24VDC load voltages. For a load current duration of maximum 3s for a make/break ratio of 1:10.
 - 3) Current and time are compatible with circuit protection by a typical automotive fuse. Relay will make, carry and break the specified current.
 - 4) See chapter Diagnostics of Relays in our Application Notes or consult the internet at <http://relays.te.com/appnotes/>
 - 5) For unsuppressed relay coil. A low resistive suppression device in parallel to the relay coil increases the release time and reduces the lifetime caused by increased erosion and/or higher risk of contact tack welding.

Coil Data

Rated coil voltage	12VDC, 24VDC
--------------------	--------------


Coil versions, DC coil

Coil code	Rated voltage VDC	Operate voltage VDC	Release voltage VDC	Coil resistance ⁶⁾ Ω±10%	Rated coil power ⁶⁾ W
052	12	7.2	1.6	90	1.6
053	24	14.4	3.2	324	1.8
056	24	16.0	4.0	268	2.1
065	24	14.4	2.4	288	2.0

6) Without components in parallel.


All figures are given for coil without pre-energization, at ambient temperature +23°C.

Max. DC load breaking capacity



Load limit curve: safe shutdown, no stationary arc/make contact.
Load limit curve measured with low inductive resistors verified for 1000 switching events.

Coil operating range



Does not take into account the temperature rise due to the contact current
E = pre-energization.

Power Relay F7 (Continued)

Insulation Data

Initial dielectric strength	
between open contacts	500V _{rms}
between contact and coil	500V _{rms}
between adjacent contacts	500V _{rms}
Load dump test	
ISO 7637-1 (12VDC), test pulse 5	V _s =+86.5VDC
ISO 7637-2 (24VDC), test pulse 5	V _s =+200VDC

Other Data

EU RoHS/ELV compliance	compliant
Protection to heat and fire according UL-94	HB or better ⁷⁾
Ambient temperature	-40 to 125°C
Climatic cycling with condensation EN ISO 6988	6 cycles, storage 8/16h
Temperature cycling, IEC 60068-2-14, Nb	10 cycles, -40/+85°C (5°C/min)
Damp heat cyclic, IEC 60068-2-30, Db, Variant 1	6 cycles, upper air temp. 55°C
Damp heat constant, IEC 60068-2-3, Ca	56 days
Category of environmental protection, IEC 61810	RT1 – dustproof, RT III – sealed
Degree of protection, IEC 60529	IP54 (dustproof), IP67 (sealed)
Corrosive gas	
IEC 60068-2-42	10±2cm ³ /m ³ SO ₂ , 10 days
IEC 60068-2-43	1±0.3cm ³ /m ³ H ₂ S, 10 days
Vibration resistance (functional) IEC 60068-2-6 (sine sweep)	10 to 500Hz, min. 5g ⁸⁾
Shock resistance (functional) IEC 60068-2-27 (half sine)	6ms, min. 30g ⁸⁾
Drop test, free fall IEC 60068-2-32	1m onto concrete

Other Data (continued)

Terminal type	plug-in, QC/ PCB
Cover retention	
axial force	150N
pull force	150N
push force	150N
Terminal retention	
pull force	100N
push force	100N
resistance to bending	10N ⁸⁾
force applied to side	10N ⁸⁾
torque	0.3Nm
Weight	approx. 38g (1.3oz)
Resistance to soldering heat THT IEC 60068-2-20	260°C, 10s
Packaging unit	
plug-in:	210 pcs.
plug-in with bracket:	208 pcs.
PCB	315 pcs.

7) Refers to used materials.

8) No change in the switching state >1µs. Valid for NC contacts, NO contact values significantly higher.


8) Values apply 2mm from the end of the terminal. When the force is removed, the terminal must not have moved by more than 0.3mm.

Accessories


For details see datasheet Connectors for Maxi ISO Relays

Terminal Assignment


NO
1 form A, NO



NOR
1 form A, NO with resistor




NOD
1 form A, NO with diode



Power Relay F7 (Continued)


Dimensions

Power Relay F7 with quick connect terminals




Quick connect terminal similar to ISO 8092-1


View of the terminals (bottom view)



Power Relay F7 with PCB terminals




View of the terminals (bottom view)



PCB Layout

Bottom view on solder pins



Power Relay F7 (Continued)

Product code structure

Typical product code **V23134 -J 0 052 -D642**

Type V23134 Power Relay F	
Contact arrangement J 1 form A, 1 NO	
Cover 0 Standard 1 Bracket near terminal 30 ISO	
Coil 052 12VDC 053 24VDC 056 24VDC (contact gap >0.8mm) 065 24VDC	
Terminal/arrangement D642 Plug-in/NO Xnnn Customized (nnn: version number)	

Product code	Arrangement	Cover	Coil suppr.	Circuit ¹⁾	Coil	Cont. material	Terminals	Part number
V23134-J0052-D642	1 form A, 1 NO	Standard		NO	12VDC	Silver based	Plug-in, QC	7-1393303-3
V23134-J0052-X429			Resistor 680Ω	NOR				1-1414147-0
V23134-J0052-X439				Diode (cathode 86)				1-1414286-0
V23134-J0052-X455				Resistor 470Ω			PCB	1-1414478-0
V23134-J0052-X511				NO				3-1415001-2
V23134-J0052-X461				Resistor 560Ω			Plug-in ³⁾	1-1414469-0
V23134-J0053-D642				NO	24VDC		Plug-in, QC	9-1393303-7
V23134-J0056-X408 ²⁾				Resistor 1200Ω		NOR		
V23134-J0065-X497 ⁴⁾				NO			PCB	3-1414937-3
V23134-J1052-D642		Bracket			12VDC		Plug-in, QC	0-1393304-9
V23134-J1052-X281			Resistor 560Ω	NOR				1-1393304-0
V23134-J1053-D642				NO	24VDC			1-1393304-1
V23134-J1053-X282				Resistor 1200Ω		NOR		

1) See terminal assignment diagrams.

2) Special feature: contact gap >0.8mm.

3) Special feature: 14.5mm load terminals.

4) Packed in tray with 300 pcs. per unit.

Other types on request.

This list represents the most common types and does not show all variants covered by this datasheet.