

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

RELEASED FOR PUBLICATION
FREI FUER VERÖFFENTLICHUNG

MATED WITH:
PASSEND ZU:
HA.10

LOC
AI

DIST
-

REVISIONS
ÄNDERUNGEN

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	D1	Change Tyco electronics logo to new TE format	05.09.07	SR	ST
	D2	ECR-10-007735	18MAY10	RK	SRE

1,6

SCREW TERMINATION

3

M3x10

7,8

49.5

56.5

16.5

31

16

22.8

1

CRIMP TERMINATION

4

M3x10

7,8

49.5

56.5

16.5

31

16

22.8

2

SPRING CLAMP TERMINATION

5

M3x10

7

49.5

56.5

13

27.5

16

22.8

Notes

1

SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM

2

SUITABLE HOOD SIZE 2: SERIES HA; HD
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264

3

Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm

4

STANDARDS:
DIN EN 61984; DIN EN 60664-1

5

PACKAGING
10 SETS IN A CARTON, PRE-MOUNTED

6

SPECIAL PACKAGING
200 PIECES IN A KANN-BAN BOT

7

SPECIAL PACKAGING
100 PIECES IN A KANN-BAN BOT

CONTACT ARRANGEMENT / VIEW FROM TERMINATION SIDE

1

2

3

4

5

6

7

8

9

10

ASSEMBLING INSTRUCTION

distance for safety
contact marking max. 24 mm

22.3

8

Panel cut-out for contact insert
when used without housing

M3

43.5

10

16

24

4.5

49.5

				4		4				fixing screw	stainl.steel	blank		8	M3x10
4		4			4		4	4	4	fixing screw	steel	nickel plated	blue	7	M3x10
				1						pin insert screw		PBT	hellbeige	6	with AU-contacts
							1			cover spring strain clip		PBT	hellbeige	5	
	1					1		1		cover crimp		PBT	helbeige	4	
1		1	1	1	1				1	cover screw		PBT	hellbeige	3	
								1		pin insert spring strain clip		PBT	helbeige	2	
1	1	1	1	1		1		1	1	pin insert screw		PBT	helbeige	1	
1-2	1-0	0-9	0-8	0-4	0-6	0-5	7-1	2-3	1-1	DESCRIPTION / BENENNUNG	MATERIAL	Oberfläche	COLOR / FARBE	ITEM NO. POS.	REMARKS / BEMERKUNGEN
HA.10.Sti.S.WIE	HA.10.Sti.C-OBS	HA.10.Sti.S.KM	HA.10.Sti.S-OBS	HA.10.Sti.S-VA	HA.10.Sti.S-AU	HA.10.Sti.C-VA	HA.10.Sti.SC	HA.10.Sti.C	HA.10.Sti.S	ORDERING TEXT / BESTELLTEXT	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWELNS LETZTGÜELTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE. DIMENSIONS: DIMENSIONEN: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN ISO 8015 ISO 2768 - mH -E DIN 16901 - 140 0 PLC 1 PLC 2 PLC 3 PLC ANGLES /WINKEL FINISH /OBERFLÄECHE/FARBE	DWN Schneider 08.02.2000 CHK Schweiger 08.02.2000 APVD - PRODUCT SPEC PRODUKTSPEZ. 108-74007 APPLICATION SPEC VERARBEITUNGSSPEZ 114-74009 WEIGHT GEWICHT - CUSTOMER DRAWING /KUNDENZEICHNUNG	NAME HTS Elektrotechnik 53819 Neunkirchen, Germany SIZE A3 CAGE CODE 00779 DRAWING NO ZEICHNUNGS-NR. C-1103414 RESTRICTED TO NUR FUER -	MASSSTAB 1:1 BLATT 1 OF VON 1 REV D2	

AMP 1470-19 REV 27JUN96

This is a TRANSLATED file from
Computervision, Inc., Medusa Revision 12.2.5T