



PRODUCT SPECIFICATION

Attn: _____

SPEC. No: _____

DATE: July.05.2012

CUSTOMER PRODUCT NAME:

TDK PRODUCT NAME:

WT-1005660-12K2-A6-G

THIS SPECIFICATION IS:

TDK-EPC Corporation

Head Office Address:

1-13-1, Nihonbashi, Chuo-ku, Tokyo
103-0027, Japan

SALES

MANAGER	SALES

ENGINEERING

APPROVED	CHECKED	ISSUED

Sales Office _____

Sales Tel. _____

PRODUCT CLASSIFICATION CODE	
--------------------------------	--

REVISED HISTORY

CUSTOMER PRODUCT NAME: _____

TDK PRODUCT NAME: **WT-1005660-12K2-A6-G**


NO.	REV.	REVISED CONTENT	REVISED REASON	DATE
1	0	To establish specification		2012.07.05

CUSTOMER PRODUCT NAME:


WT-1005660-12K2-A6-G

Weight: 46.7 g (Typ.)


TOP VIEW




Lead wire pitch
position



BOTTOM VIEW



SIDE VIEW



[Remarks]

- (3) Day: 01,02,03,...31.

PRODUCT SPECIFICATION

TDK PRODUCT NAME:

WT-1005660-12K2-A6-G

SPEC. NO.

CUSTOMER PRODUCT NAME:

(2) Air coil specification


Wire Diameter: $\phi 0.08\text{mm} \times 105$ (Type2 Wire)

Coil Turns: 12TS / 1 layer

(3) Electrical Characteristics

No.	Parameter	Specification		Test Instrument
1	Inductance	Coil 0	$12.5 \mu\text{H} \pm 10\%$	HP 4284A DIGITAL LCR METER or EQUIVALENT (@100kHz 1.0 Vrms)
		Coil 1	$11.5 \mu\text{H} \pm 10\%$	
		Coil 2	$12.5 \mu\text{H} \pm 10\%$	
2	Q Value	Coil 0	70 (Min.)	HP 4284A DIGITAL LCR METER or EQUIVALENT (@100kHz 1.0 Vrms)
		Coil 1		
		Coil 2		
3	DC Resistance	Coil 0	0.08Ω (Max.) (At 25°C)	CHEN HWA 502A OHM METER or EQUIVALENT
		Coil 1		
		Coil 2		

* Remark:



(4) Temperature Characteristics

No.	Parameter	Specification
1	Operating Temperature	$-30 \sim 70^\circ\text{C}$
2	Storage Temperature	$-40 \sim 85^\circ\text{C}$

(5) Application

1. The product fit in with RoHS rule.
2. The product fit in with Halogen-Free.
3. Reflow and dip-flow soldering can not used for this product.

PRODUCT SPECIFICATION

TDK PRODUCT NAME:



WT-1005660-12K2-A6-G

SPEC. NO.

CUSTOMER PRODUCT NAME:

(6) Reliability Conditions

No.	Parameter	Conditions
1	Low Temperature (Storage)	(1) Temperature : $-40\pm 2^{\circ}\text{C}$ (2) Time : 240Hrs
2	High Temperature (Storage)	(1) Temperature : $+85\pm 2^{\circ}\text{C}$ (2) Time : 240Hrs
3	Thermal Shock	(1) Temperature : $-40\pm 5^{\circ}\text{C}$ / 30min ~ $+85\pm 5^{\circ}\text{C}$ / 30min (2) Ambient Time : 5min (3) Times : 100cycles
4	Vibration	Unpacked: (1) frequency: 10~500Hz sweep 1 octave wave / 1 min (2) Amplitude: 1.5mm (p-p) or 10G (3) Direction: X.Y.Z. direction (4) Time: X.Y.Z for 2 hours each.
5	Temperature / Humidity (Storage)	(1) Temperature : $+60\pm 2^{\circ}\text{C}$ (2) Humidity: 90% RH. (3) Time: 240Hrs
6	Temperature / Humidity (OP)	(1) Temperature : $+60\pm 2^{\circ}\text{C}$ (2) Humidity: 90% RH. (3) Time: 240Hrs (4) Current: DC 1.0A (5) Frequency: 100kHz
7	Package Drop	(1) Drop the sample package in a carton box. (2) Height : 100 cm (3) Direction : 1corner, 3 edges, 6 faces (4) Drop time : 16 times
8	ESD(HBM)	(1) Test Voltage: 1000V (2) Ambient: $25\pm 5^{\circ}\text{C}$ (3) Time: Negative / Positive each 1 time (4) Resistance: 1500 Ω (5) Capacitance: 100pF
9	ESD(MM)	(1) Test Voltage: 100V (2) Ambient: $25\pm 5^{\circ}\text{C}$ (3) Time: Negative / Positive each 1 time (4) Capacitance: 200pF



PRODUCT SPECIFICATION


TDK PRODUCT NAME:

WT-1005660-12K2-A6-G

SPEC. NO.

CUSTOMER PRODUCT NAME:

(7) Construction



(8) Material List

No.	Material Name
1	PET Tape
2	Ferrite Sheet
3	Adhesive Tape
4	Air Coil
5	Glue
6	Ink


PRODUCT SPECIFICATION

TDK PRODUCT NAME:	SPEC. NO.	CUSTOMER PRODUCT NAME:
WT-1005660-12K2-A6-G		


(9) Packing

1. To stack the the Trays onto 4 Layers:

- PET tray dimension: 326*329*11.0mm (REF.)
- 6 Pcs / per PET tray (REF.)




Total : 2x3=6pcs



Total : 6x3=18pcs

2. To put 2 Trays of products into the small Carton and affixing the out-going label on the outside .

- Small carton dimension: 331*337*33mm (REF.)
- 4 PET Trays / per small carton (PET tray of the top side is empty in the small carton)



CUST PROD ID(P): 123456789.		Customer	SAMPLE
QTY(Q): 72 (6P):TTXDF12345TWN273711000		ROHS	
TDK ITEM(1P): WT-1005660-12K2-A6-G		VDR(V):TDK	
LOT NO(1D): WL12K34567+M0001		DATE CODE(T): 1411	0001
2011/11/22		MADE IN TAIWAN	001/009
(ITEM: WT-1005660-12K2-A6-G)		M/TTXDF12345	12325A0435
		TDK	(S)
		TDK TAIWAN CORPORATION	


Out-going Label

PRODUCT SPECIFICATION


TDK PRODUCT NAME: WT-1005660-12K2-A6-G	SPEC. NO.	CUSTOMER PRODUCT NAME:
--	-----------	------------------------

3. To put 3 small carton into the Carton .

- Outer carton dimension: 347*340*124mm (REF.)
- 3 small cartons / per outer carton
- Total quantity : 54 Pcs (REF.)




3 small cartons



Outer carton

4. Packing.

- To pack the carton by scotch tape and affix out-going label (outside) on it outside.
- The Inspection data in the box , there would be a signet mark on it outside.



scotch tape

INSPECTION DATA
ENCLOSED
檢驗紀錄表在內

signet mark of Inspection data

(3S) T1W#WL12K0600200101400000360		CUSTOMER: Customer	
		CUST. PART NO(P): 12A34567-89A	
(6S) C/NO:1	BOX COUNT 001/009	TDK ITEM CODE(GP): TTXDF12345TWN	
SHIPPING MARK		P/O NO.(K): TTTT-S123456789	
ROHS			
SAMPLE		LOT NO.(IT): WL12345678	DATE: Nov.22.2011
		QTY(Q): 288	
Customer Location		TDK ITEM (IP): WT-1005660-12K2-A6-G	
MADE IN TAIWAN WL12K34567 12345A6789 		(WT-1005660-12K2-A6-G)	
		SUB P/O NO.(GK): 4500059424	
C/NO:1		TDK SPEC.	
WAREHOUSE NW 3.6 GW 4.0	(CT)	TDK TAIWAN CORPORATION	YANGMEI, TAIWAN 9

out-going label