



What can we

[Products](#) [Industries](#) [Resources](#) [About TE](#) [Support Center](#) [My Account](#)

DR-25-3/4-0-SP Product Details

[Share](#) [Print](#) [Email](#)


DR-25-3/4-0-SP

TE Internal Number: 5039254029

[Active](#)

Heat Shrink Tubing

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = DR-25
- Product Source = U.K., U.S.
- Flexible
- Medium Wall Style

[View all Features](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Thermofit DR-25 Tubing Elastomeric, Fluid Resistant...](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Material = Elastomer
- Color = Black

Electrical Characteristics:

- Product Source = U.K., U.S.
- [Expanded ID, Min. \(mm \[in\]\)](#) = 19.00 [0.748]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 9.50 [0.374]
- Product Use = Cables, Harnesses

Body Features:

- [Product Name](#) = DR-25
- Pliancy = Flexible
- [Wall Style](#) = Medium
- [Wall Type](#) = Single
- [Shrink Ratio](#) = 2:1
- Fluid Type = Aviation Fuel, Brake Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Water
- Resistant To = Abrasion, Fluids, Mechanical Damage
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 1.44 [0.057]

Housing Features:

- Material Systems = Yes
- [Material Systems Code](#) = 25

Environmental:

- Fluid Resistance = Splash Protection
- [Operating Temperature \(°C\)](#) = -75 - +150

Conditions for Usage:

- Full Recovery Temperature (°C) = 175
- Shrink Temperature, Min. (°C) = 150
- High Temperature Compatible = Yes

Operation/Application:

- Application = Aerospace, Harness Protection, Insulation and Protection, Military
- Emission Free = No

Packaging Features:

- Packaging Method = Spool

Other:

- Brand = Raychem