



FIG. 1



FIG. 2



FIG. 3
(8 POS ONLY)



.210/.180
(STD .125 PC LEAD)
.265/.235
(LONG .180 PC LEAD)



P.C.B. HOLE LAYOUT
TOLERANCE ±.003

1 MATERIALS:
INSULATOR: POLYESTER, UL RATED 94V-0
CONTACT:
800 & 1800 SERIES CONTACT: 4 BEAM, COPPER ALLOY, MACHINED (PREMIUM VERSION) OR FORMED (ECONOMY VERSION, WITH SUFFIX -ES OR -ESL).
800 SERIES HIGH RETENTION CONTACT: 4 BEAM, COPPER ALLOY, MACHINED.
1000 SERIES CONTACT: 6 BEAM, COPPER ALLOY, MACHINED (LOW INSERTION FORCE SERIES)
SLEEVE- ALL SERIES: COPPER ALLOY, FORMED

2 ELECTRICAL:
CONTACT RESISTANCE: 10 MILLIOHMS MAX
CONTACT RATING: 3 AMPS
CAPACITANCE: 1.0 pF PER MIL-STD-202, METHOD 305
INSULATION RESISTANCE: 5000 OHMS MIN @ 500 VDC PER MIL-STD-1344, METHOD 3003.1
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS (RMS) PER MIL-STD-1344, METHOD 3001.1

3 MECHANICAL:
AFTER INSERTION FORCE: 37 GRAMS AVG (6 BEAM CONTACT) 134 GRAMS AVG (4 BEAM PREMIUM) 179 GRAMS AVG (4 BEAM ECONOMY) AND 334 GRAMS AVG (HIGH RETENTION)
AFTER WITHDRAWAL FORCE: 15 GRAMS AVG (6 BEAM CONTACT) 63 GRAMS AVG (4 BEAM PREMIUM OR ECONOMY) AND 245 GRAMS AVG (HIGH RETENTION)

4 ENVIRONMENTAL:
OPERATING TEMPERATURE: -55°C TO -105°C

5 PLATING: 25μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 5μ" MIN GOLD OVER 50μ" MIN NICKEL SLEEVE.

6 PLATING: 25μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN TIN-LEAD OVER 50μ" MIN COPPER SLEEVE.

7 PLATING: 80μ" MIN TIN-LEAD OVER 75μ" MIN COPPER CONTACT WITH 180μ" MIN TIN-LEAD OVER 75μ" MIN NICKEL SLEEVE.

8 PLATING: 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL CONTACT WITH 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL SLEEVE.

9 PLATING: 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN TIN-LEAD OVER 50μ" MIN COPPER SLEEVE.

10 PLATING: 7.5μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN TIN-LEAD OVER 50μ" MIN COPPER SLEEVE.

11 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.

12 806-AGXXD-XXX SERIES IS SUPERSEDED BY 506-AGXXD-XXX SERIES (REFER TO CUSTOMER DRAWING 1437532-2)

13 PLATING: 25μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN MATTE TIN OVER 50μ" MIN COPPER SLEEVE.

14 PLATING: 80μ" MIN MATTE TIN OVER 75μ" MIN COPPER CONTACT WITH 180μ" MIN MATTE TIN OVER 75μ" MIN NICKEL SLEEVE.

15 PLATING: 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN MATTE TIN OVER 50μ" MIN COPPER SLEEVE.

16 PLATING: 7.5μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN MATTE TIN OVER 50μ" MIN COPPER SLEEVE.

17 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8 XX - AX XXX D - XXX - LF
800 SERIES POSITIONS
LF = LEAD FREE
BLANK = MACHINED CONTACT
ES = FORMED CONTACT, GOLD PLATE, NOTE 1
ESL = FORMED CONTACT, LOW GOLD PLATE, 5μIN MAX
D = PC TAIL STANDARD
LSG STYLE AND TAIL CONFIGURATION
AG = INSULATOR
AR = INSULATOR WITH RAILS
(ALMOST RUN THE LENGTH UNDER THE INSULATOR INSIDE THE CONTACT ROWS, .075 REF HIGH & .045 REF WIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN R BROWN 06MAY04	Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: INCHES		CHK K WRIGHT 06MAY04	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K WRIGHT 06MAY04	NAME
0 PLC ± -	1 PLC ± -	PRODUCT SPEC	DIP SOCKET, 800 SERIES
2 PLC ± -	3 PLC ± .005	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO
4 PLC ± -	ANGLES ± -	WEIGHT	A1 00779 ©=1437539-2
MATERIAL	FINISH	CUSTOMER DRAWING	RESTRICTED TO
		SCALE 1:1	SHEET 1 OF 4
		REV A3	

800 SERIES MACHINED PREMIUM CONTACT LEAD FREE PART NUMBER TABLE

Table with columns: COMMENTS, PLATING, C, B, A, FIG, AUGAT PART NO., TE PART NO. and rows listing various part numbers and specifications.

800 SERIES MACHINED PREMIUM CONTACT PART NUMBER TABLE

Table with columns: COMMENTS, PLATING, C, B, A, FIG, AUGAT PART NO., TE PART NO. and rows listing various part numbers and specifications.

800 SERIES MACHINED PREMIUM CONTACT PART NUMBER TABLE

Table with columns: COMMENTS, PLATING, C, B, A, FIG, AUGAT PART NO., TE PART NO. and rows listing various part numbers and specifications.

Technical drawing information including Tyco Electronics logo, product name (DIP SOCKET, 800 SERIES), dimensions, tolerances, and drawing number (1437539-2).

800 SERIES STAMPED ECONOMY CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	W/RAILS	13	.595/.605	.700	2.400	2	848-AR11D-ES-LF	8-1437540-0
OBSOLETE	W/RAILS	14					840-AR12D-ES-LF	6-6447099-8
OBSOLETE	W/RAILS	15					840-AR11D-ESL-LF	7-1437540-2
OBSOLETE	W/RAILS	13	.595/.605	.700	2.000	2	840-AR11D-ES-LF	7-1437540-1
	.180 PC LEAD	15					840-AG44D-ESL-LF	7-1437540-0
OBSOLETE	W/RAILS	15					832-AR11D-ESL-LF	0-6437540-9
OBSOLETE	W/RAILS	13					832-AR11D-ES-LF	0-6437540-8
	.180 PC LEAD	13	.595/.605	.700	1.600	2	832-AG44D-ES-LF	0-6437540-7
	.180 PC LEAD	14					832-AG43D-ES-LF	0-6437540-6
OBSOLETE	.180 PC LEAD W/RAILS	15					828-AR44D-ESL-LF	9-6437539-8
OBSOLETE	W/RAILS	14					828-AR12D-ES-LF	6-6447099-7
OBSOLETE	W/RAILS	13	.595/.605	.700	1.400	1	828-AR11D-ES-LF	9-6437539-6
	.180 PC LEAD	13					828-AG44D-ES-LF	9-6437539-5
OBSOLETE	.180 PC LEAD W/RAILS	15	.295/.305	.400	1.200	1	824-AR47D-ESL-LF	8-6437533-3
OBSOLETE	W/RAILS	13	.295/.305	.400	1.200	1	824-AR31D-ES-LF	8-6437539-7
OBSOLETE	W/RAILS	14	.595/.605	.700	1.200	1	824-AR12D-ES-LF	6-6447099-6
	.180 PC LEAD	15	.595/.605	.700	1.200	1	824-AG44D-ESL-LF	8-6437539-3
	.180 PC LEAD	13	.295/.305	.400	1.100	1	822-AG44D-ES-LF	6-6437539-5
	.180 PC LEAD	13	.295/.305	.400	1.000	1	820-AR11D-ESL-LF	5-6437539-8
OBSOLETE	W/RAILS	15					820-AR11D-ES-LF	5-6437539-7
OBSOLETE	W/RAILS	13					816-AR11D-ESL-LF	3-6437539-5
OBSOLETE	W/RAILS	15					816-AR11D-ES-LF	3-6437539-4
	.180 PC LEAD	13	.295/.305	.400	.800	1	816-AG44D-ESL-LF	3-6437539-2
OBSOLETE	W/RAILS	13	.295/.305	.400	.700	1	814-AR11D-ES-LF	2-6437539-2
OBSOLETE	W/RAILS	13					808-AR11D-ES-LF	1-6437539-0
	.180 PC LEAD	14	.295/.305	.400	.400	1	808-AG43D-ES-LF	6437537-6
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY CONTACT PART NUMBER TABLE

17	OBSOLETE	.180 PC LEAD W/RAILS	9	.295/.305	.400	1.200	1	824-AR47D-ESL	8-1437533-3
SUPERSEDED	.180 PC LEAD W/RAILS S/B 8-1437539-3	9	.595/.605	.700	1.200	1	824-AR44D-ESL	8-1437533-2	
17	OBSOLETE	W/RAILS	9	.295/.305	.400	1.200	1	824-AR31D-ESL	3-1437540-9
OBSOLETE	W/RAILS	6					824-AR31D-ES	8-1437539-7	
OBSOLETE	W/RAILS	7					824-AR12D-ES	6-1447099-6	
OBSOLETE	W/RAILS	9	.595/.605	.700	1.200	1	824-AR11D-ESL	8-1437539-6	
OBSOLETE	W/RAILS	6					824-AR11D-ES	8-1437539-5	
OBSOLETE	-	9	.395/.405	.500	1.200	1	824-AG66D-ESL	8-1437539-4	
	-	5					824-AG65D-ES	0-1571180-1	
17	OBSOLETE	.180 PC LEAD	9	.595/.605	.700	1.200	1	824-AG44D-ESL	8-1437539-3
	-	7					824-AG32D-ES	8-1437539-1	
	-	9					824-AG31D-ESL	7-1437539-7	
	-	6	.295/.305	.400	1.200	1	824-AG31D-ES	7-1437539-6	
	-	8					824-AG30D-ESL	7-1437539-4	
	-	5					824-AG30D-ES	7-1437539-3	
	-	7					824-AG12D-ES	7-1437539-2	
	-	9	.595/.605	.700	1.200	1	824-AG11D-ESL	7-1437539-0	
	-	6					824-AG11D-ES	6-1437539-9	
	-	5					824-AG10D-ES	6-1437539-7	
OBSOLETE	.180 PC LEAD	6					822-AG44D-ES	6-1437539-5	
	-	7					822-AG12D-ES	6-1437539-4	
	-	9	.295/.305	.400	1.100	1	822-AG11D-ESL	6-1437539-3	
	-	6					822-AG11D-ES	6-1437539-2	
17	OBSOLETE	-	5				822-AG10D-ES	6-1437539-0	
SUPERSEDED	.180 PC LEAD W/RAILS S/B 7-1437537-4	9					820-AR44D-ESL	7-1437533-1	
17	OBSOLETE	W/RAILS	9				820-AR11D-ESL	5-1437539-8	
OBSOLETE	W/RAILS	6	.295/.305	.400	1.000	1	820-AR11D-ES	5-1437539-7	
	.180 PC LEAD S/B 7-1437537-4	9					820-AG44D-ES	7-1437533-0	
	-	7					820-AG12D-ES	5-1437539-6	
	-	9					820-AG11D-ESL	5-1437539-3	
	-	6					820-AG11D-ES	5-1437539-2	
	-	5					820-AG10D-ES	5-1437539-0	
	.180 PC LEAD W/RAILS S/B 4-1437539-9	9					818-AR44D-ESL	6-1437533-4	
OBSOLETE	W/RAILS	9					818-AR11D-ESL	4-1437539-8	
OBSOLETE	W/RAILS	6					818-AR11D-ES	4-1437539-7	
	.180 PC LEAD S/B 6-1437537-1	9	.295/.305	.400	.900	1	818-AG44D-ESL	6-1437533-3	
	-	7					818-AG12D-ES	4-1437539-6	
	-	9					818-AG11D-ESL	4-1437539-4	
	-	6					818-AG11D-ES	4-1437539-3	
	-	5					818-AG10D-ES	4-1437539-1	
OBSOLETE	W/RAILS	9					816-AR11D-ESL	3-1437539-5	
OBSOLETE	W/RAILS	6					816-AR11D-ES	3-1437539-4	
	.180 PC LEAD	5	.295/.305	.400	.800	1	816-AG45D-ES	3-1437539-3	
OBSOLETE	.180 PC LEAD	9					816-AG44D-ESL	3-1437539-2	
	-	7					816-AG12D-ES	3-1437539-1	
	-	9					816-AG11D-ESL	2-1437539-9	
	-	6					816-AG11D-ES	2-1437539-8	
	-	5					816-AG10D-ES	2-1437539-6	
17	OBSOLETE	-	7				814-AR44D-ESL	5-1437533-3	
OBSOLETE	W/RAILS	9					814-AR11D-ESL	2-1437539-3	
OBSOLETE	W/RAILS	6					814-AR11D-ES	2-1437539-2	
	.180 PC LEAD	9	.595/.605	.700	2.000	2	814-AG45D-ES	2-1437539-1	
	-	7					814-AG44D-ESL	4-1437540-5	
	-	9					814-AG12D-ES	2-1437539-0	
	-	6					814-AG11D-ESL	1-1437539-7	
	-	5					814-AG11D-ES	1-1437539-6	
OBSOLETE	-	7	.595/.605	.700	1.800	2	836-AG12D-ES	1-1437540-2	
	-	9					836-AG11D-ESL	1-1437540-1	
	-	6					836-AG11D-ES	1-1437540-0	
OBSOLETE	W/RAILS	9					832-AR11D-ESL	0-1437540-9	
OBSOLETE	W/RAILS	6					832-AR11D-ES	0-1437540-8	
	.180 PC LEAD S/B 1437540-1	8					832-AG45D-ESL	6-1437538-0	
	.180 PC LEAD S/B 1437540-7	9	.595/.605	.700	1.600	2	832-AG44D-ESL	9-1437533-5	
OBSOLETE	.180 PC LEAD	6					832-AG44D-ES	0-1437540-7	
	-	7					832-AG43D-ES	0-1437540-6	
	-	9					832-AG12D-ES	0-1437540-5	
	-	6					832-AG11D-ESL	0-1437540-3	
	-	5					832-AG11D-ES	0-1437540-2	
OBSOLETE	.180 PC LEAD W/RAILS	9					832-AG10D-ES	0-1437540-1	
OBSOLETE	W/RAILS	7					828-AR44D-ESL	9-1437539-8	
OBSOLETE	W/RAILS	9					828-AR12D-ES	6-1447099-7	
OBSOLETE	W/RAILS	6					828-AR11D-ESL	9-1437539-7	
OBSOLETE	W/RAILS	9					828-AR11D-ES	9-1437539-6	
17	OBSOLETE	.180 PC LEAD	6	.595/.605	.700	1.400	1	828-AG44D-ES	9-1437539-5
	-	7					828-AG12D-ES	9-1437539-4	
	-	9					828-AG11D-ESL	9-1437539-2	
	-	6					828-AG11D-ES	9-1437539-1	
	-	5					828-AG10D-ES	8-1437539-9	
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.	

800 SERIES STAMPED ECONOMY CONTACT PART NUMBER TABLE

17	OBSOLETE	-	7				864-AG12D-ES	5-1437538-3	
	-	9	.895/.905	1.000	3.200	2	864-AG11D-ESL	5-1437538-0	
	-	6					864-AG11D-ES	4-1437538-9	
17	OBSOLETE	-	5				864-AG10D-ES	3-1437540-2	
OBSOLETE	W/RAILS	9					848-AR11D-ESL	6-1437540-2	
OBSOLETE	W/RAILS	6					848-AR11D-ES	3-1437540-0	
	-	7	.595/.605	.700	2.400	2	848-AG12D-ES	2-1437540-8	
	-	9					848-AG11D-ESL	4-1437538-2	
17	OBSOLETE	-	6				848-AG11D-ES	2-1437540-6	
	-	9	.595/.605	.700	2.100	2	848-AG10D-ES	2-1437540-5	
	-	6					842-AG11D-ESL	2-1437540-4	
	.180 PC LEAD W/RAILS S/B 2-1437540-0	9					842-AG11D-ES	2-1437540-3	
17	OBSOLETE	W/RAILS	7				840-AR44D-ESL	0-1437534-7	
OBSOLETE	W/RAILS	9					840-AR12D-ES	6-1447099-8	
OBSOLETE	W/RAILS	6					840-AR11D-ESL	2-1437540-2	
	.180 PC LEAD	9	.595/.605	.700	2.000	2	840-AR11D-ES	2-1437540-1	
	-	7					840-AG44D-ESL	2-1437540-0	
	-	9					840-AG12D-ES	1-1437540-9	
	-	6					840-AG11D-ESL	1-1437540-7	
	-	5					840-AG11D-ES	1-1437540-6	
17	OBSOLETE	-	7				840-AG10D-ES	1-1437540-4	
	-	9	.595/.605	.700	1.800	2	836-AG12D-ES	1-1437540-2	
	-	6					836-AG11D-ESL	1-1437540-1	
	-	9					836-AG11D-ES	1-1437540-0	
OBSOLETE	W/RAILS	9					832-AR11D-ESL	0-1437540-9	
OBSOLETE	W/RAILS	6					832-AR11D-ES	0-1437540-8	
	.180 PC LEAD S/B 1437540-1	8					832-AG45D-ESL	6-1437538-0	
	.180 PC LEAD S/B 1437540-7	9	.595/.605	.700	1.600	2	832-AG44D-ESL	9-1437533-5	
OBSOLETE	.180 PC LEAD	6					832-AG44D-ES	0-1437540-7	
	-	7					832-AG43D-ES	0-1437540-6	
	-	9					832-AG12D-ES	0-1437540-5	
	-	6					832-AG11D-ESL	0-1437540-3	
	-	5					832-AG11D-ES	0-1437540-2	
OBSOLETE	.180 PC LEAD W/RAILS	9					832-AG10D-ES	0-1437540-1	
OBSOLETE	W/RAILS	7					828-AR44D-ESL	9-1437539-8	
OBSOLETE	W/RAILS	9					828-AR12D-ES	6-1447099-7	
OBSOLETE	W/RAILS	6					828-AR11D-ESL	9-1437539-7	
17	OBSOLETE	.180 PC LEAD	6	.595/.605	.700	1.400	1	828-AR11D-ES	9-1437539-6
	-	7					828-AG44D-ES	9-1437539-5	
	-	9					828-AG12D-ES	9-1437539-4	
	-	6					828-AG11D-ESL	9-1437539-2	
	-	5					828-AG11D-ES	9-1437539-1	
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN R BROWN 06MAY04	APPROVED: K. WRIGHT 06MAY04	NAME: Tyco Electronics	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
1 PLC ± .005	2 PLC ± .005	3 PLC ± .005	4 PLC ± .005	ANGLES ± .005	
MATERIAL: -	FINISH: -	WEIGHT: -	SIZE: A1	CAGE CODE: -	DRAWING NO: 1437539-

1000 SERIES MACHINED PREMIUM CONTACT, LOW INSERTION FORCE PART NUMBER TABLE

COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.
S/B 4-1437538-8	6	.895/.905	1.000	3.200	2	1064-AG11D	2-1437529-4
S/B 3-1437540-1	5	.895/.905	1.000	3.200	2	1064-AG10D	2-1437529-3
S/B 3-1437538-0	6	.595/.605	.700	2.000	2	1040-AG11D	2-1437529-2
S/B 2-1437538-2	6	.595/.605	.700	1.600	2	1032-AG11D	2-1437529-1
S/B 1437538-4	6	.595/.605	.700	1.400	1	1028-AG11D	1-1437529-9
S/B 8-1437537-9	6	.295/.305	.400	1.200	1	1024-AG31D	1-1437529-8
S/B 8-1437537-2	6	.595/.605	.700	1.200	1	1024-AG11D	1-1437529-6
S/B 8-1437537-1	5	.595/.605	.700	1.200	1	1024-AG10D	1-1437529-5
S/B 6-1437537-6	6	.295/.305	.400	1.000	1	1020-AG11D	1-1437529-4
S/B 6-1437537-4	5	.295/.305	.400	1.000	1	1020-AG10D	1-1437529-3
S/B 5-1437537-7	6	.295/.305	.400	.900	1	1018-AG11D	1-1437529-2
S/B 5-1437537-6	5	.295/.305	.400	.900	1	1018-AG10D	1-1437529-1
S/B 4-1437537-0	6	.295/.305	.400	.800	1	1016-AG11D	1-1437529-0
S/B 3-1437537-7	5	.295/.305	.400	.800	1	1016-AG10D	0-1437529-9
S/B 2-1437537-4	6	.295/.305	.400	.700	1	1014-AG11D	0-1437529-7
S/B 2-1437537-1	5	.295/.305	.400	.700	1	1014-AG10D	0-1437529-6
S/B 1437537-8	6	.295/.305	.400	.400	3	1008-AG11D	0-1437529-5
S/B 1437537-5	5	.295/.305	.400	.400	3	1008-AG10D	0-1437529-4

1800 SERIES MACHINED PREMIUM CONTACT, LOW GOLD PART NUMBER TABLE

	S/B 5-1437538-0	10	.895/.905	1.000	3.200	2	1864-AG111D	5-1437529-1
	S/B 6-1437540-2 W/RAILS	10	.595/.605	.700	2.400	2	1848-AR111D	5-1437529-0
	S/B 4-1437538-2	10	.595/.605	.700	2.100	2	1848-AG111D	4-1437529-9
	S/B 2-1437540-4	10	.595/.605	.700	2.100	2	1842-AG111D	4-1437529-8
	S/B 2-1437540-2 W/RAILS	10	.595/.605	.700	2.000	2	1840-AR111D	4-1437529-7
	S/B 1-1437540-7	10	.595/.605	.700	2.000	2	1840-AG111D	4-1437529-6
	S/B 1437540-3	10	.595/.605	.700	1.600	2	1832-AG111D	4-1437529-5
	S/B 9-1437539-7 W/RAILS	10	.595/.605	.700	1.400	1	1828-AR111D	4-1437529-4
	S/B 9-1437539-2	10	.595/.605	.700	1.400	1	1828-AG111D	4-1437529-3
	S/B 3-1437540-9 W/RAILS	10	.295/.305	.400	1.200	1	1824-AR131D	4-1437529-2
OBSOLETE	S/B 8-1437539-6 W/RAILS	10	.595/.605	.700	1.200	1	1824-AR111D	4-1437529-1
OBSOLETE	S/B 8-1437539-4	10	.395/.405	.500	1.200	1	1824-AG141D	4-1437529-0
	S/B 7-1437539-7	10	.295/.305	.400	1.200	1	1824-AG131D	3-1437529-9
	S/B 7-1437539-0	10	.595/.605	.700	1.200	1	1824-AG111D	3-1437529-8
	S/B 6-1437539-3	10	.395/.405	.500	1.100	1	1822-AG111D	3-1437529-7
	S/B 5-1437539-8 W/RAILS	10	.295/.305	.400	1.000	1	1820-AR111D	3-1437529-6
SUPERSEDED	S/B 5-1437539-3	10	.295/.305	.400	1.000	1	1820-AG111D	3-1437529-5
	S/B 4-1437539-8 W/RAILS	10	.295/.305	.400	.900	1	1818-AR111D	3-1437529-5
	S/B 4-1437539-4	10	.295/.305	.400	.900	1	1818-AG111D	3-1437529-3
OBSOLETE	S/B 3-1437539-5 W/RAILS	10	.295/.305	.400	.800	1	1816-AR111D	3-1437529-2
	S/B 2-1437539-9	10	.295/.305	.400	.800	1	1816-AG111D	3-1437529-1
	S/B 2-1437539-3 W/RAILS	10	.295/.305	.400	.700	1	1814-AR111D	3-1437529-0
	S/B 1-1437539-7	10	.295/.305	.400	.700	1	1814-AG111D	2-1437529-9
	S/B 1-1437539-1 W/RAILS	10	.295/.305	.400	.400	3	1808-AR111D	2-1437529-6
	S/B 1437539-6	10	.295/.305	.400	.400	3	1808-AG111D	2-1437529-5
OBSOLETE	S/B 1437539-8	10	.295/.305	.400	.300		1806-AG111D	0-1437535-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN R BROWN 06MAY04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK K WRIGHT 06MAY04	Tyco Electronics	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K WRIGHT 06MAY04	NAME	
0 PLC ± .005		PRODUCT SPEC		
1 PLC ± .005		APPLICATION SPEC		
2 PLC ± .005		SIZE CASE CODE DRAWING NO		
3 PLC ± .005		WEIGHT		
4 PLC ± .005		A1 00779 1437539-2		
ANGLES ± .005		CUSTOMER DRAWING		
MATERIAL		SCALE 1:1 SHEET 4 OF 4 REV A3		