


COIL: @ +25 °C  
 RESISTANCE 700 OHMS ± 10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 13.5 VDC  
 MUST RELEASE 8.0 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 100 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX  
RELEASE 4 MS MAX  
CONTACT BOUNCE 2.0 MS MAX  
ALL OTHER REQUIREMENTS TO M39016/6-209L

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
2 AMPS 28 VDC RESISTIVE 100,000  
OPERATIONS

DR. R.B. 5/3/96 CK. 5/3/96 JRB



CUST. QPL  
 CUST. NO. M39016/6-209L

TYPE "HFW" RELAY

HFW1201K46