


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A1	REVISED PER ECO-09-000408	15JAN09	HMR	MW		

Specifications

Rating, UL/CSA	3A @ 125 VAC
Contact resistance, initial	100 milliohms max
Insulation resistance	100 megohms min. 500 VDC, 1 minute hold
Dielectric withstanding voltage, initial	1,000 VAC
Life expectancy	6,000 cycles min on resistive load of 3A @ 125VAC
Operating force	50 grams force max.
Release force	8 grams force min
Pretravel (PT)	3 mm. max.
Overtravel (OT)	.6 mm min.
Free position (FP)	10.1 mm max.
Operating position (OP)	7.9 +/- .8 mm.
Movement differential (MD)	.8 mm max



VIEW SHOWN WITH LEVER REMOVED



SUPERSEDED BY 1-1825043-5

Finish	Material	Item Name	Item No
	PBT, 30% GF, UL94 V-0, black	Housing	1
	PBT, 30% GF, UL94 V-0, black	Cover	2
	PA 6/6, 30% GF, UL94 V-0, black	Button	3
contact area: gold over nickel solder area: tin/lead over nickel	Brass	Terminals (3)	4
none	Beryllium copper	Spring contact	5
none	Stainless steel	Lever	6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 23OCT2001	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		CHK M ZITTO 22OCT2001	NAME M ZITTO 22OCT2001	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M ZITTO 22OCT2001	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		
1 PLC ± -		WEIGHT		
2 PLC ± 0.40		SCALE 6:1		
3 PLC ± -		SHEET 1 OF 1		
4 PLC ± -		REV A1		
ANGLES ± -		CUSTOMER DRAWING		
FINISH		SIZE A2 CAGE CODE 00779 C=147991		
MATERIAL		RESTRICTED TO		