

4

3

2

1

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				K	REDRAWN PER AF-6644	4/16/90	PF/JR

1.046

.470 DIA

.323 DIA ±.005

.384

1 CONTINUOUS STRIP ON REELS

.030±.001

.155

.186

.200  
.175

.240  
.215

.245  
.220

SECTION A-A SECTION B-B

F or 0	.210	.220	F	.155	.087	14
					.081	16
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

.000080 MIN TIN PL PER MIL-T-10727	.120-.180 DIA	16-14 AWG	42752-2
			42752-1
FINISH	INSULATION RANGE	WIRE SIZE	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± -	DR 4/16/90 P FORTNEY	<b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 4/16/90 JR RUTH			
MATERIAL #2 HARD BRASS	APPD 4/16/90 G YETTER	RING		
FINISH SEE TABLE	APPD 4/15/90 R KUZO			
	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
	APPLICATION SPEC	B	00779	42752
	WEIGHT	SCALE	4:1	SHEET
				1 OF 1

AMP 1470-15 REV 11-89

CUSTOMER DRAWING