

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00	F	0G3C-0856-04	07OCT05	RB JG

.006 MAX LOOSE PIECE CUT-OFF BOTH ENDS

.195 MIN (CRIMP AREA)

A B

.145 MAX (5)

.060 ±.002 .100 .090 .170 (CONTACT AREA)

.025 ±.001

.025 +.005 -.002

.085 (4)

.806 +.008 -.013

.025 +.003 -.000

.075 +.010 -.000

.062 +.010 -.000

SECTION A-A  
 ROTATED 90° CW  
 INSULATION RANGE .054 MAX

SECTION B-B  
 ROTATED 90° CW  
 WIRE RANGE #22-#26

1 .000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL ENTIRE CONTACT

2 .000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

3 .000030 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

4 POINT OF MEASUREMENT FOR PLATING THICKNESS

5 GOLD PLATING NOT REQUIRED IN THIS AREA

6 .000100-.000200 BRIGHT TIN OVER .000030 NICKEL ENTIRE CONTACT.

7 .000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

8 .000030 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

9 .000100-.000200 MATTE TIN OVER .000030 NICKEL ENTIRE CONTACT.

10 .000015 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

11 .000030 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

11	5-104505-7	5-104505-6
10	5-104505-5	5-104505-4
9	5-104505-3	5-104505-2
8	1-104505-3	1-104505-2
7	1-104505-1	1-104505-0
6	104505-9	104505-8
3	104505-7	104505-6
2	104505-5	104505-4
1	104505-3	104505-2
FINISH	LOOSE PIECE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	D KEITZER	12-14-88	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: INCHES		CHK	S. SHUEY	12-15-88			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	C.SINISI	12-16-88			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH SEE TABLE		PRODUCT SPEC	-				
MATERIAL PHOS BRONZE		APPLICATION SPEC	-		NAME	PIN CONTACT, AMPMODU, MTE	
WEIGHT -		SIZE	A2	CAGE CODE	00779	DRAWING NO	C=104505
CUSTOMER DRAWING		SCALE	10:1	SHEET	1 OF 1	RESTRICTED TO	-
		REV	F				

AMP 1471-9 REV 31MAR2000

104505

B

A