





Telecom-, Signal and RF Relays

Disclaimer

While Tyco Electronics has made every reasonable effort to ensure the accuracy of the information in this datasheet, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties (and all express warranties, except as otherwise stated in this datasheet) regarding the information contained herein, including but not limited to any implied warranties or merchantability or fitness for a particular purpose. It is recommended that you test any new or replacement product before incorporating into a system.

The dimensions in this datasheet are for reference purpose only and are subject to change without notice. Specifications are subject to change without notice.

Index

Dimensions	4
Coil Operating Range	5
Coil Data and Ordering Information	6
Contact Data	7
Insulation	8
General Data	8
Packing	9

2 pole telecom/signal relay Through Hole Type (THT) Non-polarized. non-latching 1 coil


ROHS compliant (Directive 2002/95/EC) as per product date code 0416.

Features

- · Telecom/signal relay (dry circuit, test access, ringing)
- Slim line 20 x 10 mm, 0.795 x 0.393 inch
- · Switching current 2 A
- 2 changeover contacts (2 form C / DPDT)
- · Bifurcated contacts
- Meets FCC Part 68 and ITU-T K20

Typical applications

- Communications equipment Linecard application – analog, ISDN, xDSL, PABX Voice over IP
- · Office and business equipment
- Measurement and control equipment
- Consumer electronics
 Set top boxes, HiFi
- · Medical equipment
- · Automotive Equipment




AXICOMTelecom-, Signal and RF Relays

MT2 Relay

Dimensions Dimensions in mm


	THT	
	mm	inch
L	20.2 + 0.05/-0.20	0.795 + 0.002/-0.0080
W	10.0 + 0.05/-0.20	0.393 + 0.002/-0.0080
Н	11.0 + 0.20/-0.20	0.433 + 0.008/-0.0080
Т	3.20 ± 0.30	0.126 ± 0.011
T1	N/A	N/A
T2	7.62 ± 0.15	0.300 ± 0.005
Tw	0.55	0.021
S	0.50	0.020

THT Version



Mounting hole layout


View onto the component side of the PCB (top view)




Terminal assignment


Relay - top view


Non-latching 1 coil not energized condition





Coil Operating Range











- U_{nom} = Nominal coil voltage
- U_{max.} = Upper limit of the operative range of the coil voltage (limiting voltage) when coils are continously energized
- U_{op. min.} = Lower limit of the operative range of the coil voltage (reliable operate voltage)
- U_{rel. min.} = Lower limit of the operative range of the coil voltage (reliable release voltage)

Telecom-, Signal and RF Relays

MT2 Relay

Coil Data (values at 23 °C) **Ordering Information** Nominal Operate/set voltage range Release/ Coil Coil Relay Tyco part voltage reset voltage power Resistance code number $U_{\text{nom}} \\$ Minimum Minimum Maximum voltage U_{min} voltage U_{max} Vdc Vdc Vdc Vdc mW Ω / \pm 10 % High Sensitive Version (150 mW) non-latching 1 coil 3 2.10 8.1 0.30 150 60 C 93400 1-1462001-2 3.3 2.30 8.8 0.33 150 72 C 93407 1-1462001-3 4.5 3.20 12.2 0.45 150 136 C 93406 2-1462000-2 5 3.60 13.5 0.50 150 168 C93401 1462000-1 6 4.30 16.2 0.60 150 240 C 93427 5-1462000-6 9 6.40 24.3 0.90 150 544 C 93405 2-1462000-0 12 8.60 32.4 1.20 150 968 C 93402 1462000-7 24 17.10 64.8 2.40 150 3872 C 93403 1-1462000-3 48 129.6 34.10 4.80 150 15468 C 93404 1-1462000-8 Sensitive Version (200 mW) non-latching 1 coil 3 2.00 7.0 0.30 200 45 1-1462001-1 C 93414 4.5 3-1462000-0 2.90 10.5 0.45 200 101 C 93415 5 3.30 11.6 0.50 200 125 C 93416 3-1462000-1 6 3.90 14.0 0.60 200 180 C 93428 5-1462000-7 9 5.90 405 21.0 0.90 200 C93417 3-1462000-6 12 7.80 28.0 1.20 200 720 C 93418 3-1462000-7 24 15.60 59.9 2.40 200 2880 C 93419 4-1462000-1 48 31.20 112.0 4.80 200 11520 C 93420 4-1462000-5 Sensitive Version (300 mW) non-latching 1 coil 4.5 3.10 8.9 0.45 300 73 C 93433 6-1462000-6 5 3.40 9.9 0.50 300 90 C 93434 6-1462000-8 12 2-1462000-6 8.25 23.6 1.20 300 515 C 93412 24 16.50 47.3 2.40 300 2060 C 93435 7-1462000-0 48 300 7-1462000-2 32.50 54.6 4.80 8240 C 93436 Standard Version (400 mW) non-latching 1 coil 4.5 2.90 8.9 0.45 400 50 C 93421 4-1462000-7 5 3.30 9.9 0.50 400 63 C 93422 4-1462000-8 6 3.90 11.8 0.60 400 90 C 93429 5-1462000-8 9 5.90 17.7 0.90 400 203 C 93423 5-1462000-0 12 7.80 23.6 1.20 400 360 C 93424 5-1462000-1 24 15.60 47.3 2.40 400 1440 C 93425 5-1462000-3 48 31.20 94.6 4.80 400 5760 C 93426 5-1462000-5 Standard Version (550 mW) non-latching 1 coil 4.5 2.90 6.3 0.45 550 C 93438 7-1462000-7 36 5 3.30 7.0 8-1462000-5 0.50 550 45 C 93450 6 7-1462000-6 3.90 8.4 0.60 550 66 C 93437 12 7.80 16.8 1.20 550 280 C 93432 6-1462000-2 24 15.60 33.6 2.40 550 1050 C 93431 6-1462000-1

Further coil versions are available on request.

550

4100

4.80

5-1462000-9

C 93430

67.2

48

31.20


AXICOMTelecom-, Signal and RF Relays

MT2 Relay

Contact Data

Number of contacts ar	nd type	2 changeover contacts
Contact assembly		Bifurcated contacts
Contact material		Silver-nickel, gold-covered
Limiting continuous cu	urrent at max. ambient temperature	2 A
Maximum switching c	urrent	2 A
Maximum swichting voltage		220 Vdc 250 Vac
Maximum switching c	apacity	60 W, 62.5 VA
Thermoelectric potent	tial	< 10 µV
Minimum switching voltage		100 μV
Initial contact resistan	ce / measuring condition: 10 mA / 20 mV	< 70 mΩ
Electrical endurance Resistive load	Contact application 0 (\leq 30 mV / \leq 10 mA) Cable load open end 150 V / 0.2 A - 30 W 24 V / 1.25 A - 30 W	min. 5.0 x 10 ⁶ operations min. 2.5 x 10 ⁶ operations min. 2.0 x 10 ⁵ operations min. 2.0 x 10 ⁵ operations
Mechanical endurance	е	typ. 108 operations
UL contact ratings		220 Vdc / 0.24 A - 60 W 125 Vdc / 0.24 A - 30 W 250 Vac / 0.25 A - 62.5 VA 125 Vac / 0.5 A - 62.5 VA 30 Vdc / 2 A - 60 W

Max. DC Load Breaking Capacity



Telecom-, Signal and RF Relays

MT2 Relay

Insulation

Insulation resistance at 500 Vdc	> 10 ⁹ Ω
Dielectric test voltage (1 min) between coil and contacts between adjacent contact sets between open contacts	1050 Vrms 750 Vrms 750 Vrms
Surge voltage resistance according to FCC 68 (10 / 160 µs) and IEC (10 / 700 µs) between coil and contacts between adjacent contact sets between open contacts	1500 V 1500 V 1500 V

High Frequency Data

Capacitance between coil and contacts between adjacent contact sets between open contacts	max. 4 pF max. 2 pF max. 2 pF
RF Characteristics Isolation at 100 MHz / 900 MHz Insertion loss at 100 MHz / 900 MHz V.S.W.R. at 100 MHz / 900 MHz	- 31.8 dB / - 14.2 dB - 0.02 dB / - 0.97 dB 1.03 / 1.31

General Data

Operate time at U _{nom} typ. / max.	4 ms / 5 ms
Release time without diode in parallel (non-latching), typ. / max.	1 ms / 3 ms
Release time with diode in parallel (non-latching), typ. / max.	4 ms / 6 ms
Bounce time at closing contact, typ. / max.	1 ms / 5 ms
Maximum switching rate without load	50 operations/s
Ambient temperature	-55 °C +85 °C
Thermal resistance	< 85 K/W
Maximum permissible coil temperature	115 °C
Vibration resistance (function)	10 G 10 to 500 Hz
Shock resistance, half sinus, 11 ms	10 G / 30 G (function) 500 G (damage)
Degree of protection / Environmental protection	immersion cleanable, IP 67 / RT III
Needle flame test	application time 10 s
Mounting position	any
Processing information	Ultrasonic cleaning is not recommended
Weight (mass)	max. 5 g
Terminal surface	SnCu 0.7
Resistance to soldering heat	265 °C / 10 s


All data refers to 23 °C unless otherwise specified.

AXICOM

Telecom-, Signal and RF Relays

MT2 Relay

Packing Dimensions in mm



Tube for THT version 25 relays per stick 1'000 relays per box

AXICOM

Telecom-, Signal and RF Relays

MT2 Relay

IM Relays

4th generation slim line – low profile polarized 2 c/o telecom signal relay with bifurcated contacts, available as non latching or latching relay with 1 coil. Nominal voltage range from 1.5 ... 24 V, coil power consumption of 50 ... 200 mW, latching relays with 1 coil 100 mW. The IM relay is available as through hole and surface mount type (J-Legs and Gull Wings) and capable to switch loads up to 60 W/62,5 VA. It is currently the only 2 A rated 4G relay on the market. Dielectric strength fulfills the Telcordia requirements according GR 1089 (2,5 kV – 2 / 10 μ s) and FCC part 68 (1,5 kV – 10 / 160 μ s). The IM relay is tested according CECC/IECQ and certified in accordance with IEC/EN 60950 and UL 60950.

Dimensions approx. 10 x 6 mm board space and 5.65 mm height.

P2 Relays

3rd generation polarized 2 c/o telecom relay with bifurcated contacts, available as non latching or latching relay with 1 or 2 coils. Nominal voltage range from 3 ... 24 V, coil power consumption 140 mW, latching relays with 1 coil 70 mW. The P2 Relay is available as through hole or surface mount type and capable to switch currents up to 5 A. Dielectric strength fulfills the Telcordia requirements according GR 1089 (2,5 kV - 2 / 10 μ s) and FCC part 68 (1,5 kV - 10 / 160 μ s). The P2 relay is tested according CECC/IECQ and certified in accordance with IEC/EN 60950 and UL 60950. Dimensions approx. 15 x 7,5 mm board space and 10 mm height.

FX2 Relays

3rd generation polarized 2 c/o telecom relay with bifurcated contacts, available as non latching or latching relay with 1 coil. Nominal voltage range from 3 ... 48 V, coil power consumption of 80 ... 260 mW for the high sensitive version, 140... 300 mW for the standard version, latching relays with 1 coil 100 mW. The FX2 relay is available as through hole type and capable to switch loads up to 60 W/62,5 VA. Dielectric strength fulfills the Telcordia requirements according GR 1089 (2,5 kV - 2 / 10 μ s) and FCC part 68 (1,5 kV - 10 / 160 μ s). The FX2 relay is tested according CECC/IECQ and certified in accordance with IEC/EN 60950 and UL 60950. Dimensions approx. 15 x 7,5 mm board space and 10,7 mm height.

FT2 / FU2 Relays

3rd generation non polarized, non latching 2 c/o telecom relay with bifurcated contacts. Nominal voltage range from 3 ... 48 V, coil power consumption 200 ... 300 mW. Most sensitive 48 V relay. Available as through hole and surface mount type. Dielectric strength fulfills the Telcordia requirements according GR 1089 (2,5 kV - 2 / 10 μs) and FCC part 68 (1,5 kV - 10 / 160 μs). The FT2/FU2 relay is tested according CECC/IECQ and certified in accordance with IEC/EN 60950 and UL 60950.

Dimensions approx. 15 x 7,5 mm board space and 10 mm height.

FP2 Relays

3rd generation polarized 2 c/o telecom relay with bifurcated contacts, available as non latching or latching relay with 1 or 2 coils. Nominal voltage range from 3 ... 48 V, coil power consumption of 80 ... 260 mW for the high sensitive version, 140... 300 mW for the standard version, latching relays with 1 coil 100 mW.. The FP2 Relay is available as through hole type and capable to switch loads up to 60 W/62,5 VA. Dielectric strength fulfills FCC part 68 (1,5 kV - 10 / 160 μs). The FP2 is tested according CECC/IECQ approved.

Dimensions approx. 14 x 9 mm board space and 5 mm height.

MT2

2nd generation non polarized, non latching 2 c/o telecom and signal relay with bifurcated contacts. Nominal voltage range from 3 ... 48 V, coil power consumption 150/200/300/400 and 550 mW. Dielectric strength fulfills the requirements according FCC part 68 (1,5 kV - 10 / 160 μs).

Dimensions approx. 20 x 10 mm board space and 11 mm height.

D2n Relays

2nd generation non polarized 2 c/o relay for telecom and various other applications. Nominal voltage range from 3 ... 48 V, coil power consumption from 150 500 mW. The D2n relay is capable to switch currents up to 3 A. Dielectric strength fulfills the requirements according FCC part 68 (1,5 kV - 10 / 160 μs). Dimensions approx. 20 x10 mm board space and 11 mm height.

P1 Relays

Extremely sensitive, polarized 1 c/o relay with bifurcated contacts for a wide range of applications, available as non latching or latching relay with 1 or 2 coils. Nominal voltage range from 3 ... 24 V, coil power consumption 65 mW, latching relays with 1 coil 30 mW. The P1 relay is available as through hole or surface mount type and capable to switch currents up to 1 A. Dielectric strength fulfills the requirements according FCC part 68 (1,5 kV - 10 / 160 μ s). Dimensions approx. 13 x 7,6 mm board space and 7 mm height for THT or 8 mm height for SMT version.

W11 Relays

Low cost, non polarized 1 c/o relay for various applications. Nominal voltage range from 3 \dots 24 V, coil power consumption 450 mW, sensitive versions 200 mW. The W11 relay is capable to switch currents up to 3 A. Dielectric strength 1000 Vrms.

Dimensions approx. 15,6 x 10,6 mm board space and 11,5 mm height.

Reed Relays

High sensitive, non polarized relay for telecom and various other applications, available with 1 n/o, 2 n/o or 1c/o contacts. Nominal voltage range from 5 ... 24 V, coil power consumption 50...280 mW for 1 n/o and 125 ... 280 mW for 2 n/o or 1 c/o versions. Reedrelays are available in DIP or SIL housing and capable to switch currents up to 0,5 A. Integrated diode and/or electrostatic shield optional. Dielectric strength 1500 Vdc. Dimensions approx. 19,3 x 7 mm board space and 5 ... 7,5 mm height for DIP or 19,8 x 5 mm board space and 7,8 mm height for SIL version.

Cradle Relays

Extremely reliable and mature relay family of 1st generation for various signal switching applications. Available as non polarized, polarized / latching and relay with AC coil. The benefit is the possibility of combining various contact sets from 1 up to 6 poles, single and bifurcated contacts, different contact materials with a coil voltage range from 1,5 Vdc to 220 Vac. Cradle relays are available as dust protected and hermetically sealed versions, with plug in or solder terminals and are capable to switch currents up to 5 A. Forcibly guided (linked) contact sets optional. Dielectric strength 500 Vrms. Dimensions from approx. 19 x 24 to 19x35 mm board space and 30 mm height.

Other Relays

We offer a variety of different relay families for maintenance and replacement purposes. These relays are up to 60 years old now, such as Card Relay SN (V23030 series), Small General Purpose Relay (V23006 series), Small Polarized Relay (V23063 ... V23067 and V23163 ... V23167 series). Accessories like sockets, hold down springs, etc. optional.

High Frequency Relays

HF3 / HF3S / HF6 series RF relays offering excellent RF characteristics in a small package. All HF series relays are suitable for SMD soldering processes. Available as non latching or latching versions with 1 or 2 coils and a nominal coil voltage range from 3 ... 24 V, a coil power consumption of 140 mW or 70 mW (single coil latching types).

HF3: Low cost RF relay suitable up to 3 GHz. Impedance 50 and 75 Ohm. 50 W hot switching and 50 W RF power carry capability. Dimensions $14.6 \times 7.3 \times 10.3$ mm.

HF3S: High performance, high power RF relay suitable up to 3 GHz, 50 W hot switching and 150 W RF power carry capability. Dimensions $15 \times 7.6 \times 10.6$ mm.

HF6: High performance, high power RF relay suitable up to 6 GHz, 50 W hot switching and 50 W RF power carry capability. Dimensions $15 \times 7.6 \times 10.6 \text{ mm}$.



Tyco Electronics Logistics AG Werk Axicom Au Seestrasse 295 CH-8804 Au-Wädenswil / Switzerland Phone +41 44 782 91 11

Phone +41 44 782 91 11 Fax +41 44 782 90 00

E-mail: axicom@tycoelectronics.com



Tyco Electronics
Paulsternstrasse 26
D-13629 Berlin / Germany
Phone +49 30 386 38573
Fax +49 30 386 38575

E-mail: axicom@tycoelectronics.com



Tyco Electronics EC Trutnov s.r.o. Komenského 821 CZ-541 01 Trutnov / Czech Republic E-mail: axicom@tycoelectronics.com

AXICOMTelecom-, Signal and RF Relays

Tyco Electronics Corporation POB 3608, Harrisburg, PA 17105, USA Phone +1 800-522-6752

