

## [Features]

- RGB interface
- 8-bit digital signals for data of RGB
- low cost
- High contrast ratio



<b>Pixel</b>	480RGB * 272
<b>Display area</b>	95.04 * 53.86mm
<b>Display color</b>	16.7M
<b>Pixel pitch</b>	0.198 * 0.198mm
<b>Luminance</b>	400 cd/m <sup>2</sup> (typ.)
<b>LED lifetime</b>	30K hours
<b>Contrast ratio</b>	900:1 (typ.)
<b>Viewing angle <sup>*1</sup></b>	Up: 70° (typ.), Down: 50° (typ.), Left: 70° (typ.), Right: 70° (typ.)
<b>Response time <sup>*2</sup></b>	20ms (typ.)
<b>Interface</b>	RGB 8-bit
<b>Operating temperature</b>	-20°C to +70°C
<b>Storage temperature</b>	-20°C to +80°C
<b>Polarizer surface</b>	Antiglare
<b>Color gamut<sup>*3</sup></b>	50% (typ.)
<b>Module size</b>	105.5 * 67.20 * 2.90 mm
<b>Weight</b>	44.4g (typ.)
<b>Backlight</b>	LED backlight

\*1: Contrast ratio ≥ 10:1

\*2: Ton+Toff (10%←→90%)

\*3: Against NTSC color space

\*All information is subject to change without notice.

\*Screen image is simulated.