




LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	EC 063C 0826 04			15FEB05	BSV	JLG



RECOMMENDED BOARD LAYOUT

1. DIMENSION APPLIES OVER 99.06mm [3.900 INCHES].
2. HOUSING: BLACK THERMOPLASTIC, 94V-0 RATED, HIGH TEMPERATURE COMPATIBLE. POST: PHOSPHOR BRONZE.
3. FINISH: 0.00076[.000030] GOLD IN MATING AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN–LEAD ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
4. POINT OF MEASUREMENT FOR PLATING THICKNESS.
5. THE NOTED DIMENSION APPLIES AT INTERSECTION OF POST AND HOUSING.
6. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PCB.
7. PARTS ARE TO BE PACKAGED ON A REEL.
8. REELED ASSEMBLIES ARE TO BE BROKEN TO THE DESIRED POSITION SIZE AND USED AS A FUNCTIONAL SUBSTITUTE/ALTERNATIVE TO THE EXISTING AMP PART NUMBER SERIES 102976 AND 146277. THESE ASSEMBLIES ARE THE SAME IN FIT AND FUNCTION, BUT THE FORM WILL BE SLIGHTLY DIFFERENT (i.e. MOLDED HOUSING APPEARANCE AND BOW, DUE TO REELING REQUIREMENTS).
9. THIS PART NUMBER SPECIFIES ONE(1) LINE (i.e. PIN).
10. FINISH: 0.00076[.000030] GOLD IN MATING AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.

10	5-146870-1	9
3	146870-1	9
PLATING	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F. BRANDBERG 05-SEP-97	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		OK C. SCHMID 05-SEP-97	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. SCHMID 05-SEP-97	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE
1 PLC ± -		WEIGHT		CAGE CODE
2 PLC ± 0.13 [005]		CUSTOMER DRAWING		DRAWING NO
3 PLC ± -		SCALE 10:1		SHEET 1 OF 1
4 PLC ± -		REV B		REV
ANGLES ± -				
FINISH SEE TABLE				