

POST OMITTED (SEE TABLE FOR LOCATION)	FINISH	NO. OF DUAL POSITIONS	PART NUMBER
19, 20, 21, 22, 23, 24, 27, 28, 31, 32, 35, 36, 39	△6	11	8-5530843-5
40, 43, 44, 45, 46, 47, 48, 51, 52, 55, 56, 59, 60	△6	31	8-5530843-4
3, 4, 5, 6, 19, 20, 21, 22	△6	12	8-5530843-3
-	△6	3	7-5530843-7
-	△6	6	7-5530843-6
-	△6	5	7-5530843-5
-	△6	6	7-5530843-4
-	△6	5	7-5530843-3
-	△5	31	6-5530843-5
-	△6	30	6-5530843-4
-	△6	31	6-5530843-3
-	△6	30	6-5530843-2
-	△6	31	6-5530843-1
-	△6	30	5-5530843-7
-	△6	34	5-5530843-6
-	△6	35	5-5530843-3
-	△6	49	5-5530843-2
-	△6	50	5-5530843-0
-	△6	24	2-5530843-6
-	△6	25	1-5530843-6
-	△6	42	1-5530843-3
-	△6	43	1-5530843-0
-	△6	30	1-5530843-8
-	△6	29	1-5530843-7
-	△6	39	1-5530843-4
-	△6	40	2-5530843-0
-	△6	30	1-5530843-8
-	△6	34	2-5530843-3
-	△6	35	2-5530843-2
-	△6	49	2-5530843-3
-	△6	50	2-5530843-0
-	△6	24	1-5530843-6
-	△6	25	1-5530843-3
-	△6	42	1-5530843-0
-	△6	43	1-5530843-3
-	△6	35	5530843-8
-	△6	36	5530843-7
-	△6	29	5530843-4
-	△6	30	5530843-3
-	△6	28	5530843-6
-	△6	27	5530843-5
-	△6	24	5530843-3
-	△6	25	5530843-5
-	△6	21	5530843-4
-	△6	22	5530843-3
-	△6	17	5530843-3
-	△6	18	5530843-4
-	△6	14	5530843-2
-	△6	15	5530843-3
-	△6	11	5530843-1
OMITTED PIN	△6	12	5530843-1

- △1 MATERIAL: HOUSING - GLASS FILLED POLYESTER, COLOR BLACK CONTACT - PHOSPHOR BRONZE
- △2 FINISH: (SEE TABLE FOR GOLD PLATING) IN CONTACT AREA. .000100 MIN MATTE TIN ON SOLDER POSTS. ALL OVER .000050 MIN THK. NICKEL
- △3 AMP LOGO, TE PART NUMBER, DATE CODE AND CSA LOGO INK STAMPED WHITE (HOT STAMPED OR LAZER PRINTED) IN THE APPROXIMATE AREA SHOWN, EITHER SIDE PERMISSIBLE WHEN HOUSING SIZE PERMITS
- 4. RECOMMENDED PCB FINISHED HOLE  $\phi$ .040 ± .003
- △5 .000015 MIN
- △6 .000030 MIN
- △7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

REV	DESCRIPTION	DATE	BY	CHKD	APP'D
E2	REV PER ECO-09-024025				
E3	REV PER ECO-10-000444	22JAN10	HK	IHR	
E4	REV PER ECO-10-016782	22SEP10	RG	MS	

300012009  
 E-HOMARD  
 TICO Electronics  
 HARRISBURG, PA 17105-8088


300012009  
 E-HOMARD  
 TICO Electronics  
 HARRISBURG, PA 17105-8088

CONNECTOR ASSEMBLY  
 STANDARD EDGE 11,  
 .100 CENTERLINE


SIZE CODE DRAWING NO.  
 A1100779

RESTRICTED TO

SCALE 4:1 SHEET 1 OF 2 REV E4



RECOMMENDED MAIN BOARD EDGE CONFIGURATION



RECOMMENDED PC BOARD HOLE LAYOUT

<p>THE INFORMATION CONTAINED HEREIN IS UNCLASSIFIED EXCEPT WHERE SHOWN OTHERWISE BY THE FOLLOWING IDENTIFICATION DATA:</p> <p>CLASSIFICATION AUTHORITY: 15X-10000</p> <p>DECLASSIFICATION DATE: 15X-10000</p>	
<p>OPERATIONS:</p> <p>INCHES</p>	<p>TOLERANCES UNLESS OTHERWISE SPECIFIED:</p> <p>0 P.C. ±</p> <p>1 P.C. ±.005</p> <p>2 P.C. ±.005</p> <p>3 P.C. ±.005</p> <p>4 P.C. ±.005</p> <p>FINISH:</p>
<p>DATE: 30 OCT 12 00 9</p> <p>BY: E. HORNARD</p> <p>APP. 109-9039</p> <p>114-13018</p>	<p>TRIO Electronics</p> <p>Harrisburg, PA 17105-8008</p> <p>CONNECTOR ASSEMBLY</p> <p>STANDARD EDGE 11,</p> <p>.100 CENTERLINE</p> <p>SIZE: CODE: DRAWING NO.:</p> <p>A1100779 5530843</p> <p>SCALE: 4:1 SHEET 2 OF 2 REV. A</p>