


## Solid Tantalum Chip Capacitors, TANTAMOUNT<sup>®</sup>, Conformal Coated



### FEATURES

- Pad compatible with 194D and MIL-C-55365/4 (CWR06)
- 8 mm, 12 mm 16 mm Tape to EIA-481-2 and reeling per IEC 286-3. 7" [178 mm] standard 13" [330 mm] available.
- Terminations: Tin (2) standard
- Compliant to RoHS directive 2002/95/EC



Available  
**RoHS\***  
COMPLIANT

### PERFORMANCE CHARACTERISTICS

**Operating Temperature:** - 55 °C to + 85 °C  
(To + 125 °C with voltage derating)

#### Note

- Refer to Doc. 40088

**Capacitance Range:** 1.0 µF to 270 µF

**Capacitance Tolerance:** ± 10 %, ± 20 % standard

**Voltage Rating:** 4 WVDC to 50 WVDC

ORDERING INFORMATION						
695D	475	X0	004	A	2	T
TYPE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT + 85 °C	CASE CODE	TERMINATION	REEL SIZE AND PACKAGING
	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	<b>X0 = ± 20 %</b> <b>X9 = ± 10 %</b>	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V).	See ratings and case codes table	<b>2 = 100 % Tin</b> 4 = Gold plated 8 = Solder plated (60/40) Special order	<b>T = Tape and reel*</b> <b>7" [178 mm] reel</b> W = 13" [330 mm] reel See tape and reel specifications

#### Notes

- Preferred tolerance and reel sizes are in bold
- We reserve the right to supply higher voltage ratings and tighter capacitance tolerance capacitors in the same case size.
- Voltage substitutions will be marked with the higher voltage rating.

DIMENSIONS in inches [millimeters]							
CASE CODE	L (MAX.)	D (REF.)	W	H	A	B	J (MAX.)
A	0.135 [3.4]	0.100 [2.54]	0.050 ± 0.015 [1.27 ± 0.38]	0.050 ± 0.015 [1.27 ± 0.38]	0.023 ± 0.010 [0.584 ± 0.25]	0.067 ± 0.015 [1.70 ± 0.38]	0.004 [0.10]
B	0.185 [4.7]	0.150 [3.81]	0.050 ± 0.015 [1.27 ± 0.38]	0.050 ± 0.015 [1.27 ± 0.38]	0.040 ± 0.015 [1.02 ± 0.38]	0.120 ± 0.015 [3.05 ± 0.38]	0.004 [0.10]
D	0.185 [4.7]	0.140 [3.56]	0.095 ± 0.015 [2.41 ± 0.38]	0.050 ± 0.015 [1.27 ± 0.38]	0.040 ± 0.015 [1.02 ± 0.38]	0.110 ± 0.020 [2.79 ± 0.51]	0.004 [0.10]
E	0.235 [6.0]	0.200 [5.08]	0.095 ± 0.015 [2.41 ± 0.38]	0.050 ± 0.015 [1.27 ± 0.38]	0.040 ± 0.015 [1.02 ± 0.38]	0.170 ± 0.020 [4.32 ± 0.51]	0.004 [0.10]
F	0.255 [6.5]	0.220 [5.59]	0.135 ± 0.015 [3.43 ± 0.38]	0.070 ± 0.015 [1.78 ± 0.38]	0.040 ± 0.015 [1.02 ± 0.38]	0.185 ± 0.020 [4.70 ± 0.51]	0.004 [0.10]
G	0.300 [7.6]	0.260 [6.60]	0.100 ± 0.015 [2.54 ± 0.38]	0.100 ± 0.015 [2.54 ± 0.38]	0.040 ± 0.015 [1.02 ± 0.38]	0.220 ± 0.020 [5.59 ± 0.51]	0.004 [0.10]
H	0.303 [7.7]	0.265 [6.73]	0.150 ± 0.015 [3.81 ± 0.38]	0.110 ± 0.015 [2.79 ± 0.38]	0.050 ± 0.015 [1.27 ± 0.38]	0.220 ± 0.020 [5.59 ± 0.51]	0.004 [0.10]

#### Note

- The anode termination (D less B) will be a minimum of 0.010" (0.3 mm). T Case = 0.005 (0.13 mm) minimum.

\* Pb containing terminations are not RoHS compliant, exemptions may apply

RATINGS AND CASE CODES								
μF	4 V	6 V	10 V	15 V	20 V	25 V	35 V	50 V
0.10								A
0.15								A
0.22							A	B
0.33							A	B
0.47						A	B	D
0.68						A	B	D
1.0					A	B	D	D
1.5				A	B	D	D	E
2.2				A	B	D	E	F
3.3			A	B	D	D	F	F
4.7	A	A	B	D	D	E	F	G
6.8	B	B	D	D	E	F	F	H
10	B	D	D	D	F	F	G	H
15	D	D	D	E	F	G	H	
22	D	D	E	F	G	H		
33	E	E	F	F	G	H		
47	F	F	F	G	H			
68	F	F	G	H				
100	F	G	G	H				
120	G	G	H					
150	G	H	H					
180	H	H						
220	H	H						
270	H							

STANDARD RATINGS							
CAPACITANCE (μF)	CASE CODE	PART NUMBER*	MAX. DCL AT + 25 °C (μA)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I <sub>rms</sub> (A)	
<b>4 WVDC AT + 85 °C, 2.7 WVDC AT + 125 °C</b>							
4.7	A	695D475X_004A2T	0.5	6	11	0.07	
6.8	B	695D685X_004B2T	0.5	6	9.0	0.09	
10	B	695D106X_004B2T	0.5	6	8.5	0.09	
15	D	695D156X_004D2T	0.6	6	2.2	0.20	
22	D	695D226X_004D2T	0.9	6	2	0.21	
33	E	695D336X_004E2T	1.3	6	1.5	0.25	
47	F	695D476X_004F2T	1.9	6	1.0	0.33	
68	F	695D686X_004F2T	2.7	6	0.9	0.35	
100	F	695D107X_004F2T	4.0	8	0.9	0.35	
120	G	695D127X_004G2T	4.8	8	0.7	0.41	
150	G	695D157X_004G2T	6.0	8	0.65	0.43	
180	H	695D187X_004H2T	7.2	8	0.40	0.61	
220	H	695D227X_004H2T	8.8	8	0.35	0.65	
270	H	695D277X_004H2T	10.8	8	0.35	0.65	
<b>6 WVDC AT + 85 °C, 4 WVDC AT + 125 °C</b>							
4.7	A	695D475X_006A2T	0.5	6	11	0.07	
6.8	B	695D685X_006B2T	0.5	6	9.0	0.07	

**Note**

\* For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".

Solid Tantalum Chip Capacitors,  
TANTAMOUNT® Leadframeless Molded

Vishay Sprague

<b>STANDARD RATINGS</b>						
CAPACITANCE ( $\mu$ F)	CASE CODE	PART NUMBER*	MAX. DCL AT + 25 °C ( $\mu$ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz ( $\Omega$ )	MAX. RIPPLE 100 kHz I <sub>rms</sub> (A)
<b>6 WVDC AT + 85 °C, 4 WVDC AT + 125 °C</b>						
10	D	695D106X_006D2T	0.6	6	8.5	0.1
15	D	695D156X_006D2T	0.9	6	2.2	0.2
22	D	695D226X_006D2T	1.3	6	2.0	0.32
33	E	695D336X_006E2T	2.0	6	1.5	0.25
47	F	695D476X_006F2T	2.8	6	1.0	0.33
68	F	695D686X_006F2T	4.1	6	0.9	0.35
100	G	695D107X_006G2T	6.0	8	0.9	0.37
120	G	695D127X_006G2T	7.2	8	0.7	0.41
150	H	695D157X_006H2T	9.0	8	0.65	0.48
180	H	695D187X_006H2T	10.8	8	0.40	0.61
220	H	695D227X_006H2T	13.2	8	0.35	0.65
<b>10 WVDC AT + 85 °C, 7 WVDC AT + 125 °C</b>						
3.3	A	695D335X_010A2T	0.5	6	11.5	0.07
4.7	B	695D475X_010B2T	0.5	6	10.6	0.08
6.8	D	695D685X_010D2T	0.7	6	2.6	0.18
10	D	695D106X_010D2T	1.0	6	2.5	0.18
15	D	695D156X_010D2T	1.5	6	2.2	0.20
22	E	695D226X_010E2T	2.2	6	2.0	0.22
33	F	695D336X_010F2T	3.3	6	1.2	0.30
47	F	695D476X_010F2T	4.7	6	1.0	0.33
68	G	695D686X_010G2T	6.8	6	0.75	0.40
100	G	695D107X_010G2T	10	8	0.75	0.40
120	H	695D127X_010H2T	12	8	0.45	0.58
150	H	695D157X_010H2T	15	8	0.40	0.61
<b>15 WVDC AT + 85 °C, 10 WVDC AT + 125 °C</b>						
1.5	A	695D155X_015A2T	0.5	6	14	0.07
2.2	A	695D225X_015A2T	0.5	6	12	0.07
3.3	B	695D335X_015B2T	0.5	6	10.8	0.08
4.7	D	695D475X_015D2T	0.7	6	2.8	0.17
6.8	D	695D685X_015D2T	1	6	2.6	0.18
10	D	695D106X_015D2T	1.5	6	2.5	0.18
15	E	695D156X_015E2T	2.3	6	2.3	0.20
22	F	695D226X_015F2T	3.3	6	1.4	0.28
33	F	695D336X_015F2T	5	6	1.2	0.30
47	G	695D476X_015G2T	7.1	6	0.8	0.39
68	H	695D686X_015H2T	10.2	6	0.5	0.55
100	H	695D107X_015H2T	15	8	0.45	0.58
<b>20 WVDC AT + 85 °C, 13 WVDC AT + 125 °C</b>						
1.0	A	695D105X_020A2T	0.5	4	15	0.06
1.5	B	695D155X_020B2T	0.5	6	12	0.08
2.2	B	695D225X_020B2T	0.5	6	11	0.08
3.3	D	695D335X_020D2T	0.7	6	3.0	0.17

**Note**








\* For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".

<b>STANDARD RATINGS</b>							
CAPACITANCE ( $\mu\text{F}$ )	CASE CODE	PART NUMBER*	MAX. DCL AT + 25 °C ( $\mu\text{A}$ )	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz ( $\Omega$ )	MAX. RIPPLE 100 kHz I <sub>rms</sub> (A)	
<b>20 WVDC AT + 85 °C, 13 WVDC AT + 125 °C</b>							
4.7	D	695D475X_020D2T	0.9	6	2.8	0.17	
6.8	E	695D685X_020E2T	1.4	6	2.55	0.19	
10	F	695D106X_020F2T	2.0	6	1.8	0.25	
15	F	695D156X_020F2T	3.0	6	1.5	0.27	
22	G	695D226X_020G2T	4.4	6	0.9	0.37	
33	G	695D336X_020G2T	6.6	6	0.8	0.39	
47	H	695D476X_020H2T	9.4	6	0.5	0.55	
<b>25 WVDC AT + 85 °C, 17 WVDC AT + 125 °C</b>							
0.47	A	695D474X_025A2T	0.5	4	17	0.06	
0.68	A	695D684X_025A2T	0.5	4	15	0.06	
1.0	B	695D105X_025B2T	0.5	4	13	0.08	
1.5	D	695D155X_025D2T	0.5	6	4.2	0.14	
2.2	D	695D225X_025D2T	0.6	6	3.5	0.16	
3.3	D	695D335X_025D2T	0.8	6	3.0	0.17	
4.7	E	695D475X_025E2T	1.2	6	2.75	0.19	
6.8	F	695D685X_025F2T	1.7	6	2.0	0.23	
10	F	695D106X_025F2T	2.5	6	1.8	0.25	
15	G	695D156X_025G2T	3.8	6	1.0	0.35	
22	H	695D226X_025H2T	5.5	6	0.7	0.46	
33	H	695D336X_025H2T	8.3	6	0.8	0.50	
<b>35 WVDC AT + 85 °C, 23 WVDC AT + 125 °C</b>							
0.22	A	695D224X_035A2T	0.5	4	20	0.05	
0.33	A	695D334X_035A2T	0.5	4	18	0.06	
0.47	B	695D474X_035B2T	0.5	4	15	0.07	
0.68	B	695D684X_035B2T	0.5	4	14	0.07	
1.0	D	695D105X_035D2T	0.5	4	8.0	0.10	
1.5	D	695D155X_035D2T	0.5	6	4.2	0.14	
2.2	E	695D225X_035E2T	0.8	6	4.0	0.15	
3.3	F	695D335X_035F2T	1.2	6	3.2	0.19	
4.7	F	695D475X_035F2T	1.6	6	2.7	0.20	
6.8	F	695D685X_035F2T	2.4	6	2.0	0.23	
10	G	695D106X_035G2T	3.5	6	1.3	0.30	
15	H	695D156X_035H2T	5.3	6	0.8	0.43	
<b>50 WVDC AT + 85 °C, 33 WVDC AT + 125 °C</b>							
0.10	A	695D104X_050A2T	0.5	4	32	0.04	
0.15	A	695D154X_050A2T	0.5	4	30	0.04	
0.22	B	695D224X_050B2T	0.5	4	18	0.06	
0.33	B	695D334X_050B2T	0.5	4	16	0.07	
0.47	D	695D474X_050D2T	0.5	4	9.0	0.10	
0.68	D	695D684X_050D2T	0.5	4	8.5	0.10	
1.0	D	695D105X_050D2T	0.5	4	8.0	0.10	
1.5	E	695D155X_050E2T	0.8	6	5.5	0.13	
2.2	F	695D225X_050F2T	1.1	6	3.9	0.17	
3.3	F	695D335X_050F2T	1.7	6	3.2	0.19	
4.7	G	695D475X_050G2T	2.4	6	2.5	0.22	
6.8	H	695D685X_050H2T	3.4	6	1.2	0.35	
10	H	695D106X_050H2T	5.0	6	1.0	0.39	

**Note**

\* Preliminary values, contact factory for availability. For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".

**TYPICAL CURVES AT + 25 °C, IMPEDANCE AND ESR VS. FREQUENCY**





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.